

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A00183 MST GUM REMOVER II 12net6

Material number : 00000000001001654

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers**For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation
Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616**SECTION 2. HAZARDS IDENTIFICATION****Emergency Overview**

Appearance	Aerosol containing a liquefied gas
Colour	clear
Odour	odourless

GHS ClassificationFlammable aerosols : Category 1
Gases under pressure : Liquefied gas**GHS Label element**

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.
H280 Contains gas under pressure; may explode if heated.Precautionary statements : **Prevention:**
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Pressurized container: Do not pierce or burn, even after use.
Storage:
P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

Potential Health Effects
Carcinogenicity:
IARC

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

OSHA

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical Name	CAS-No.	Concentration [%]
butane	106-97-8	>= 70 - < 90
propane	74-98-6	>= 20 - < 30

SECTION 4. FIRST AID MEASURES

- General advice : Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.
- If inhaled : If unconscious place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Get medical attention if irritation develops and persists.
Wash contaminated clothing before re-use.
Wash off immediately with plenty of water for at least 15 minutes.
- In case of eye contact : Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
If in eyes, rinse with water for 15 minutes.
- If swallowed : Keep respiratory tract clear.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
DO NOT induce vomiting unless directed to do so by a

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

physician or poison control center.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
Water spray jet
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : For safety reasons in case of fire, cans should be stored separately in closed containments.
Use a water spray to cool fully closed containers.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Ensure adequate ventilation.
Remove all sources of ignition.
Evacuate personnel to safe areas.
Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Sweep up or vacuum up spillage and collect in suitable container for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

Take precautionary measures against static discharges.
 Provide sufficient air exchange and/or exhaust in work rooms.
 Open drum carefully as content may be under pressure.
 Dispose of rinse water in accordance with local and national regulations.
 Always replace cap after use.
 Do not breathe vapours or spray mist.

Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
 No smoking.
 Observe label precautions.
 Keep in a cool, well-ventilated place.
 Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
butane	106-97-8	TWA	800 ppm 1,900 mg/m ³	NIOSH REL
		TWA	800 ppm 1,900 mg/m ³	OSHA P0
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0

Personal protective equipment

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment.

Hand protection
 Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection : Eye wash bottle with pure water
 Tightly fitting safety goggles

Skin and body protection : impervious clothing
 Choose body protection according to the amount and concentration of the dangerous substance at the work place.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

Hygiene measures : Wash hands before breaks and at the end of workday.
When using do not smoke.
When using do not eat or drink.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Colour : clear

Odour : odourless

Odour Threshold : no data available

pH : not applicable

Melting point/freezing point : no data available

Boiling point : no data available

Flash point :
no data available

Evaporation rate : no data available

Upper explosion limit : no data available

Lower explosion limit : no data available

Vapour pressure : no data available

Relative vapour density : no data available

Density : no data available

Solubility(ies)

Water solubility : negligible

Partition coefficient: n-octanol/water : no data available

Auto-ignition temperature : not determined

Thermal decomposition : no data available

Viscosity

Viscosity, kinematic : no data available

Heat of combustion : 49.35 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity : Stable

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : No decomposition if stored and applied as directed.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

Vapours may form explosive mixture with air.

Conditions to avoid	:	Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	:	Strong oxidizing agents
Hazardous decomposition products	:	Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity**

no data available

Skin corrosion/irritation

no data available

Serious eye damage/eye irritation

no data available

Respiratory or skin sensitisation

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

no data available

Reproductive toxicity

no data available

butane:**propane:****STOT - single exposure**

no data available

STOT - repeated exposure

no data available

Aspiration toxicity

no data available

Further information**Product:**

Remarks: no data available

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

SECTION 12. ECOLOGICAL INFORMATION
Ecotoxicity

no data available

Persistence and degradability

no data available

Bioaccumulative potential
Product:

 Partition coefficient: n-
 octanol/water : Remarks: no data available

Components:
butane :

 Partition coefficient: n-
 octanol/water : Pow: 2.89

Mobility in soil

no data available

Other adverse effects

no data available

Product:

 Regulation 40 CFR Protection of Environment; Part 82 Protection of
 Stratospheric Ozone - CAA Section 602 Class I
 Substances

 Remarks This product neither contains, nor was manufactured
 with a Class I or Class II ODS as defined by the U.S.
 Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A
 + B).

 Additional ecological
 information : no data available

SECTION 13. DISPOSAL CONSIDERATIONS
Disposal methods

Waste from residues : Dispose of in accordance with local regulations.

 Do not dispose of waste into sewer.
 Do not contaminate ponds, waterways or ditches with
 chemical or used container.

 Contaminated packaging : Empty remaining contents.
 Dispose of as unused product.
 Do not re-use empty containers.
 Do not burn, or use a cutting torch on, the empty drum.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, 2.1, - Limited quantity

SECTION 15. REGULATORY INFORMATION**EPCRA - Emergency Planning and Community Right-to-Know Act****CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Sudden Release of Pressure Hazard
Fire Hazard

SARA 302 : SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL.
AICS On the inventory, or in compliance with the inventory
NZIoC On the inventory, or in compliance with the inventory
PICCS On the inventory, or in compliance with the inventory
IECSC On the inventory, or in compliance with the inventory

A00183 MST GUM REMOVER II 12net6


Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015

Inventory Acronym and Validity Area Legend:

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TSCA (USA)

SECTION 16. OTHER INFORMATION**Further information****NFPA:****HMIS III:**

HEALTH	3
FLAMMABILITY	4
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA GHS Label Information:

Hazard pictograms



Signal word

: **Danger:**

Hazard statements

: Extremely flammable aerosol. Contains gas under pressure; may explode if heated.

Precautionary statements

:

Prevention: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source.
Pressurized container: Do not pierce or burn, even after use.

Storage: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.

A00183 MST GUM REMOVER II 12net6

Version 1.0

Revision Date 02/24/2015

Print Date 06/01/2015
