

APEX **6500**

PEAK COOLING, INTELLIGENT CONTROL

Experience the Portacool Apex[™] 6500, where innovation and simplicity keep you cool in any environment. With a noise level similar to a hairdryer at 68 dB, this cooler is perfect for large spaces spanning up to 6500 square feet. It's well-suited for industrial warehouses, manufacturing facilities, expansive commercial venues, and outdoor festivals, providing ample cooling coverage without causing excessive noise disturbances. Enjoy a refreshing breeze that extends up to 40 ft. while ensuring a comfortable sound level.

- 1. Smart, Connected Cooling
- 2. Quiet, Efficient, and Far-Reaching
- 3. Rugged, Portable, and Smartly Designed



POWERED BY COOLSYNC™ TECHNOLOGY.

The ultimate evaporative coolers are here. Connectivity powered by CoolSync[™] Technology. Sync your cooler to your smartphone and take total control from anywhere.

- Easily adjust fan speeds
- Control multiple units simultaneously
- Schedule run-times in advance
- Set a timer for the cooling duration

Lifetime warranty on all molded housings.

3yr. *Limited warranty on motor and electrical components.



PORTACOOL

POWERFUL & EFFICIENT COOLING:

This chart illustrates the remarkable cooling capabilities of the Apex Series high-velocity evaporative coolers. The Apex 6500, designed for cooling spaces up to 6500 square feet, creates a refreshing breeze that extends up to 40 feet.



APEX 6500

- Extended Cooling Reach -Our high-velocity cooler delivers a refreshing breeze up to 40 ft. away.
- Whisper Quiet Performance The unique fan blade and
 motor design combination
 minimizes noise, creating a
 tranquil environment while
 delivering powerful cooling.
- Simplify Your Space New housing design keeps cords and connections neatly tucked away at the back for a cleaner, smarter cooler experience.
- Unmatched Portability -Built-in handles and lightweight housing ensure easy transportation over any terrain.

Tough-coat rotational molded textured housing

Built-in handles

Enhanced fan and motor design is quieter and more efficient

Durable polyolefin wheels _____

Digital display with CoolSync™ technology

Improved /8" Portacool edge-coat media technology with new water distribution process

Recessed hose and power cord location

MODEL NUMBER	OPTIMAL COOLING (Sq. Ft.)	VELOCITY (Mph)	AIR FLOW REACH (Ft.)	NOISE (dB)	WATER RESERVOIR (Gallons)	PRODUCT WEIGHT (Without Water)	AIRFLOW (CFM'S)	AMP'S	DIMENSIONS (In.)
PACA65001A1	UP TO 6500	24	40	68	66	290	22000	14.7	(HEIGHT) 90 (DEPTH) 39 (WIDTH) 78

Lifetime warranty on all molded housings.

3yr. *Limited warranty on motor and electrical components.



www.portacool.com

Portacool parts and accessories are available online at portacool.com or through your local distributor or retail location.

PARMKTLT508 3/04/24