



The Cruiser is a durable, versatile tool for industrial counting and weighing needs. Ideal for inventory control tasks or checkweighing during packaging processes, Cruiser can help reduce waste and eliminate overages. Backlit display changes color to show if a sample is under, over, or within the preset limits. Store and recall up to 100 product lookups or piece weights to improve efficiency in production or warehouse applications. Designed to be tough, the Cruiser features ABS housing, stainless steel platform, non-slip feet and load cell protection.

## Powerful Performance for Industrial Applications



### Features

- Backlit display changes color for quick notification of checkweighing limits
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows swift cleaning
- RS-232 interface is available to provide speedy connection to computers and printers
- Optional USB interface simplifies data communication
- Sealed keypad protects against dirt and spills
- Solid ABS housing is durable for industrial use
- Adjustable leveling feet help optimize setup
- Drip channels help divert spills away from the scales internal components
- Checkweighing with audible alarm
- External calibration allows for verification and adjustment with weights
- Internal counting resolution 1:600,000 for precise results
- Parts counting optimization automatically refines piece weight as parts are added
- Parts counting with freely selectable sample sizes
- Preset tare function speeds the process of repetitive weighing
- Product look up (PLU) memory locations store a range of items for recall
- Programmable auto power-off to save energy
- Rechargeable battery included for operation almost anywhere

### Applications

- Weighing
- Parts counting
- Checkweighing
- Check counting
- Accumulation
- Percentage weighing
- Net total weighing

### About ADAM:

For more than 45 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	CKT 4	CKT 8	CKT 16	CKT 32	CKT 48	CKT 8H	CKT 8UH	CKT 16UH	CKT 32UH	CKT 48UH
<b>Capacity</b>	8lb / 4kg	16lb / 8kg	35lb / 16kg	70lb / 32kg	100lb / 48kg	16lb / 8kg	16lb / 8000g	35lb / 16kg	70lb / 32kg	100lb / 48kg
<b>Readability</b>	0.0002lb / 0.1g	0.0005lb / 0.2g	0.001lb / 0.5g	0.002lb / 1g	0.005lb / 2g	0.0002lb / 0.1g	0.0001lb / 0.05g	0.0002lb / 0.1g	0.0005lb / 0.2g	0.001lb / 0.5g
<b>Repeatability (S.D.)</b>	0.0004lb / 0.2g	0.001lb / 0.4g	0.002lb / 1g	0.004lb / 2g	0.01lb / 4g	0.0004lb / 0.2g	0.0002lb / 0.1g	0.0004lb / 0.2g	0.001lb / 0.4g	0.002lb / 1g
<b>Linearity (+/-)</b>	0.0006lb / 0.3g	0.001lb / 0.6g	0.003lb / 1.5g	0.006lb / 3g	0.01lb / 6g	0.0006lb / 0.3g	0.0006lb / 0.3g	0.001lb / 0.6g	0.003lb / 1.2g	0.006lb / 3g
<b>Pan Size</b>	8.3"x11.8" / 210x300mm									
<b>Weighing Units</b>	g, kg, lb, oz, lb:oz									
<b>Stabilization Time (sec)</b>	2									
<b>Interface</b>	RS-232, Optional USB									
<b>Calibration</b>	External calibration									
<b>Display</b>	Backlit LCD with 0.6" / 15mm -high digits									
<b>Power Supply</b>	12VDC 800mA adapter / Internal rechargeable battery									
<b>Operating Temperature</b>	-10° to 40°C / 14° to 104°F									
<b>Housing</b>	ABS plastic									
<b>Overall Dim.</b>	12.8"x14"x4.5" / 326x355x115mm (wxdxh)									
<b>Net Weight</b>	7.3lb / 3.29kg									

## Accessories

Item number	Description
3022013912	Hard carrying case with lock
2020013913	In-use cover (pack of 5)
2020013914	In-use cover (pack of 10)
3022013911	In-use wet cover
3074010267	USB cable
3014011014	RS-232 cable M-F
1120014641	AIP impact printer
1120011156	ATP thermal printer
600002028	AdamDU Data Collection Program
202000001	Weigh-below hook (factory fitted)
700660290	Calibration certificate
2020013915	USB option

## Key Accessories



### ATP thermal printer

Easy-to-use features combined with quick set-up equals a truly versatile thermal printer. A single push-button feed key and three easy-to-read LED indicators make operation simple.



### AdamDU data collection program

Adam DU software connects a balance to the laboratory network, helping to achieve seamless data collection, transfer and analysis. DU features an easy-to-use interface with a main command window, allowing users to quickly collect information from up to eight Adam balances simultaneously using RS-232 or USB connections.

## Supplied by