



FEATURES:

- Adjustable height for easy transition between carpet and hard floor surfaces.
- LED headlight and full bag indicator.
- Deodorizing carbon HEPA filter; 2 filtration system.
- Lays completely flat for easy cleaning under low furniture.
- On-board tools including: telescopic wand; crevice tool; upholstery tool; dust brush; extension wand; small area turbo brush.
- Pigtail detachable power cord, with drop-down cord wrap.
- Easy-access magnet cap prevents metal debris from entering the vacuum.

SPECIFICATIONS:

Cleaning Path:	14"
Motor:	1000W; 9.2 Amp; Single Fan
Power Cord:	50' detachable
Cubic Ft./Min:	112
Bag Capacity:	6.62 Liter
Full Bag Indicator:	Yes
Power Control:	1 Speed
Carpet/Floor:	Yes
Water Lift:	78"
Dimensions:	14.6"L x 15.8"W x 44.9"H
Weight:	20 Lbs.
Filtration:	Deodorizing HEPA Filter & Filter Bag
Decibels:	69
Hose Length:	6-1/2'
RPM:	2720
Head Light:	LED
Certification:	ETL; cETL

