

# SAFETY DATA SHEET



Issuing Date: 06-Mar-2015

Revision Date: 06-Mar-2015

Version 1

## 1. IDENTIFICATION

<b>Product Name</b>	Tide Pods - Ocean Mist
<b>Product ID:</b>	97050613_RET_NG
<b>Product Type:</b>	Finished Product - Consumer (Retail) Use Only
<b>Recommended Use</b>	Laundry Care
<b>Restrictions on Use</b>	Use only as directed on label. Keep out of reach of children.
<b>Synonyms</b>	Tide Pods - Spring Meadow (97050612_RET_NG)
<b>Manufacturer</b>	PROCTER & GAMBLE - Fabric and Home Care Division. Ivorydale Technical Centre. 5289 Spring Grove Avenue, Cincinnati, Ohio 45217-1087 USA
<b>E-mail Address</b>	pgsds.im@pg.com
<b>Emergency Telephone</b>	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

## 2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

**This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:**

### Hazard Category

<b>Acute toxicity - Oral</b>	Category 4
<b>Skin corrosion/irritation</b>	Category 2
<b>Eye Damage / Irritation</b>	Category 2A

**Signal Word** WARNING

**Hazard Statements**  
Causes serious eye irritation  
Harmful if swallowed  
Causes skin irritation

**Hazard pictograms**

**Precautionary Statements - Prevention**

Wash hands thoroughly after handling  
Do not eat, drink or smoke when using this product

**Precautionary Statements - Response**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
If eye irritation persists: Get medical advice/attention  
IF SWALLOWED:  
Rinse with plenty of water  
Drink 1 or 2 glasses of water  
Call a POISON CENTER or doctor/physician if you feel unwell  
IF ON SKIN:  
Rinse with plenty of water  
If skin irritation occurs, get medical advice/attention

**Precautionary Statements - Storage**

None

**Precautionary Statements - Disposal**

None

**Hazards not otherwise classified (HNOC)**

None

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
MEA-Dodecylbenzenesulfonate	-	No	68910-32-7	20 - 25
Propylene glycol	-	No	57-55-6	15 - 20
Alcohols, C12-16, ethoxylated	-	No	68551-12-2	10 - 15
Ethanol, 2-amino-, compds. with polyethylene glycol hydrogen sulfate C12-15-alkyl ethers	-	No	162201-45-8	10 - 15
Glycerin	-	No	56-81-5	1 - 5
Ethanol, 2-amino-, 2-hydroxy-1,2,3-propanetricarboxylate (1:?)	-	No	17863-38-6	1 - 5
Glycine, N,N-bis[2-[bis(carboxymethyl)amino]ethyl]-, sodium salt (1:5)	-	No	140-01-2	0.5 - 1.5

### 4. FIRST AID MEASURES

**First aid measures for different exposure routes****Eye contact**

Rinse with plenty of water. Get medical attention immediately if irritation persists.

**Skin contact**

Rinse with plenty of water. Get medical attention if irritation develops and persists.

**Ingestion**

Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

**Inhalation** Move to fresh air. If symptoms persist, call a physician.

**Most important symptoms/effects, acute and delayed** None under normal use conditions.

**Indication of immediate medical attention and special treatment needed, if necessary**

**Notes to Physician** Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

**Suitable extinguishing media** Dry chemical, CO<sub>2</sub>, alcohol-resistant foam or water spray.

**Unsuitable Extinguishing Media** None.

**Special hazard** None known.

**Special protective equipment for fire-fighters** As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**Specific hazards arising from the chemical** None.

## 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

**Advice for emergency responders** Use personal protective equipment as required.

**Methods and materials for containment and cleaning up**

**Methods for containment** Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.

**Methods for cleaning up** Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

## 7. HANDLING AND STORAGE

**Precautions for safe handling**

**Advice on safe handling** Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible products** None known.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control parameters**

**Exposure Guidelines** .

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
Glycerin	56-81-5		TWA: 15 mg/m <sup>3</sup> mist, total particulate TWA: 5 mg/m <sup>3</sup> mist, respirable fraction (vacated) TWA: 10 mg/m <sup>3</sup> mist, total particulate (vacated) TWA: 5 mg/m <sup>3</sup> mist, respirable fraction	Mexico: TWA 10 mg/m <sup>3</sup>

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Propylene glycol	57-55-6			TWA: 10 mg/m <sup>3</sup> TWA: 50 ppm TWA: 155 mg/m <sup>3</sup>	
Glycerin	56-81-5	TWA: 10 mg/m <sup>3</sup>	TWA: 10 mg/m <sup>3</sup>	TWA: 10 mg/m <sup>3</sup>	TWA: 10 mg/m <sup>3</sup> TWA: 3 mg/m <sup>3</sup>

No relevant exposure guidelines for other ingredients

### Exposure controls

#### Engineering Measures

##### **Distribution, Workplace and Household Settings:**

Ensure adequate ventilation

##### **Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

### Personal Protective Equipment

#### Eye Protection

##### **Distribution, Workplace and Household Settings:**

No special protective equipment required

##### **Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**

Use appropriate eye protection

#### Hand Protection

##### **Distribution, Workplace and Household Settings:**

For sensitive skin or prolonged use, wear gloves

##### **Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**

Protective gloves

#### Skin and Body Protection

##### **Distribution, Workplace and Household Settings:**

No special protective equipment required

##### **Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**

Wear suitable protective clothing

#### Respiratory Protection

##### **Distribution, Workplace and Household Settings:**

No special protective equipment required

##### **Product Manufacturing Plant (needed at Product-Producing Plant ONLY):**

In case of insufficient ventilation wear suitable respiratory equipment

## 9. PHYSICAL AND CHEMICAL PROPERTIES

**Physical State @20°C**

liquid

**Appearance**

Liquid that varies in color

**Odor**

Scented

**Odor threshold**

No information available

<u>Property</u>	<u>Values</u>	<u>Note</u>
pH value	6.8 - 7.4	
Melting/freezing point	No information available	
Boiling point/boiling range	No information available	
Flash point	> 93.3 °C / > 200 °F	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	1.07	
Water solubility	100%	
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity of Product	4500 - 7500 cps	
VOC Content (%)	Products comply with US state and federal regulations for VOC content in consumer products.	

## 10. STABILITY AND REACTIVITY

<b>Reactivity</b>	None under normal use conditions.
<b>Stability</b>	Stable under normal conditions.
<b>Hazardous polymerization</b>	Hazardous polymerization does not occur.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Conditions to Avoid</b>	None under normal processing.
<b>Materials to avoid</b>	None in particular.
<b>Hazardous Decomposition Products</b>	None under normal use.

## 11. TOXICOLOGICAL INFORMATION

### Product Information

#### Information on likely routes of exposure

<b>Inhalation</b>	No known effect.
<b>Skin contact</b>	Irritating to skin.
<b>Ingestion</b>	May be harmful if swallowed.
<b>Eye contact</b>	Causes serious eye irritation. Irritating, but will not permanently injure eye tissue.

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

<b>Acute toxicity</b>	May be harmful if swallowed.
<b>Skin corrosion/irritation</b>	Irritating to skin.
<b>Serious eye damage/eye irritation</b>	Causes serious eye irritation.
<b>Skin sensitization</b>	No known effect.
<b>Respiratory sensitization</b>	No known effect.
<b>Germ cell mutagenicity</b>	No known effect.
<b>Neurological Effects</b>	No known effect.
<b>Reproductive toxicity</b>	No known effect.
<b>Developmental toxicity</b>	No known effect.
<b>Teratogenicity</b>	No known effect.
<b>STOT - single exposure</b>	No known effect.

**STOT - repeated exposure** No known effect.  
**Target Organ Effects** No known effect.  
**Aspiration hazard** No known effect.  
**Carcinogenicity** No known effect.

**Component Information**

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Propylene glycol	57-55-6	22000 mg/kg (rat)	2000 mg/kg (rabbit)	> 317.042 mg/L (Guideline not indicated; rabbit; 2 h)
Glycerin	56-81-5	-	-	> 2.75 mg/L (Rat)
Glycine, N,N-bis[2-[bis(carboxymethyl)amino ethyl]-, sodium salt (1:5)	140-01-2	> 5000 mg/kg bw (Read across data (test substance name not indicated); OECD 401; standard acute method; rat)	> 2000 mg/kg bw (OECD 402 and EU Method B.3; standard acute method; rat)	-

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

The product is not expected to be hazardous to the environment.

**Persistence and degradability** No information available.

**Bioaccumulative potential** No information available.

**Mobility** No information available.

**Other adverse effects** No information available.

**13. DISPOSAL CONSIDERATIONS****Waste treatment**

**Waste from Residues / Unused Products** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**California Hazardous Waste Codes (non-household setting)** 331

**14. TRANSPORT INFORMATION**

**DOT** Not regulated

**IMDG** Not regulated

**IATA** Not regulated

**15. REGULATORY INFORMATION****U.S. Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**CERCLA**

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Sodium hydrogensulphite ...%	7631-90-5	5000 lb	-	

**Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)**

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

**Clean Water Act**

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hydrogensulphite ...%	7631-90-5	5000 lb	-	-	X

**California Proposition 65**

This product is not subject to warning labeling under California Proposition 65.

**U.S. State Regulations (RTK)**

Chemical Name	CAS-No	New Jersey
Propylene glycol	57-55-6	X
Glycerin	56-81-5	X

Chemical Name	CAS-No	Massachusetts
Glycerin	56-81-5	X

Chemical Name	CAS-No	Pennsylvania
Propylene glycol	57-55-6	X
Glycerin	56-81-5	X
Sodium hydrogensulphite ...%	7631-90-5	X
9-Octadecenoic acid (9Z)-	112-80-1	X
Dipropylene Glycol	25265-71-8	X

**International Inventories****United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

**Canada**

This product is in compliance with CEPA for import by P&G.

**Legend**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**CEPA** - Canadian Environmental Protection Act

<b>16. OTHER INFORMATION</b>
------------------------------

**Revision Date:** 06-Mar-2015

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**