



Industrial Containers



Steel King

**Strength. Innovation.
Integrity.**

Steel King leads the way in rack technology with innovation and draws on more than 40 years of experience in the materials handling industry.

Our superior product designs give you a rugged, long lasting, truly economical alternative to other materials.



How to design your container

What type of container do you need?

Construction Requirements

- Load information
- Load weight – maximum and average
- The parts or loads you will be storing
- Whether the new units need to interstack with any existing units

Container Size

Overall and usable sizes (in inches) – length x width x height

Container Type

- Round Corner Corrugated
- Heavy-Duty Bulk Storage
- Hold 'N Fold Collapsible
- Stow Gate
- Workingtainer

Select your options



Sides and deck material – wire mesh, corrugated steel, expanded metal or combinations

Optional drop gates – up to all four sides

Optional skid bars

Optional fork stirrups or fork tubes



Select your color



Vista Green



Poppy Orange



Yellow



Precaution Blue



Black*



White*



Castle Gray*



Platinum*



Kelly Green*



Apricot*



Arctic Blue*



Fire Engine Red*



Navy Blue*

**Minimum order size may apply.*



Round Corner Corrugated Steel Containers

Heavy corrugated steel sides and deck make Steel King's round corner corrugated containers a rugged and durable general purpose industrial container. Universal stacking feet provide easy stackability. Looking for low cost bulk industrial storage for parts? Look no further: Round Corner Corrugated Containers are the answer.

- Stackable 4 High while loaded
- 4000# Capacity each
- Universal Stacking Legs made of 1/4" steel



RCCM

48 HOUR » QUICK SHIP

	Weight	Length	Width	Height
RCCM324024VG	205#	33.5"	41.5"	28.5"
RCCM404824VG	258#	41.5"	49.5"	28.5"

Heavy-Duty Bulk Storage Containers

Utilizing super-strong tubular-frame construction, Steel King Heavy-Duty Rigid Containers are made to stand up to rugged everyday use. These containers are custom designed to your requirements and can be made in virtually any size.

- Standard units up to 6,000 lb capacity
- Most stackable up to six high while fully loaded
- Side materials can include flat or corrugated steel, wire mesh, expanded metal or combinations
- Base materials can include flat or corrugated steel, wire mesh, expanded metal or bar grating

Available options include: Drop gates; Skid Bars, Fork Stirrups; Crane eyes/hooks; Roll-over Runners, Casters and Galvanizing



Heavy-Duty Rigid Containers



Workingtainer

Double your space utilization by turning work areas into storage. Now, instead of storing parts in one area and then moving to work stations as you need them, you can store them right where they will be used—with Steel King WorkingTainers. Simply open the container door to the working tray position and you have easy access to parts.

- Ergonomic design improves productivity and reduces repetitive-stress injuries
- Wide, adjustable side door opens to tray position – eliminating the need to reach over the top for materials
- Rugged 4,000 lb. capacity standard – larger capacities available
- Stackable up to six high while fully loaded
- Tubular construction – for increased rigidity and durability



Workingtainer



48 HOUR » QUICK SHIP

	Weight	Length	Width	Height
HDWT3036VG	159#	30"	36"	30.5"
HDWT3240VG	182#	32"	40"	30.5"
HDWT3644VG	203#	36"	44"	30.5"
HDWT4048VG	224#	40"	48"	30.5"

Stow Gate

The Stow Gate Container is a customizable, multi-use container. Making this product unique is the fact that both ends are half drop gates or full drop ends. Once folded, the ends slide out of the way under the deck, allowing for fork truck access from every side.

Because the container can be reconfigured, it can provide a variety of uses at an individual station. This makes it ideal for assembly, work-in-progress and dispensing. The ability to utilize this container for inter-plant shipping is an added benefit.



Stow Gate



Valued for its versatility, the Stow Gate container adapts easily to multiple configurations.



Hold 'n Fold Containers

Save valuable floor space. With Steel King's® patented Hold 'n Fold design you can store or stage ready for use on your production floor, three containers in the same space as one rigid container. Simply lift sides into position (they automatically lock in place) and it's ready to fill. Use Hold 'n Fold for intra-plant shipments and save shipping costs returning empty containers. Hold 'n Fold self-locks when folded, eliminating the need for banding.

- Collapsible – generates a 3:1 space savings
- Rugged 4,000 lb. capacity standard – larger capacities available
- Patented mechanism – only Hold 'n Fold operates this easily
- Tubular construction – increases rigidity and durability
- Stackable – up to six high, even when loaded to full capacity
- Optional drop gates simplify positioning for loading and unloading



Hold 'n Fold



	Weight	Length	Width	Height
HF4WM454842VG	325#	45"	48"	42"
HF4CM454842VG	436#	45"	48"	42"

Options and Accessories

In addition to custom design, the following are standard options and accessories available:

Half Drop Gate

- 1 long side
- 2 long sides
- 1 short side
- 2 short sides
- All 4 sides

Fork Stirrups

- All 4 sides
- 2 long sides
- 2 short sides

Floor Runners

- All 4 sides
- 2 long sides
- 2 short sides

Caster Plates & Casters

- Crane Eyes
- Crane Lifting Lugs
- Drains / Valves
- Fork Pockets
- Roll-Over Runners
- Universal Stacking Legs

Why Choose Steel King?

Industry Leadership – With our state-of-the-art facilities and active participation in the associations that develop the national specifications for quality and safety, we lead the way with our uncompromising dedication to engineering and manufacturing excellence.

Expertise and Versatility – Our in-house engineering and drafting staff has decades of experience designing thousands of rack systems, which means we can custom engineer a solution for any storage challenge and ensure efficient space utilization.

Quality and Safety – Steel King is committed to providing customers with the highest quality and safest products possible. Our structural engineers design our products to strictly conform to industry design codes to ensure product and worker safety. Steel King facilities and processes are tested and fabricator licenses are approved for the City of Los Angeles and the City of Phoenix.

Durability – Made with the highest quality materials available, Steel King products are built to last. We design them to better resist the daily rigors of your environment, which means they last longer, require less maintenance and provide greater safety.

Single Source Responsibility – Our wide breadth of product offerings allows us single-source responsibility that ensures both cost and quality control.

Welder Certification – Our welders are trained and qualified to American Welding Society (AWS) D1.1 and D1.3 standards. We also have an in-house Certified Welding Inspector (CWI).

We are a “one-stop shop” for all your storage needs.



Dynamic Storage



Pallet Rack



Rack Storage Systems

Steel King has been delivering customized storage solutions

since 1970,

designing and manufacturing pallet racking systems and related material handling products that improve operational efficiency in manufacturing, warehousing and distribution facilities.

When it comes to offering the highest quality, safest and most diverse product offerings,

Steel King is built to deliver.



STEEL KING™

BUILT TO DELIVER

2700 Chamber Street, Stevens Point, WI 54481 | 715-341-3120 | 800-826-0203 | www.steelking.com

PLANT LOCATIONS

2700 Chamber Street, Stevens Point, WI 54481

325 East Beckert Road, New London, WI 54961

30 Industrial Boulevard SE, Rome, GA 30161