



DEEP FREEZE IS NORTH SLOPE CHILLERS' MOST ROBUST CHILLER

HOW LOW CAN YOU GO?

Bring on Deep Freeze for ultimate industrial cooling. Intended to provide supreme industrial chilling, Deep Freeze shares many of the same hefty qualities of Freeze, along with the capacity to cool from -112°F to 300°F (depending on model) and fully insulated internal parts to ensure no internal temperature loss. Keep your critical materials and equipment cool even in hot conditions.



Shortest Industry Lead Times
Made in the USA
Award-Winning Manufacturer



World-Class Custom
Engineering Team
UL Safety Listed
Smart Chiller™
capabilities available



Ideal process cooling solution
for Biotech, Dairy, Chemicals,
Cannabis, Oil Extraction, EDM,
Fermentation, Hydroponics,
Lasers, Printing, Welding, Food,
and Plastics



ENVIRONMENTALLY
ACCEPTABLE r404a
REFRIGERANT

POWDER-COATED
STEEL CABINET

BRAZED PLATE
HEAT EXCHANGER



CORROSION RESISTANT,
THERMALLY INSULATED
RESERVOIR

MOUNTED ON FOUR CASTERS
FOR EASY MOBILITY



DEEP FREEZE

www.globalindustrial.com | 1.888.978.7759

Model Number	Fluid Temp Range (F)	Ambient Temp Range	Refrigerant	Inlet/Outlet	Pump			Reservoir Capacity	Cooling Capacity (BTU/hr)	Dimensions	Max Amps (FLA)	Recommended Breaker/Service (MCA)	Available Voltages
NSC0500-LT	10°F - 45°F	40°F - 100°F	R404a	1/2" NPT	Continuous Duty, non-ferrous	1/3 HP Fixed Displacement Pump	4 GPM Fixed 50 PSI Max	4 Gallon Poly Tank	10°F - 2,500 BTU/hr 45°F - 5,070 BTU/hr	28.25"L x 22.5"W x 32.5"H	16.6 Amps	20 Amp	120/1/60 (std)
NSC1000-LT	10°F - 45°F	40°F - 100°F	R404a	1/2" NPT	Continuous Duty, non-ferrous	1/3 HP Fixed Displacement Pump	4 GPM Fixed 50 PSI Max	15 Gallon Poly Tank	10°F - 5,900 BTU/hr 45°F - 11,900 BTU/hr	34½"L x 28¾"W x 39"H	16.3 Amps (std) 14 Amps 6 Amps	20 Amp (std) 20 Amp 15 Amp	208-240/1/60 (std) 208-240/3/60 480/3/60
NSC2000-LT	10°F - 45°F	40°F - 100°F	R404a	3/4" NPT	Continuous Duty, Stainless Steel	3/4 HP Centrifugal Pump	15 GPM @ 28 PSI 25 GPM @ 23 PSI 35 GPM @ 16 PSI 45 GPM Max	15 Gallon Poly Tank	10°F - 13,800 BTU/hr 45°F - 27,200 BTU/hr	34¾"L x 43¾"W x 40"H	30.9 Amps (std) 20.1 Amps 9.2 Amps	40 Amp (std) 25 Amp 15 Amp	208-240/1/60 (std) 208-240/3/60 480/3/60
NSC5000-LT	10°F - 45°F	40°F - 90°F	R404a	1-1/4" NPT	Continuous Duty, Stainless Steel	1-1/2 HP Centrifugal Pump	15 GPM @ 39 PSI 30 GPM @ 35 PSI 45 GPM @ 28 PSI 60 GPM Max	50 Gallon Poly Tank	0°F - 19,200 BTU/hr 45°F - 44,900 BTU/hr	34"L x 65"W x 62"H	29.3 Amps 13.6 Amps (std)	35 Amp 20 Amp (std)	208-240/3/60 480/3/60 (std)
NSC5000E-LT	10°F - 45°F	0°F - 90°F	R404a	1-1/4" NPT	Continuous Duty, Stainless Steel	1-1/2 HP Centrifugal Pump	15 GPM @ 39 PSI 30 GPM @ 35 PSI 45 GPM @ 28 PSI 60 GPM Max	50 Gallon Poly Tank	0°F - 19,200 BTU/hr 45°F - 44,900 BTU/hr	34"L x 65"W x 62"H	29.3 Amps 13.6 Amps (std)	35 Amp 20 Amp (std)	208-240/3/60 480/3/60 (std)
NSC10000-LT	10°F - 45°F	40°F - 90°F	R404a	1-1/4" NPT	Continuous Duty, Stainless Steel	2 HP Centrifugal Pump	15 GPM @ 54 PSI 30 GPM @ 48 PSI 45 GPM @ 40 PSI 65 GPM Max	50 Gallon Poly Tank	15°F - 53,000 BTU/hr 45°F - 90,000 BTU/hr	34"L x 65"W x 62"H	26.6 Amps (std)	35 Amp (std)	480/3/60 (std)
NSC10000E-LT	10°F - 45°F	0°F - 90°F	R404a	1-1/4" NPT	Continuous Duty, Stainless Steel	2 HP Centrifugal Pump	15 GPM @ 54 PSI 30 GPM @ 48 PSI 45 GPM @ 40 PSI 65 GPM Max	50 Gallon Poly Tank	15°F - 53,000 BTU/hr 45°F - 90,000 BTU/hr	34"L x 65"W x 62"H	26.6 Amps (std)	35 Amp (std)	480/3/60 (std)
Model Number	Fluid Temp Range (F)	Refrigerant	Condenser	Inlet/Outlet	Pump			Reservoir Capacity	Cooling Capacity (BTU/hr)	Dimensions	Max Amps (FLA)	Recommended Breaker/Service (MCA)	Available Voltages
NSC0500-ULT	-112°F to +70°F -80°C to +21°C	R404a/ R508b	Air-cooled	1/2" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	4 GPM Fixed	5 Gallon Stainless Steel	-40°C (-40°F) - 1,700 Watts (5,800 BTU/hr) -80°C (-112°F) - 600 Watts (2,000 BTU/hr)	28.25"L x 22.5"W x 32.5"H	16 Amps	20 Amp	208-240/3/60 (std)
NSC01000-ULT	-112°F to +70°F -80°C to +21°C	R404a/ R508b	Air-cooled	3/4" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	4 GPM Fixed	10 Gallon Stainless Steel	-40°C (-40°F) - 3,700 Watts (12,000 BTU/hr) -80°C (-112°F) - 1,750 Watts (4,600 BTU/hr)	34½"L x 28¾"W x 39"H	25 Amps (std)	30 Amp (std)	208-240/3/60 (std)
NSC2000-ULT	-112°F to +70°F -80°C to +21°C	R404a/ R508b	Air-cooled	3/4" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	8 GPM Fixed	20 Gallon Stainless Steel	-40°C (-40°F) - 7,000 Watts (24,000 BTU/hr) -80°C (-112°F) - 3,000 Watts (10,200 BTU/hr)	34¾"L x 43¾"W x 40"H	20 Amps (std)	30 Amp (std)	480/3/60 (std)
NSC0500-ULT	-112°F to +300°F -80°C to +150°C	R404a/ R508b	Air-cooled	1/2" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	4 GPM Fixed	5 Gallon Stainless Steel	-40°C (-40°F) - 1,700 Watts (5,800 BTU/hr) -80°C (-112°F) - 600 Watts (2,000 BTU/hr)	28.25"L x 22.5"W x 32.5"H	16 Amps	20 Amp	208-240/3/60 (std)
NSC01000-ULT	-112°F to +300°F -80°C to +150°C	R404a/ R508b	Air-cooled	3/4" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	4 GPM Fixed	10 Gallon Stainless Steel	-40°C (-40°F) - 3,700 Watts (12,000 BTU/hr) -80°C (-112°F) - 1,750 Watts (4,600 BTU/hr)	34½"L x 28¾"W x 39"H	25 Amps (std)	30 Amp (std)	208-240/3/60 (std)
NSC2000-ULT	-112°F to +300°F -80°C to +150°C	R404a/ R508b	Air-cooled	3/4" NPT	Continuous Duty, Stainless Steel	Fixed Displacement	8 GPM Fixed	20 Gallon Stainless Steel	-40°C (-40°F) - 7,000 Watts (24,000 BTU/hr) -80°C (-112°F) - 3,000 Watts (10,200 BTU/hr)	34¾"L x 43¾"W x 40"H	20 Amps (std)	30 Amp (std)	480/3/60 (std)

DEEP FREEZE INDOOR & OUTDOOR INDUSTRIAL CHILLERS

ULTRA-LOW TEMP

ULTRA-LOW TEMP PROCESS