MAINTAIN OPTIMAL TEMPERATURES IN HAZARDOUS LOCATIONS



HAZARDOUS LOCATIONS

Have peace of mind with CID2 certified products

FULL-COVERAGE

Provide an insulated, full-wrap design

SAFE

Deliver safe, distributed heat to temperature sensitive materials

PROTECT

Preserve expensive materials without overheating or burning

NO MORE WASTE

Prevent product waste by safely maintaining consistent temperatures

VISCOSITY

Improve viscosity and flow with easy-toapply controlled heat



CONTROL CRITICAL TEMPERATURES IN HAZARDOUS LOCATIONS

HAZLOC HEATERS: Quickly heat materials to a preset state 80° F (± 20° F) / 27° C (± 7° C)*

ACCESSORY PRODUCTS: Improve thermal insulation with available top and bottom pieces

STANDARD SIZES: Available for 55 gallon drums and 275 & 330 gallon totes**

*Product Temperatures may vary depending on boundary conditions
**Hazardous area products include 33-foot cord (plug not included)

HAZARDOUS LOCATION HEATERS

Electrical equipment can cause explosions when used in areas with explosive substances. To prevent this, Powerblanket has developed the most advanced hazardous area heating systems on the market, complete with special wiring and safety equipment to ensure the highest standards of safety. Powerblanket hazardous locations blankets have been thoroughly tested and certified to the most stringent safety standards. Now you can rest easy as Powerblanket solves your heating problems with complete safety.

Product Category	Model #	Temperature Control	Approximate Product Temp*	Container Volume	Container Dimensions	AC Voltage	Nominal Power	Nominal Amperage	Approximate Weight/ Mass
HAZARDOUS AREA HEATERS	BH55-C1D2T4- 100F	Internal Preset	80° F (± 10° F) / 27° C (± 3° C)	55 Gal / 208 L	23.3"D x 34.9"H/ 59 cm D x 89 cm H	120V	800	6.67	11 lbs / 5 kg
	TH275-CID2- 122F	Internal Preset	90° F (+- 10° F) / 32° C (+- 3° C)	275 Gallon / 1000 L	48″L x 40″W x 46″H	120V	1440	12	100 lbs / 45 kg
	TH330-CID2- 122F	Internal Preset	90° F (+- 10° F) / 32° C (+- 3° C)	330 Gallon / 1250 L	48″L x 40″W x 53″H	120V	1440	12	105 lbs / 48 kg
	*Cord length is 33 ft w/ no plug								

POWERBLANKET CID2 DRUMS & TOTES





MIKE ROBERTS, MANAGER HOWARD MARTEN FLUID TECHNOLOGIES

Powerblanket drum and bucket heaters are a drastic improvement over the original band heaters we used to offer. With Powerblanket products we no longer have to worry about overheating or unpredictable thermostats. The Powerblanket Technology provides uniform heat throughout the entire barrel of product which is paramount to what we do. Powerblanket products are very durable, look great, and are the only heaters we will offer our customers.



ERIC, A COLORADO ENERGY COMPANY

Powerblanket, your tote heater blankets have been wonderful to work with and have kept our totes warm and protected from the harsh conditions here in the cold Rocky Mountains. We have love these blankets because they are extremely easy to install and the controller is very convenient. The blankets do not flake, tear, or rip in any way, and we appreciate the weather resistance. Thank you for assisting us with our heating frustrations and protecting our materials. You have helped to keep our company running efficiently and retaining profit. We love your tote heaters and would recommend them to anyone.



