



fitted with

3 x 3.5W LED modules, 5000K, 1500 lumens

work equipment

LED convertor

connected load
power consumption
system of protection
class of protection
technology
usage
luminaire head
lamp cover
tubular sections
balance of articulation
joints weight (net)
mains lead

120V 50/60 Hz
approx. 13.2 W
IP 20
I
multi-stage switchable
switch
plastic, light grey
screen, milky
steel tube, painted, light grey
spring
approx. 4.7 kg (10.4 lbs)
approx. 3.3 m (11 ft), plug in transformer

fastening

table clamp (included)

lens; dimensions
lens; diopters
add-on lens;
special features

162 x 105 (6.38" x 4.13")
3
4 or 4+12 diopters (optional add on) light
output controlled with 2-way-switch



NEMA 1-15P

illuminance

Comment: d=15cm

Em: 4252 lx
Emax: 6096 lx
Emin: 1967 lx

