SAFETY DATA SHEET

Issue Date 18-Jan-2023 **Revision Date** 18-Jan-2023 **Version** 2

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier
Product Name Clinging Bowl Cleaner

Other means of identification
Product Code 640409
Synonyms None

Details of the supplier of the safety data sheet
Company Name Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(888) 978-7759

Emergency telephone number Chemtrec 1-800-424-9300
Emergency Telephone

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status
This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Category 5
Acute toxicity - Inhalation (Gases)	Category 4
Skin corrosion/irritation	Category 1 Sub-category A
Serious eye damage/eye irritation	Category 1

Label elements

Emergency Overview

Danger

Hazard statements
May be harmful if swallowed
Harmful if inhaled
Causes severe skin burns and eye damage



Appearance Clear Blue **Physical state** Liquid **Odor** Mint

Precautionary Statements - Prevention
Use only in a well-ventilated area
Do not breathe dust/fume/gas/mist/vapors/spray
Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response
Specific Treatment (See Section 4 on the SDS)
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
Immediately call a POISON CENTER or doctor/physician
IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
Wash contaminated clothing before reuse
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Call a POISON CENTER or doctor/physician if you feel unwell
Immediately call a POISON CENTER or doctor/physician
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting
Drink plenty of water
Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Storage
Store locked up

Precautionary Statements - Disposal
Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)
Other Information

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Hydrochloric Acid	7647-01-0	5-10	*
Nonylphenol Polyethylene Glycol Ether	127087-87-0	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

General advice Immediate medical attention is required.

Skin Contact Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. For minor skin contact, avoid spreading material on unaffected skin. For severe burns, immediate medical attention is required.

Eye contact Do not rub affected area. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Keep eye wide open while rinsing.

Inhalation Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Call a physician or poison control center immediately.

Ingestion Rinse mouth. Drink plenty of water. Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Call a physician or poison control center immediately.

Self-protection of the first aider Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical
The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating and toxic gases and vapors. In the event of fire and/or explosion do not breathe fumes.

Explosion data
Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with skin, eyes or clothing. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Dam up. Dike far ahead of liquid spill for later disposal. Prevent product from entering drains. Soak up with inert absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment. Use only with adequate ventilation and in closed systems.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep out of the reach of children. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers.

Incompatible materials Strong bases. Ammonia. Chlorinated compounds. Contact with metals may evolve flammable hydrogen gas. Metals. Incompatible with strong acids and bases. Incompatible with oxidizing agents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines .

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Hydrochloric Acid 7647-01-0	Ceiling: 2 ppm	(vacated) Ceiling: 5 ppm (vacated) Ceiling: 7 mg/m³ Ceiling: 5 ppm Ceiling: 7 mg/m³	IDLH: 50 ppm Ceiling: 5 ppm Ceiling: 7 mg/m³
2-(2-methoxypropoxy)propano 34590-94-8	TWA: 50 ppm	TWA: 100 ppm TWA: 600 mg/m³ (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m³ (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m³ (vacated) S* S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m³ STEL: 150 ppm STEL: 900 mg/m³
Propargyl Alcohol 107-19-7	TWA: 1 ppm S*	(vacated) TWA: 1 ppm (vacated) TWA: 2 mg/m³ (vacated) S*	TWA: 1 ppm TWA: 2 mg/m³

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Tight sealing safety goggles. Wear a face shield if splashing hazard exists.

Skin and body protection Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Keep away from food, drink and animal feeding stuffs. When using do not eat, drink or smoke. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Avoid contact with skin, eyes or clothing. Take off all contaminated clothing and wash it before reuse. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear Blue
Color Blue
Odor Mint

Odor threshold No Information available

Property	Values	Remarks • Method
pH	<1	
Specific Gravity	1.05	
Viscosity	300 - 400 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	210 °F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.75
VOC Content (%)	1.5

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Conditions to avoid
Exposure to air or moisture over prolonged periods.

Incompatible materials
Strong bases. Ammonia. Chlorinated compounds. Contact with metals may evolve flammable hydrogen gas. Metals. Incompatible with strong acids and bases. Incompatible with oxidizing agents.

Hazardous Decomposition Products
Thermal decomposition can lead to release of irritating and toxic gases and vapors.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information The primary effects and toxicity of this material are due to it corrosive nature.

Inhalation Harmful if inhaled. Breathing of vapor can cause respiratory irritation and inflammation. Breathing of mist or liquid can cause burns to the respiratory tract.

Eye contact Avoid contact with eyes. Corrosive to the eyes and may cause severe damage including blindness.

Skin Contact Avoid contact with skin. Corrosive. Contact with skin may cause severe irritation and burns.

Ingestion May be harmful if swallowed. Ingestion causes acute irritation and burns to the mucous

membranes of the mouth, trachea, esophagus and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrochloric Acid 7647-01-0	= 700 mg/kg (Rat)	> 5010 mg/kg (Rabbit)	= 1.68 mg/L (Rat) 1 h
Nonylphenol Polyethylene Glycol Ether 127087-87-0	= 1310 mg/kg (Rat) = 2590 mg/kg (Rat)	= 2 mL/kg (Rabbit) = 1780 µL/kg (Rabbit)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Corrosivity Causes burns. Extremely corrosive and destructive to tissue. Risk of serious damage to eyes.

Sensitization No Information available.

Germ cell mutagenicity No Information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Hydrochloric Acid 7647-01-0	-	Group 3	-	X

IARC (International Agency for Research on Cancer)
Group 3 -Not classifiable as a human carcinogen
OSHA (Occupational Safety and Health Administration of the US Department of Labor)
X - Present

Reproductive toxicity No Information available.

STOT - single exposure No Information available.

STOT - repeated exposure No Information available.

Chronic toxicity Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Avoid repeated exposure. Possible risk of irreversible effects.

Target organ effects Central nervous system, EYES, Respiratory system, Skin.

Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 2,554.60

ATEmix (dermal) 37,260.80

ATEmix (inhalation-gas) 6,166.4171

ATEmix (inhalation-dust/mist) 5.484

12. ECOLOGICAL INFORMATION

Ecotoxicity

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Hydrochloric Acid 7647-01-0	-	282:96 h Gambusia affinis mg/L	-
2-(2-methoxypropoxy)propano 34590-94-8	-	10000: 96 h Pimephales promelas mg/L LC50 static	1919: 48 h Daphnia magna mg/L LC50
Propargyl Alcohol 107-19-7	-	1.49 - 1.56: 96 h Pimephales promelas mg/L LC50 flow-through	-

Persistence and degradability
No Information available.

Bioaccumulation
Bioaccumulative potential.

Chemical Name	Partition coefficient
Nonylphenol Polyethylene Glycol Ether 127087-87-0	5.669 3.7

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

Chemical Name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Propargyl Alcohol 107-19-7	P102	-	-	-

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

UN/ID No.	UN1760
Proper shipping name	Corrosive liquids, n.o.s.
Hazard Class	8
Packing Group	II
Special Provisions	B2, IB2, T11,TP2, TP27
Description	UN1760, Corrosive liquids, n.o.s. (contains Hydrochloric Acid), 8, II
Emergency Response Guide Number	154

TDG

UN/ID No.	UN1760
Proper shipping name	Corrosive liquids, n.o.s.
Hazard Class	8
Packing Group	II
Description	UN1760, Corrosive liquids, n.o.s. (Contains Hydrochloric Acid), 8, II

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
Hydrochloric Acid - 7647-01-0	1.0

2-(2-methoxypropoxy)propano - 34590-94-8	1.0
Nonylphenol Polyethylene Glycol Ether - 127087-87-0	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Hydrochloric Acid 7647-01-0	5000 lb	-	-	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Hydrochloric Acid 7647-01-0	5000 lb	5000 lb	RQ 5000 lb final RQ RQ 2270 kg final RQ

US State Regulations

California Proposition 65

WARNING: This product can expose you to chemicals including Methanol. which is known to the state of California to cause birth defects or other reproductive harm. For More Information go to www.P65Warnings.ca.gov.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Hydrochloric Acid 7647-01-0	X	X	X
2-(2-methoxypropoxy)propano 34590-94-8	X	X	X
Propargyl Alcohol 107-19-7	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	**Health hazards** 3	**Flammability** 0	**Instability** 0	**Physical and Chemical Properties** -
HMIS	**Health hazards** 3	**Flammability** 0	**Physical hazards** 0	**Personal protection** C

Issue Date 18-Jan-2023
Revision Date 18-Jan-2023
Revision Note
No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet