Magni ier luminaire SNLQ 54/2 113460006



fitted with

work equipment

connected load power consumption system of protection class of protection technology usage luminaire head lamp cover tubular sections balance of articulation joints weight (net) mains lead fastening lens; dimensions lens; diopters add-on lens; special features

Waldmann W

ENGINEER OF LIGHT.

3 x 3.5W LED modules, 5000K, 1500 lumens

LED convertor

120V 50/60 Hz approx. 12 W IP 20 L multi-stage switchable switch plastic, light grey screen, milky steel tube, painted, light grey spring approx. 4.7 kg (10.4 lbs) approx. 3 m (9.84 ft) table clamp (included) 162 x 105 (6.38" x 4.13") 3 4 or 4+12 diopters (optional add on) light output controlled with 2-way-switch



nema 5-15p

illuminance 550 Comment: d=15cm 4252 lx Em: Emax: Emin: 6096 lx 1967 lx 30 cm 3000 3500 7000 25 4000 6000 4500 E[lx] 5000 5000 20 5500-4000 ²298x194x64 6000 15 3000 2000 20 25²⁰⁰ 15 10 1000 5 10 15 20 0 5 10 E[Ix] 아남 25 'n 0 5 10 15 20 25 30 cm 30 cm

Errors and technical changes excepted. Images can vary from original.