

243227 Top Mount Freezer

Nexel® Refrigerator/Freezer 10 cu.ft. BLACK

- KEY BENEFITS**
- DOE Listed
 - Electronic Temperature Control LED interior Light
 - Versatile Door Storage
 - Frost Free
 - Fresh Food Compartment
 - 2 Full Glass Shelves
 - 1 Width Crisper Drawers
 - Top Mount Freezer Compartment
 - 1 Full Glass Shelves



Weights & Dimensions

Width	23.58"	Height	59.72"
Depth	25.71"	Weight	114.9 lbs

Product Details

Body Color Family	Black	Reversible Door	Yes
Light	Yes	Number of Level Legs	4
Door Swing	Reversible	Brand	Nexel
Adjustable Shelf	No	Type	Top Mount
Number of Full Door Shelves	6	Shelf Type	Adjustable Glass
Defrost Type	Automatic	Energy Usage	DOE
Number of Shelves	5	Handle Type	Recessed Door Pull
Material	Stainless Steel	Capacity	280L, 10 ft ³
Door Color Family	Black	Voltage	120V 60Hz
Number of Crispers	1	Thermostat Type	Electronic
Crisper Drawer Material	GPPS	Refrigerant Type	R600A
Manufacturers Part Number	BCD-280		

Warranty

Warranty	1 yr	Certifications	CUL
----------	------	----------------	-----

Compliance & Certifications

For more information, visit globalindustrial.com or call 1-800-645-1232.