

SAFETY DATA SHEET (SDS)

		5711 21	I DATE D	HEET (SDS)	
Section 1. Identification					
Product identifie	LORIS 0.	13% BZK W	IPE		
Other means of		of product 12			
Recommended u	ise and restrictions on use			99 % of water)	
Initial supplier i	dentifier			c., 2323 Halpern, St-Laurent (Montre	eal) Québec, Canada H4S 1S3
		Telephone	e: 514-331-40	534	
Emergency telep	ohone number/restriction on use	Canada –	CANUTEC 2	24 hour number 613-996-6666	
		Section 2	. Hazard id	lentification	
Classification of	hazardous product (name of the o	category or	subcategory	of the hazard class)	
Not regulated	<u> </u>			·	
Information eler	nents (symbols, signal words, haza	ard stateme	nts and prec	autionary statements of the catego	ry/subcategory)
None mandatory				-	
Other hazards k	nown None				
	Section 7	3. Compos	ition/infori	nation on ingredients	
Chemical name	(common name/synonyms)	•		CAS number or other	Concentration (%)*
	enzyl ammonium chloride (C12-18)			68391-01-5	< 1.0 %
			ad of the actua	concentration(s) considered trade secret	(s).
		Section	4. First-aid	l measures	
Inhalation	None in normal conditions of use.				
Ingestion	IF SWALLOWED: Immediately	call a doctor	r. DO NOT I	NDUCE VOMITING. NEVER give	anything by mouth if victim is
J	rapidly losing consciousness, or	is unconscio	ous or convu	lsing. Rinse mouth thoroughly with	water. Have victim drink two
	glasses of water. If vomiting occur	rs naturally,	have victim	lean forward to reduce risk of aspirat	ion.
Skin contact	None in normal conditions of use.				
Eye contact	IF IN EYES: Rinse eyes with water	er (5-10 min	utes).		
Most important	Most important symptoms and effects (acute or delayed) None				
Indication of im	mediate medical attention/special	treatment	In all cases	, call a doctor. Do not forget this doc	ument.
		Section 5.	Fire-fighti	ng measures	
Specific hazards	of the hazardous product (hazard	lous combu	stion produc	ets)	
Carbon oxides an	nd other irritant/toxic gases and fume	es.			
Suitable and uns	suitable extinguishing media				
		agent and ap	ppropriate fo	am to extinguish surrounding produc	ts.
Special protective	Special protective equipment and precautions for fire-fighters				
During a fire, irri	During a fire, irritating/toxic smoke and fumes may be generated. Do not enter fire area without proper protection. Firefighters should wear proper				
protective equipment and self-contained breathing apparatus with full face piece. Shield personnel to protect from venting, rupturing or bursting cans.					
Move containers from fire area if it can be done without risk. Water spray may be useful in cooling equipment and cans exposed to heat and flame.					
Section 6. Accidental release measures					
	tions, protective equipment and en				
			an-up is con	ducted by trained personnel only. A	ll persons dealing with clean-up
should wear the appropriate protective equipment (See Section 8).					
Methods and materials for containment and cleaning up					
Ventilate area of release. Stop the leak if it can be done safely. Contain and absorb any spilled liquid concentrate with inert absorbent material, then					
place material into a container for later disposal (See Section 13). Contaminated absorbent material may pose the same hazards as the spilled product.					
Notify the appropriate authorities as required.					
Section 7. Handling and storage					
Precautions for safe handling					
For external use only. Use according to package label instructions. Discard after single use (see Section 13). Avoid contact with eyes. Use good					
industrial hygiene	industrial hygiene practices in handling this material. When using do not eat or drink. Refer also to Section 8.				
Conditions for safe storage, including any incompatibilities					
Keen out of reach of children. Store away from incompatible materials (see Section 10)					

Keep out of reach of children. Store away from incompatible materials (see Section 10).

Section 8. Exposure controls/Personal protection

Control parameters (biological limit values or exposure limit values and source of those values)

Exposure limits: None

Appropriate engineering controls

General ventilation normally adequate.

Individual protection measures/personal protective equipment

None required



Section 9. Physical and chemical properties					
Appearance, physical state/colour	Clear liquid	Vapour pressure	Not available		
Odour	Characteristic	Vapour density	Heavier than air		
Odour threshold	Not available	Relative density	1.0		
pH	Not available	Solubility	Soluble		
Melting/freezing point	Not available	Partition coefficient - n-octanol/water	Not available		
Initial boiling point/range	Not available	Auto-ignition temperature	Not available		
Flash point	Not available	Decomposition temperature	Not available		
Evaporation rate	Not available	Viscosity	Not available		
Flammability (solids and gases)	Not available	VOC	Not available		
Upper and lower flammability/explosive limits	Not available	Other	None known		
One than tower manufacture with the state of					

Section 10. Stability and reactivity

Reactivity

Does not react under the recommended storage and handling conditions prescribed.

Chemical stability

Stable under the recommended storage and handling conditions prescribed.

Possibility of hazardous reactions

None

Conditions to avoid (static discharge, shock or vibration)

None

Incompatible materials

Oxidizing materials; etc.

Hazardous decomposition products

None known

Section 11. Toxicological information

Information on the likely routes of exposure (inhalation, ingestion, skin and eye contact)

Causes very mild eye irritation.

Symptoms related to the physical, chemical and toxicological characteristics

None

Delayed and immediate effects (chronic effects from short-term and long-term exposure)

Skin Sensitization – No data available; Respiratory Sensitization – No data available; Germ Cell Mutagenicity – No data available; Carcinogenicity – No ingredient listed by IARC, ACGIH, NTP or OSHA Reproductive Toxicity – No data available; Specific Target Organ Toxicity — Single Exposure – No data available; Specific Target Organ Toxicity — Repeated Exposure – No data available; Aspiration Hazard – No data available; Health Hazards Not Otherwise Classified – No data available.

Numerical measures of toxicity (ATE; LD₅₀ & LC₅₀)

No data available

ATE not available in this document.

Section 12. Ecological information				
Ecotoxicity (aquatic and terrestrial information)	No data available for this product.			
Persistence and degradability	No data available			
Bioaccumulative potential	No data available			
Mobility in soil	No data available			
Other adverse effects	No data available			
Section 13 Disposed considerations				

Section 13. Disposal considerations

Information on safe handling for disposal/methods of disposal/contaminated packaging

Dispose of contents/container into safe container in accordance with local, regional or national regulations.

Section 14. Transport information

UN number; Proper shipping name; Class(es); Packing group (PG) of the TDG Regulations

Not regulated

 $\label{eq:class} \textbf{UN number; Proper shipping name; Class(es); Packing group (PG) of the IMDG (maritime)}$

Not regulated

UN number; Proper shipping name; Class(es); Packing group (PG) of the IATA (air)

Not regulated

Special precautions (transport/conveyance)	None
Environmental hazards (IMDG or other)	None
Bulk transport (usually more than 450 L in capacity)	Possible



Section 15. Regulatory information				
Safety/health Canadian regulations specifics		Refer to Section 2 for the appropriate classification. This product has been		
		classified in accordance with the hazard criteria of the Hazardous Products		
		Regulations (HPR).		
Environmental Canadian regulations specifics		Refer to Section 3 for ingredient(s) of the DSL		
Safety/health/environmental outside regulations specifics		None		
Section 16. Other information				
Date of the latest revision of the safety data sheet		August 22, 2018 version 4		
Corrections	Section 1; 3; 4; 7; 8; 11; 12;			
References	Safety Data Sheets from manufacturer/supplier & from Canadian Centre for Occupational Health and Safety, CCOHS.			
Abbreviations				
ACGIH	American Conference of Governmental Indu	ıstrial Hygienists		
ATE	Acute toxicity estimate			
CAS	Chemical Abstract Service			
DSL	Domestic Substance List			
IARC	International Agency for Research on Cancer			
IATA	International Air Transport Association			
IMDG	International Maritime Dangerous Goods Code			
LC		Lethal concentration		
LD	Lethal Dosage			
NIOSH	National Institute for Occupational Safety and Health			
NTP	National Toxicology Program (U.S.A.)			
OSHA	Occupational Safety and Health Administrat	ion (U.S.A.)		
PEL	Permissible Exposure Limit			
STEL	Short-term Exposure Limit			
TDG	Transport of dangerous goods in Canada			
TLV	Threshold Limit Value			
TSCA	Toxic Substances Control Act			
TWA	Time Weighted Average			
WHMIS	Workplace Hazardous Materials Information System			
To the best of our knowledge, the information contained berein is accurate. However, neither the above named supplier nor any of its subsidiaries.				

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.