

8'-12'

# When You Need Unprecedented Clean ... and Odor Control...



True HEPA® Filtration captures 99.97%  
of particles as small as 0.3 microns

2-Inch Pre-Filters with MERV 8 rating contribute to  
indoor air quality

Supports Clean Rooms, Healthcare, Pharmaceutical,  
Electronics & Precision Assembly/Mfg

Increases perishable product shelf life

## Mars HEPAC®

### Clean Air Series

#### BENEFITS

- Improves indoor air quality
- Inhibits microorganism growth
- Reduces odors
- Increases perishable product shelf life

#### APPLICATIONS

- Clean rooms
- Healthcare
- Pharmaceutical
- Electronics
- Precision fabrication/assembly
- Smoking areas
- Agricultural grow houses
- Sewage/waste treatment facilities



800.421.1266 [marsair.com](http://marsair.com)

**mars**

atmosphere is everything

# HEPAC® Series aesthetically-advanced design

8'-12'

## HEPAC Section Only

HEPAC Section Only	Description	HEPAC Section Length A (in)	HEPAC Section Width B (in)	HEPAC Section Depth C (in)	HEPAC Section Depth D (in)
HEC236-**	HEPAC Section for STD236	36	10 11/16	11 3/4	9 1/4
HEC242-**	HEPAC Section for STD242	42	10 11/16	11 3/4	9 1/4
HEC248-**	HEPAC Section for STD248	48	10 11/16	11 3/4	9 1/4
HEC260-**	HEPAC Section for STD260	60	10 11/16	11 3/4	9 1/4
HEC272-**	(2) 36" HEPAC Section for STD272	72	10 11/16"	11 3/4	9 1/4

\*. \*\* - Use corresponding letters for existing unit voltage options.

Section Only Example: HEC42-PW




## Complete HEPAC Unit

HEPAC with STD2 Unit Selection	Description	HEPAC Package Length A (in)	HEPAC Package Width B (in)	HEPAC Package Depth E (in)	HEPAC Package Depth F (in)
STD236-1U*-PW-HEC	STD236 with HEPAC section	36	10 11/16	21 3/4	8 1/2
STD242-1U*-PW-HEC	STD242 with HEPAC section	42	10 11/16	21 3/4	8 1/2
STD248-1U*-PW-HEC	STD248 with HEPAC section	48	10 11/16	21 3/4	8 1/2
STD260-2U*-PW-HEC	STD260 with HEPAC section	60	10 11/16	21 3/4	8 1/2
STD272-2U*-PW-HEC	STD272 with (2) 36" HEPAC sections	72	10 11/16	21 3/4	8 1/2
STD284-2U*-PW-HEC	STD2 with 2-3 motors and (2) HEPAC sections	84 and Larger	10 11/16	21 3/4	8 1/2

\*. \*\* - Use corresponding letters for existing unit voltage options.

Complete Unit Example: STD242-1UA-PW-HEC



### General Notes:

1. Pearl White is standard color. Consult factory for other colors or Stainless Steel
2. Other door opening sizes are available by combining units (Ex. STD2108 = (3) STD236 units)

## ADDITIONAL INFORMATION

For info on how quickly our units pay for themselves in energy saving, visit: [marsair.com/ROI](http://marsair.com/ROI)

For a demonstration of how air curtains work, see our CFD at: [marsair.com/science-of-air-curtains](http://marsair.com/science-of-air-curtains)

For Accessories, Revit files, brochures, CSI specs, supplements, manuals, and submittals visit our Document Library at: [marsair.com/document-library](http://marsair.com/document-library)

For Air Curtains 101, view: [marsair.com/air-curtains-101](http://marsair.com/air-curtains-101)

## VALUE ADDED ACCESSORIES

- Switches
- Control Packages
- Control Panels
- Mounting Hardware
- Sound Dampening Hardware
- Filters
- Custom Materials, Coatings, Finishes & Colors
- Specialty Construction

All accessories have been specifically designed to enhance installation, operations, and performance.

They have been tested and are compatible to work with the appropriate Mars units to ensure that efficiency standards and performance levels are met.

For a comprehensive list of the most specified accessories, please visit our document library at: [marsair.com/document-library](http://marsair.com/document-library)