

## Choosing the right portable generator.


Choosing a product that is powerful and durable enough to fit your power needs is key. The more wattage your generator produces, the more items you can power.

PowerSmart™	QuietPower™	Home	Elite™	
Lightweight and portable inverter generators for travel and recreational activities.	Designed to give you quiet confidence and reliable backup power during outages.	Versatile portable generators for powering tools and home essentials.	Built with durable, heavy-duty components for home essentials and power tools.	
<b>1700-2600</b> Running Watts <sup>1</sup> <b>2200-3000</b> Starting Watts <sup>2</sup>	<b>5000</b> Running Watts <sup>1</sup> <b>6500</b> Starting Watts <sup>2</sup>	<b>3500-6500</b> Running Watts <sup>1</sup> <b>4375-7500</b> Starting Watts <sup>2</sup>	<b>7000-10000</b> Running Watts <sup>1</sup> <b>8750-12500</b> Starting Watts <sup>2</sup>	
1700 WATTS Recreational Use	3500 WATTS Get by During an Outage	5000 WATTS for Additional Comforts	7000 WATTS for Added Convenience	10000 WATTS Almost Back to Normal
<ul style="list-style-type: none"> <li>LIGHTS</li> <li>TELEVISION</li> <li>PHONE</li> <li>MICROWAVE</li> <li>REFRIGERATOR</li> <li>HOME SECURITY</li> <li>COMPUTER</li> <li>DEEP FREEZER</li> <li>SUMP PUMP</li> <li>CLOTHES WASHER</li> <li>POWER TOOLS</li> <li>FURNACE</li> <li>WINDOW AC UNIT</li> <li>WELL PUMP</li> <li>OUTDOOR AC UNIT</li> <li>HEAVY EQUIPMENT</li> </ul>	<ul style="list-style-type: none"> <li>LIGHTS</li> <li>TELEVISION</li> <li>PHONE</li> <li>MICROWAVE</li> <li>REFRIGERATOR</li> <li>HOME SECURITY</li> <li>COMPUTER</li> <li>DEEP FREEZER</li> <li>SUMP PUMP</li> <li>CLOTHES WASHER</li> <li>POWER TOOLS</li> <li>FURNACE</li> <li>WINDOW AC UNIT</li> <li>WELL PUMP</li> <li>OUTDOOR AC UNIT</li> <li>HEAVY EQUIPMENT</li> </ul>	<ul style="list-style-type: none"> <li>LIGHTS</li> <li>TELEVISION</li> <li>PHONE</li> <li>MICROWAVE</li> <li>REFRIGERATOR</li> <li>HOME SECURITY</li> <li>COMPUTER</li> <li>DEEP FREEZER</li> <li>SUMP PUMP</li> <li>CLOTHES WASHER</li> <li>POWER TOOLS</li> <li>FURNACE</li> <li>WINDOW AC UNIT</li> <li>WELL PUMP</li> <li>OUTDOOR AC UNIT</li> <li>HEAVY EQUIPMENT</li> </ul>	<ul style="list-style-type: none"> <li>LIGHTS</li> <li>TELEVISION</li> <li>PHONE</li> <li>MICROWAVE</li> <li>REFRIGERATOR</li> <li>HOME SECURITY</li> <li>COMPUTER</li> <li>DEEP FREEZER</li> <li>SUMP PUMP</li> <li>CLOTHES WASHER</li> <li>POWER TOOLS</li> <li>FURNACE</li> <li>WINDOW AC UNIT</li> <li>WELL PUMP</li> <li>OUTDOOR AC UNIT</li> <li>HEAVY EQUIPMENT</li> </ul>	<ul style="list-style-type: none"> <li>LIGHTS</li> <li>TELEVISION</li> <li>PHONE</li> <li>MICROWAVE</li> <li>REFRIGERATOR</li> <li>HOME SECURITY</li> <li>COMPUTER</li> <li>DEEP FREEZER</li> <li>SUMP PUMP</li> <li>CLOTHES WASHER</li> <li>POWER TOOLS</li> <li>FURNACE</li> <li>WINDOW AC UNIT</li> <li>WELL PUMP</li> <li>OUTDOOR AC UNIT</li> <li>HEAVY EQUIPMENT</li> </ul>

Visit [www.BRIGGSandSTRATTON.com](http://www.BRIGGSandSTRATTON.com) for our Generator Buying Guide!

<sup>1</sup> Per ANSI/PGMA G300-2015  
<sup>2</sup> Starting Watts is the maximum current that can momentarily be supplied when starting a motor, multiplied by the generator's rated voltage.

2018 Portable Generators



**You.Powered.™**

At the end of the day, a job well done is its own reward. Our equipment is there to help make it happen. It's easy to master, durable and ready for a challenge. Just like you.

## Get the support you need.

The Briggs & Stratton customer support portal is designed to help you answer questions you have about your Briggs & Stratton branded product. Our Answer Center representatives are available Monday-Friday, 8AM-5PM CT.

### Contact Us By Phone

Connect with someone about your specific product through our call center:  
**Portable Generators: (800) 743-4115**

### Online Resources

[www.BRIGGSandSTRATTON.com](http://www.BRIGGSandSTRATTON.com)

- How-to articles
- Videos
- Frequently Asked Questions
- Maintenance Tips



MC11138

Copyright ©2016. All rights reserved.



# Power anywhere, anytime.

**YOU.POWERED.**



# Innovation inspired by you.

## StatStation® Wireless



Download the StatStation® Wireless app to monitor your generator from the comfort of your home.

- Total power used
- Hours until empty
- Total unit hours
- Maintenance reminders



<sup>1</sup> Versus a standard generator 030607

<sup>2</sup> As tested per ISO3744 power standard when compared to standard generator 030607

<sup>3</sup> At 25% load

The Bluetooth™ word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Briggs & Stratton Corporation is under license. Other trademarks and trade names are those of their respective representative.

## Q6500 QuietPower™ Series

- **30% lighter<sup>1</sup>**
- **45% more compact<sup>1</sup>**
- **Over 60% quieter than a standard generator<sup>2</sup>**



Inverter Technology  
Produces smoother power for sensitive electronics.

Up to 14 hour run time<sup>3</sup>  
Extended refueling with variable RPM engine that automatically adjusts to wattage needs.

Variable RPM engine  
Automatically adjusts to wattage needs extending refueling intervals.

Integrated engine/alternator  
Get reliable power that's more quiet, compact and lighter than ever.

Power usage meter  
Monitor total power available.

Protective shell  
Minimize noise while protecting internal components.



# Portable Generator Specifications



Series	PowerSmart Series™			QuietPower™ Series			Home Series			Elite Series™		
Model #	030651	030545	030675	030676/030680 CARB	030713	030681 CARB	030708	030710	030663A	030664A	030552A CARB	030679A
Running Watts <sup>1</sup>	1700	2600	5000	3500	5000	5000	5750	6500	7000	8000	7500	8000
Starting Watts <sup>2</sup>	2200	3000	6500	4375	6250	6250	7185	8125	8750	10000	9375	10000
Volts	120	120	120/240	120	120/240	120/240	120/240	120/240	120/240	120/240	120/240	120/240
Engine	Briggs & Stratton® OHV											
CC	111	171	306	208	389	389	389	389	420	420	420	420
Features	<ul style="list-style-type: none"> <li>Fuel Tank Capacity: 1 Gallon, 1.5 Gallon, 5 Gallon, 5 Gallons, 7.5 Gallons, 7.5 Gallons, 7.5 Gallons, 7.5 Gallons, 7.5 Gallon, 7.5 Gallons, 7.5 Gallons, 7.5 Gallons, 7.5 Gallons</li> <li>Run Time: 8 Hours (25% Load), 10 Hours (25% Load), 14 Hours (25% Load), 14 Hours (50% Load), 12 Hours (50% Load), 11.5 Hours (50% Load), 10.5 Hours (50% Load), 9 Hours (50% Load), 9 Hours (50% Load), 9 Hours (50% Load), 9 Hours (50% Load), 9 Hours (50% Load)</li> <li>Alternator: Permanent Magnet, Permanent Magnet, Permanent Magnet, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™, Power Surge™</li> <li>Starting: Recoil, Recoil, Recoil, Recoil, Recoil, Recoil, Recoil, Recoil, Recoil, Electric / Recoil, Electric / Recoil, Electric / Recoil, Electric / Recoil</li> <li>Low Oil Shutdown: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Automatic Voltage Regulation: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Automatic Idle Control: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Muffler: Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™, Super Lo-Tone™</li> <li>Spark Arrestor: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Fuel Gauge: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Hour Meter: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Rubber Outlet Covers: ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■, ■</li> <li>Wheel Kit: ■, 6", 8", 7", 10", 10", 10", 10", 10", 12", 12", 12", 12"</li> <li>Engine Oil Included: ■, ■, ■, ■, ■, ■, ■, ■, ■, Oil in crank case, Oil in crank case, Oil in crank case, Oil in crank case</li> </ul>											
Outlets	<ul style="list-style-type: none"> <li>(2) 120V-20A GFCI, (4) 120V-20A GFCI, (4) 120V-20A GFCI, (1) 120V-20A GFCI, (4) 120V-20A GFCI, (4) 120V GFCI, (4) 120V GFCI, (6) 120V-20A, (4) 120V-20A, (4) 120V-20A, (4) 120V-20A, (4) 120V-20A, (4) 120V-20A</li> <li>(1) 12V-5A, DC, (1) 12V-5A, DC, (1) 120/240V-30A Locking, (1) 120V-30A RV, (2) 120V Household, (1) 120V-30A Locking, (2) 120V Household, (1) 120V/240V-30A Locking, (1) 120V/240V-30A Locking, (1) 120V/240V-30A Locking, (1) 120V/240V-30A Locking, (1) 120V/240V-30A Locking, (1) 120V/240V-30A Locking</li> <li>(1) Parallel, (1) 120V-30A Locking, (2) USB, (1) 120/240V-30A Locking, (1) 120/240V-30A Locking</li> <li>(1) USB Adapter, (1) Parallel, (1) USB</li> </ul>											
Dimensions (L x W x H)	21" x 12.25" x 17.35"	26" x 14" x 21"	27.7" x 23.2" x 22.3"	25.53" x 21.92" x 21.43"	29" x 21.5" x 25.5"	29.0" x 21.5" x 25.5"	29" x 21.5" x 25.5"	29" x 21.5" x 25.5"	34.8" x 22.3" x 26"	34.8" x 22.3" x 26"	34.8" x 22.3" x 26"	34.8" x 22.3" x 26"
Weight	54 lbs	84 lbs	128 lbs	114 lbs	187 lbs	187 lbs	190 lbs	196 lbs	221 lbs	224 lbs	225 lbs	224 lbs
Warranty <sup>3</sup>	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	2-Year Limited Consumer 1-Year Limited Commercial	3-Year Limited Consumer 1-Year Limited Commercial	3-Year Limited Consumer 1-Year Limited Commercial	3-Year Limited Consumer 1-Year Limited Commercial	3-Year Limited Consumer 1-Year Limited Commercial

Included ■

Final product may vary from images shown.  
 Briggs & Stratton reserves the right to change specifications, features or pricing without notice.  
<sup>1</sup>Per ANSI/PGMA G300-2015.  
<sup>2</sup>Starting Watts is the maximum current that can momentarily be supplied when starting a motor, multiplied by the generator's rated voltage.  
<sup>3</sup>See operator's manual or www.briggsandstratton.com for complete warranty details.  
 The Bluetooth™ word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Briggs & Stratton Corporation is under license. Other trademarks and trade names are those of their respective representative.

## Engines Matter



### Briggs & Stratton® Engines

Powerful. Versatile. Durable.

Briggs & Stratton® engines deliver the precise amount of power and performance needed to match your demands.

Overhead Valve (OHV) technology keeps engines running cooler and cleaner for:

- More power
- Smoother operation
- Longer engine life
- Improved fuel economy
- Medium- to heavy-duty needs



Limited Warranty<sup>3</sup>

## Portable Generator Features

### Key Electric Start

Easy, reliable starting  
 No priming, no rope to pull. Quick and easy starting right from the control panel.

Models: 030663, 030664, 030679, 030552A CARB

### Never Go Flat Wheels

Easily maneuver the generator around your property.

Models available: Home and Elite Series units

### Multi-Featured Control Panel

Put the features at your fingertips with this control panel that includes household and twist lock outlets with circuit breaker protection, rubber outlet covers and hour meter.



## Why Inverters?

You like to take your power on the road for convenience and protection, whether you're camping in the wild or tailgating at the game. Our inverter generators provide the perfect quiet, fuel-efficient solution for maintaining steady, accurate and clean power output at a level similar to what you experience at home.



**1700** Running Watts<sup>1</sup>  
**2200** Starting Watts<sup>2</sup>

030651

- 111cc Engine
- Provides up to 8 Hours of Run Time at 25% Load
- Outlets: 2-120V Household 12V, 5A DC Household & Accessory USB Adapter
- 59 Decibels<sup>3</sup>
- Parallel Capable



**2600** Running Watts<sup>1</sup>  
**3000** Starting Watts<sup>2</sup>

030545

- 171cc Engine
- Provides up to 10 Hours of Run Time at 25% Load
- Outlets: 4-120V Household 1-120V, 30A Locking 12V, 5A DC Household & Accessory RV Adapter USB Port
- 58 Decibels<sup>3</sup>
- Parallel Capable



**5000** Running Watts<sup>1</sup>  
**6500** Starting Watts<sup>2</sup>

030675

- 306cc Engine
- Provides up to 14 Hours of Run Time at 25% Load
- Outlets: 120A-20A (4), USB (2), 120V-240V locking outlet
- 66 Decibels<sup>3</sup>
- QuietPower Series Inverter Technology



**Quieter<sup>3</sup>**  
 Consistent, quiet power that traditional camping generators can't match.



**Lighter<sup>4</sup>**  
 For easy mobility.



**Inverter Technology**  
 Produces smoother power for sensitive electronics.



**Powersmart Mode**  
 Automatically adjusts engine speed to save fuel and run longer.

### Parallel Kit

Connects two PowerSmart Series inverter generators together for more power. Available for models 030545 and 030651



Model: 6278

### Inverter Covers

Protects your generator from debris during storage or transportation.

- Features:
- Easy-access opening for handle
  - Side pocket for operator's manuals and accessory storage
  - Cover strap wraps under generator for secure fit
- Models and Sizes Available:
- 6494: For small generators (15 in. x 10 in. x 21 in.)
  - 6495: For medium-sized generators (20 in. x 14 in. x 25 in.)
  - 6496: For large-sized generators (18 in. x 22 in. x 27 in.)



Model: 6494

<sup>1</sup>Per CSA C22.2 No. 100-14  
<sup>2</sup>Starting Watts is the maximum current that can momentarily be supplied when starting a motor, multiplied by the generator's rated voltage.  
<sup>3</sup>Sound levels may vary based on proximity and location; measured at ¼ load at 7 meters from control panel side.  
<sup>4</sup>Compared to a traditional camping generator.