

SAFETY DATA SHEET

SECTION 01 - PRODUCT AND COMPANY IDENTIFICATION

Product Identifier:	All Clean Natural Hand Sanitizing Wipe (Wipe) – WHO Formula	
Product Code:	Hand Sanitizer 70% (Wipe)	
Other Means of Identification:	Antiseptic Skin Cleanser	
Cas Number	Ethanol (70%) 64-17-5	
Product Use and Restrictions on use:	Hand Sanitizer/ Antiseptic skin cleanser Do not use on children/infants less than 2 years of age (unless directed by a doctor/physician/health care practitioner/health care provider/health care professional).	
Supplier Identifier:	All Clean Natural Ltd. 5310 1 st Street SW Calgary, AB, T2H 0C8 (403) 455-9959	
24-hour Emergency Phone:	CANUTEC (24HR EMERGENCY TELEPHONE) (613) 996-6666	
TDG Emergency Response Plan: NWB Emergency Response	ERP 2-2063	
Assistance Canada (ERAC):	1-800-265-0212	

SECTION 02 - HAZARD IDENTIFICATION

Flammable Liquid Eye Irritation Category : Category 3 : 2A



Signal word Hazard statements (GHS-CCOHS)	: Danger : H225 - Highly flammable liquid and vapor : H319 - Causes serious eye irritation and remove contact lenses
Precautionary statements	 : P210 – Keep away from heat, hot surfaces, open flames, sparks. – No smoking : P233 - Keep container tightly closed : If in eyes – Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue to rinse. If eye irritation persists, seek medical advice/attention. : In case of fire – Use dry sand, dry chemical or alcohol resistant foam for extinction.
Storage	: Store in a well-ventilated place. Keep cool
Other Hazards:	: Not known

SECTION 03: COMPOSITION/ INFORMATION ON INGREDIENTS

Mixture Names	CAS-No	%
Ethanol	64-17-5	69.00-80.00
Hydrogen Peroxide	7722-84-1	0.125
Glycerine	56-81-5	1.45
Water	7732-18-5	Balance

SECTION 04: FIRST AID MEASURES

Eye Contact:

When using this product avoid contact with eyes. If contact occurs, rinse thoroughly with water. Stop use and ask/consult a health care professional if irritation develops.

Inhalation:

Remove the victim into the fresh air. If difficulty breathing persists, seek medical attention.

Ingestion:

Rinse mouth with water, do not induce vomiting. Call the Poison Information Centre (1-866-454-1212) SK, Canada. Consult a doctor/medical professional if you feel unwell.

Ingestion of Large Quantities:

Take individual immediately to hospital.

Note to Physician:

Treat Symptomatically.

SECTION 05: FIRE FIGHTING METHODS	
Suitable extinguishing media	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable extinguishing media	: High volume water jet.
Specific hazards arising from the hazardous prod	luct (e.g., hazardous combustion products):
Fire Hazard	: Keep away from heat and sources of ignition. Flash back possible over considerable distance. Beware of vapors accumulating to form explosive concentrations. Vapors can accumulate in low areas.
Hazardous Combustion Products	: Carbon Oxides
Special protective equipment and precautions for Specific Protective equipment for fire-fighters	or firefighters: : Use personal protective equipment.
Specific Extinguishing methods	: Use water spray to cool unopened containers. Fire residues

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures:

Protective equipment	: Remove all sources of ignition. Ensure clean-up is conducted by trained personnel only. Wear appropriate protective equipment such as gloves, safety goggles, and coveralls when handling in bulk.
Small Spill	: Dilute with water and mop up, or absorb with an inert dry material and place in an appropriate waste disposal container.
Large spill	: Flammable liquid. Keep away from heat. Keep away from sources of ignition. Stop leak if without risk.

and contaminated fire extinguishing water must be disposed of in accordance with local regulations. In the event of fire

and/or explosion do not breathe fumes.

Emergency procedures	: Mark the danger area. Consider evacuation. Stop engines and no smoking. No naked flames or sparks. Spark- and explosion- proof of appliances and lighting equipment. Keep containers closed.
Environmental precautions	: Do not allow contact with soil, surface, or ground water.
Cleaning procedure	: Eliminate all ignition sources if safe to do so. Stop leak if safe to do so. Contain spillage, and then collect with non- combustible absorbent material (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local/national regulations (see section 13). Flush away traces with water. For large spills, dike spilled material, or otherwise, contain material to ensure run off does not reach a waterway.

SECTION 07: HANDLING AND STORAGE

7.1 Precautions for Safe Handling			
Precautions for safe handling	Take necessary action to avoid static electricity discharge		
	(which might cause ignition of organic vapors). Keep away		
	from fire, sparks, and heated surfaces.		
7.2 Conditions for Safe Storage (including incompatible materials)			
	Keep away from heat and sources of ignition. Keep in a		
	cool, well-ventilated place. Keep away from oxidizing		
	agents. Keep out of reach of children. Keep container		
	tightly closed. Store in suitable labeled containers.		
Others	Good personal hygiene practices are suggested, such as		
	abstaining from eating, drinking and smoking in the		
	workplace		

SECTION 08: EXPOSURE CONTROL/ PERSONAL PROTECTION

8.1 Control Parameters Occupational Exposure Guidelines, Limits, and the Source of Those Values				
Exposure limits:	CAS-No.	Form of	Permissible	Basis
		Exposure	Concentration	
Ethanol	64-17-5	TWA	1,000 ppm	ACGIH
			1,000ppm	NIOSH
			1,900 mg/m3	REL
			1,000 ppm	OSHA Z1
			1,900 mg/m3	

Page 4 | 9

Glycerin	56-81-5	TWA	15mg/m3 (total)	OSHA
			5mg/m3	PEL
Hydrogen Peroxide	7722-84-1	TWA	1ppm (1.4mg/m3)	NIOSH
				REL
			1ppm (1.4 mg/m3)	OSHA
				PEL

8.2 Appropriate Engineering Controls

Engineering Controls

Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

8.3 Individual Protection Measures (e.g. personal protective equipment).		
Personal Protective Equipment (PPE)	No special protective equipment required	
Hand Protection		
Skin Protection		
Respiratory Protection		
Hygiene Measures		

8.4 Exposure Limits					
Ingredients	Exposure Limit	Exposure Limit	Immediately Dangerous to Life or Health		
	ACGIH	OSHA	IDLH		
Ethanol	1000 ppm TLV-TWA	1000 ppm TWA	3300 ppm		
Hydrogen	TWA-1.0 PPM	unknown	TLV BASIS- Eye, URT, & Skin Irr.		
Peroxide					
Glycerin	TWA- 10mg/m3	unknown	TLV BASIS- URT irr		
Water		unknown	Oral LD50 (Rat)> 90ml/kg		

SECTION 09: PHYSICAL AND CHEMICAL PROPERTIES

Physical and chemical properties:

Appearance (physical state, colour, etc.)
Odour
Odour threshold
Boiling point
рН
Melting point
Freezing point
Volatility
Lower flammability limit
Upper Flammability Limit
Flashpoint
Evaporation rate
Vapour pressure
Vapour density

: Gel/Translucent
: Typical lower alcohol odour
: No data available
: No data available
: 7.0-8.5
: No data available

: 0.833-0.840 @ 20°C
: Dissolved in water and
alcohol
: No data available

SECTION 10: STABILITY AND REACTIVITY

Stability and reactivity:	
Chemical stability	: Stable under normal conditions
Possibility of hazardous reactions	: No dangerous reaction known under conditions of normal use
Conditions to avoid (e.g., static discharge, shock, or vibration)	: Heat, flames and sparks.
Incompatible materials	: Strong acids. Strong bases
Hazardous decomposition products	: Fumes. Carbon monoxide. Carbon dioxide. May release flammable gases.

SECTION 11: TOXICOLOGICAL INFORMATION

Routes of Entry	: Absorbed through skin. Dermal contact. Eye contact.
	Inhalation. Ingestion.
Inhalation	: Health injuries are not known or expected under normal use.
Ingestion	: Health injuries are not known or expected under normal use.
Skin contact	: Health injuries are not known or expected under normal use.
Eye contact	: Causes serious eye irritation, redness, pain

Symptoms related to the physical, chemical and toxicological characteristics:

No symptoms known or expected.

Delayed and immediate effects, and chronic effects from short-term and long-term exposure: No symptoms known or expected

Numerical measures of toxicity, including acute toxicity estimates (ATEs):

Acute oral toxicity	••	0	Health injuries are not known or expected under normal use.
IARC			No component of this product present at levels greater than
			or equal to 0.1% is identified as probable, possible or
			confirmed human carcinogen by IARC.
OSHA			No ingredient of this product present at levels greater than or
			equal to 0.1% is identified as a carcinogen or potential
			carcinogen by OSHA.

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP. The substance or mixture is not classified as specific target

STOT-single exposure

organ toxicant, single exposure

SECTION 12: ECOLOGICAL INFORMATION

Ecological information:

Ingredients	Ecotoxicity- Fish Species Data	Toxicity to Aquatic Plants	Toxicity to Micro Organisms	Other Adverse Effects
Environmental Effects			Harmful to aquatic life	2.
Ethanol	LC 50/96 Hour Oncorhynchus	Growth inhibition/96 Hours	Pseudomonas Putida 6,500 mg/l Inhibition	BOD 740-840 mg/g
	mykiss>10,000 mg/l	Chlorella vulgaris 1000 mg/l	of cell growth	
Hydrogen Peroxide	TWA-1.0 PPM,	-	-	-
Glycerin	TWA-10mg/m3	-	-	-
Water	-	-	-	-

SECTION 13: DISPOSABLE CONSIDERATIONS

13.1 Information on Safe H	andling for Disposal and Methods of Disposal, Including any
Contaminated Packaging.	
Disposal Methods	The product should not be allowed to enter drains, water courses or the soil. Where possible, recycling is preferred to disposal or incineration. If recycling is not practicable, dispose of in compliance with local regulations. Dispose of wastes in an approved waste disposal facility.
Disposal Considerations	Dispose of as unused product. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
RCRA – Resource	D001 (ignitable)
Conservation and	
Recovery Authorization	
Act: Hazardous Waste	

SECTION 14: TRANSPORTATION INFORMATION

TDG (Canada) UN number Description of the goods Transport hazard class(es) Packing group

: UN1170 : ETHANOL Hand Sanitizer : Primary Class -3 : III

NTP

Environmental Hazards	
Transport in bulk, if applicable	

IMDG/IMO

UN number Description of the goods Marine Pollutant: : No : 242 (49 CFR 173.xxxx)

: UN- 1170 Class: 3 Packing Group: II : ETHANOL Hand Sanitizer : No

SECTION 15: REGULATORY INFORMATION

Safety, health and environmental regulations specific to the product:		
CERCLA	: This material does not contain any components with a CERCLA RQ.	
SARA 304 Extremely Hazardous Substances Reportable Quantity	: This material does not contain any components with a section 304 EHS RQ.	
SARA 311/312 Hazards	: Fire hazard acute health hazard.	
SARA 302	: SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.	
SARA 313	: SARA 313: This Material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.	
California Prop 65	: This product does not contain any chemicals known to the State of California to cause cancer, birth or any other reproductive defects.	

SECTION 16: OTHER INFORMATION

NFPA Diamond for Ethanol



NFPA Health Hazard: 2 -Moderate NFPA Fire Hazard: High NFPA Physical Hazard: 0- Not Significant, 1=Slight

Additional Information: This product has been classified in accordance with the hazard criteria of the Canadian Controlled Products Regulations (CPR) and the MSDS contain all the information required by the CPR. **Disclaimer:** NOTICE TO READER: All Clean Natural Ltd. expressly disclaims all express or implied warranties of merchantability and fitness for a particular purpose, with respect to the product or information provided herein, and shall under no circumstances be liable for incidental or consequential damages. Do not use ingredient information and/or ingredient percentages in this MSDS as a product specification. For product specification information refer to a

Page 8 | 9

Product Specification Sheet and/or a Certificate of Analysis. These can be obtained from All Clean Natural Ltd. All information appearing herein is based upon data obtained from the manufacturer and/or recognized technical sources. While the information is believed to be accurate, All Clean Natural Ltd. makes no representations as to its accuracy or sufficiency. Conditions of use are beyond All Clean Natural Ltd's control and therefore users are responsible to verify this data under their own operating conditions to determine whether the product is suitable for their particular purposes and they assume all risks of their use, handling, and disposal of the product, or from the publication or use of, or reliance upon, information contained herein. This information relates only to the product designated herein and does not relate to its use in combination with any other material or in any other process.

Note: Information in this SDS is from available published sources and is believed to be accurate. All Clean Natural Ltd. assumes no liability resulting from the use of this SDS. The responsibility to provide a safe workplace remains with the user. **Note: The responsibility to provide a safe workplace remains with the user**.

Preparation date:

:09 July 2020