

#### **Section 1: Information**

Product Name	Ox-Gard Anti-Oxidant Compound
Product Code(s)	OX-800
Recommended Usage	Lubricants, Greases and Release Products, Sealant
Manufacturer/Distributor	Power Products LLC (dba Gardner Bender)
Address	N85 W12545 Westbrook Crossing Menomonee Falls, WI 53051
Website	www.powerprodllc.com
Telephone Number	1-800-624-4320
<b>EMERGENCY Telephone Number</b>	Chemtrec: (24/7) 800-424-9300 Or International 703-527-3887

### **Section 2: Hazard Identification**

				This chemical is	s not considered hazardous	
Classification of the substance or mixture			according to the OSHA Hazard Communication			
			Standard 2012	(29 CFR 1910.1200).		
GHS Labe	el Elements			•		
Sign	al Word			None		
				The product co	ntains no substances which at their	
Haz	ard Statement			given concentra	ation are considered to be	
				hazardous to he	ealth	
Precaution	onary Statements					
Prevention			None			
Response			None			
Storage			None			
Disposal			None			
Hazards Not Otherwise Classified				Not Applicable		
				Very toxic to aquatic life with long lasting effects;		
Other Information			6.7% of the mixture consists of ingredient(s) of			
			unknown toxicity.			
NFPA	Health Hazard: 1	Flammability: 1 Ins		tability: 0	Physical & Chemical Hazard: -	
HMIS	Health Hazard: 1	Flammability: 1 Phy		ysical Hazard: 0	Personal Protection: X	

# **Section 3 - Composition/Information on Ingredients**

Substance / Mixture		Mixture	Mixture	
Chemical Name	CAS Number	Weight %	Trade Secret	
Zinc (powder)	7440-66-6	10 - 15	*	
Talc	14807-96-6	5 – 10	*	
Graphite	7782-42-5	1 - 5	*	
*The exact percentage (concentration) of composition has been withheld as a trade secret.				






















### **Section 4: First-Aid Measures**

<b>Descriptions of Fir</b>	rst Aid Measures		
General Advice	Show this safety data sheet to the doctor in attendance.		
Inhalation	Move to fresh air. If not breathing, give artificial respiration. Avoid direct contact		
IIIIIaiativii	with skin. Use barrier to give mouth-to-mouth resuscitation. Consult a physician.		
Skin	Wash off immediately with soap and plenty of water. Remove and wash		
SKIII	contaminated clothing before re-use.		
	Immediately flush with plenty of water. After initial flushing, remove any contact		
Eye	lenses and continue flushing for at least 15 minutes. If symptoms persist, call a		
	physician.		
	Clean mouth with water and afterwards drink plenty of water. Do NOT induce		
Ingestion	vomiting. Never give anything by mouth to an unconscious person. Consult a		
	physician if necessary		
	Use personal protective equipment. Avoid contact with skin, eyes and clothing.		
Protection of	Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation.		
First-aiders	Ensure that medical personnel are aware of the material(s) involved, and take		
	precautions to protect themselves.		
Most Important Symptoms/Effects (Acute & Delayed) Potential Health Effects			
Most Important Symptoms/Effects No information available.			
Indication of Immediate Medical Attention & Special Treatment Needed, If Necessary			
Note To Physician	Treat symptomatically.		

### **Section 5: Fire-Fighting Measures**

Extinguishing Media		
Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local	
Suitable Extinguishing Media	circumstances and the surrounding environment.	
	Dousing metallic fires with water may generate hydrogen gas, an	
<b>Unsuitable Extinguishing Media</b>	extremely dangerous explosion hazard, particularly if fire is in a	
	confined environment (i.e., building, cargo hold, etc.)	

Special hazards arising from the substance or mixture		
Specific Hazards Arising from the Chemical	Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.	
<b>Explosion Data: Sensitivity to Mechanical Impact</b>	None	
Explosion Data: Sensitivity to Static Discharge	None	
Protective Equipment and Precautions for Firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.	



















#### **Section 6 - Accidental Release Measures**

Personal precautions, protective equipment and emergency procedures		
Personnel Precautions	Use personal protective equipment. Keep people	
reisonnei ri ecautions	away from and upwind of spill/leak.	
	Do not allow material to contaminate ground water	
Environmental Precautions	system. Prevent further leakage or spillage if safe to	
Environmental Frecautions	do so. Avoid release to the environment. See	
	Section 12 for additional Ecological Information.	
Methods for Containment	Prevent further leakage or spillage if safe to do so.	
	Small spillage: Soak up with inert absorbent	
	material. Pick up and transfer to properly labeled	
Methods for Cleaning Up	containers. Large spillage: Dike far ahead of liquid	
	spill for later disposal. Take up mechanically and	
	collect in suitable container for disposal.	

# Section 7 - Handling and Storage

Conditions for safe storage, including a	any incompatibilities
Conditions for safe storage, including a	
	Avoid contact with skin, eyes and clothing. Wear personal protective equipment. Remove and wash contaminated
	1
Precautions for safe handling	clothing before re-use. Do not breathe vapors or spray mist. Do
	not eat, drink or smoke when using this product. Wash
	thoroughly after handling.
Storage	Keep containers tightly closed in a dry, cool and well-
	ventilated place. Keep out of the reach of children.
Incompatible Products	Acids. Oxidizing agents.

# **Section 8 - Exposure Controls/Personal Protection**

Control parameters				
Exposure Guidelines				
Chemical Name ACGIH TLV OSHA PEL NIOSH IDLH				
Talc (14807-96-6)	TWA: 2 mg/m3	(vacated) TWA: 2 mg/m3	IDLH: 1000 mg/m3 contains no asbestos and <1% quartz TWA: 2 mg/m3	



















Graphite (7782-42-5)		TWA: 15 mg/m3 total dust synthetic TWA: 5 mg/m3 total dust synthetic (vacated) TWA: 2.5 mg/m3 respirable dust natural (vacated) TWA: 10 mg/m3 total dust synthetic (vacated) TWA: 5 mg/m3 respirable fraction synthetic TWA: 15 mppcf natural	
Appropriate Engineering Controls  Showers Eyewash static Ventilation sys			
Individual Protection			
Hygiene Measures		Handle in accorda and safety practic	nce with good industrial hygiene e.
Eye/Face Protection		Safety glasses with side-shields.	
Skin & Body Protections		Impervious clothing. Nitrile gloves.	
Respiratory Protection		use conditions. If e irritation is experi respiratory protec	ipment is needed under normal exposure limits are exceeded or lenced, NIOSH/MSHA approved ction should be worn. In case of ation wear suitable respiratory

## **Section 9 - Physical and Chemical Properties**

Information on Physical and Chemical Properties				
Appearance (physical state, color)	Semi Solid; Gray	Flash Point	>221 C	
Odor	Petroleum Like	Vapor Density	N/A	
Odor Threshold	N/A	Specific Gravity	1.37	
рН	Neutral	<b>Relative Density</b>		
Melting Point/ Freezing Point	>138 C / 280.4 F N/A	Solubility in Water	Negligible	
Volatiles by Wt. (%):	N/A	Partition coefficient: n-octanol/water	N/A	
Flammability (solid, gas)	N/A	Auto-ignition temperature	N/A	
<b>Evaporation Rate</b>	N/A	Decomposition temperature	N/A	
Viscosity	N/A			





















## **Section 10: Stability and Reactivity**

Reactivity	No data available.	
Chemical Stability	Stable under recommended storage conditions.	
Dossibility of Hazardous Doostions	Mixture reacts slowly with water resulting in evolution of	
Possibility of Hazardous Reactions	hydrogen	
Hazardous Polymerization	Hazardous polymerization does not occur.	
Conditions to Avoid Incompatible products.		
Incompatible Materials Acids. Oxidizing agents.		
<b>Hazardous Decomposition Products</b>	None known based on information supplied.	

### **Section 11 - Toxicological Information**

3					
Information on Toxicological Effects					
Acute Toxicity		6.7% of the mixture consists of ingredient(s) of unknown toxicity.			
LD50 Oral		5575 mg/kg; Acute toxicity estimate			
Information on The Likely Routes of Exposure					
ΙΝΟΔΕΤΙΛΝ		route of exposure. Ingestion may cause rritation, nausea, vomiting and diarrhea.			
<b>Potential Chronic Health Effects</b>					
Carcinogenicity	Contains no ingredients above reportable quantities listed as a carcinogen.				
Mutagenicity	No information a	No information available.			
Teratogenicity	No information available.				
Developmental Effects	No information a	No information available.			
Fertility Effects	No information available.				

# **Section 12 - Ecological Information**

Chemical	Toxicity to Algae	Toxicity to Fish	Daphnia Magna
Name			(Water Flea)
Zinc (powder)	EC50 72 h: 0.09 - 0.125	LC50 96 h: 0.211-0.269 mg/L semi-	EC50 48 h: 0.139 -
7440-66-6	mg/L static	static (Pimephales promelas)	0.908 mg/L Static
	(Pseudokirchneriella	LC50 96 h: 2.16-3.05 mg/L flow-	(Daphnia magna)
	subcapitata)	through (Pimephales promelas)	
	EC50 96 h: 0.11 - 0.271	LC50 96 h: = 0.24 mg/L flow-through	
	mg/L static	(Oncorhynchus mykiss)	
	(Pseudokirchneriella	LC50 96 h: = 0.41 mg/L static	
	subcapitata)	(Oncorhynchus mykiss)	
		LC50 96 h: = 0.45 mg/L semi-static	
		(Cyprinus carpio)	
		LC50 96 h: = 0.59 mg/L	
		semi-static (Oncorhynchus mykiss)	





















	LC50 96 h: = 2.66 mg/L static	
	(Pimephales promelas)	
	LC50 96 h: = 3.5 mg/L static (Lepomis	
	macrochirus)	
	LC50 96 h: = 30 mg/L (Cyprinus	
	carpio)	
	LC50 96 h: = 7.8 mg/L static	
	(Cyprinus carpio)	
Talc	LC50 96 h: > 100 g/L semi-static	
14807-96-6	(Brachydanio rerio)	
Persistence and Degradability	No information available.	
Bioaccumulative Potential	No information available.	
Other Adverse Effects	No information available.	

## **Section 13 - Disposal Considerations**

Waste Disposal Methods	Dispose of in accordance with federal, state, and local regulations
Contaminated Packaging	Do not re-use empty containers.

### **Section 14 - Transport Information**

DOT	Not regulated		
TDG			
UN-	Number	UN3082	
Proj	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.	
Haz	ard Class	9	
Pacl	king Group	III	
Desc	cription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc	
		(powder)), 9, III	
MEX			
UN-	Number	UN3082	
Proj	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.	
Haz	ard Class	9	
Pacl	king Group	III	
Desc	cription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc	
		(powder)), 9, III	
ICAO			
UN-	Number	UN3082	
Proj	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.	
Haz	ard Class	9	
Pacl	king Group	III	
Desc	cription	UN3082, Environmentally hazardous substance, liquid, n.o.s., 9, III	



















IATA		
	-Number	UN3082
	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.
	zard Class	9
	cking Group	III
	scription	
Des	scription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc (powder)), 9, III
IMDG/IMI	p	(powder)), 5, 111
•	-Number	UN3082
_	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.
	zard Class	9
Pac	cking Group	III
	S No.	F-A, S-F
	scription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc
	•	(powder)), 9, III
RID		
UN-	-Number	UN3082
Pro	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.
Haz	zard Class	9
Pac	cking Group	III
Clas	ssification Code	M6
Des	scription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc
		(powder)), 9, III
ADR		
UN-	-Number	UN3082
	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.
	zard Class	9
	cking Group	III
	ssification Code	M6
	nnel Restriction	(E)
Cod		
Des	scription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc
4.5	D /DYD Y 1 1	(powder)), 9, III
	R/RID Labels	0
ADN	Oli I N	
	per Shipping Name	Environmentally hazardous substance, liquid, n.o.s.
	zard Class	9
	cking Group	
	ssification Code	M6
	ecial Provisions	274, 335, 601
Des	scription	UN3082, Environmentally hazardous substance, liquid, n.o.s. (Zinc
		(powder)), 9, III



















_	
Limited Quantity 5 L	

### **Section 15 - Regulatory Information**

Section 13 - Regulatory Information								
U.S. Federal Regulations								
SARA 313								
Chemical Name	CAS – No		Weight %		Threshold Value %			
Zinc (Powder)	7	440-66	-6		10 - 15		1.0	
SARA 311/312 Hazard Categories								
Acute Health Hazard			No	No				
Chronic Health Ha	azard			No	No			
Fire Hazard				No	No			
Sudden Release o	f Pressu	re Haza	rd	No				
Reactive Hazard				No				
Clean Water Act								
Chemical Name To		Toxic Po	Toxic Pollutants		Priority Pollutants			
Zinc (Powder)		X			X			ζ
CERCLA								
Chemical Name	Hazardous Sub		bstances RQs			RQ		
Zinc (Powder)		1000 Lb.		RQ 454 kg final RQ				
, ,				RQ 1000 lb final RQ				
California Proposition 65This product does not contain any Proposition 65 chem			on 65 chemicals.					
U.S. State Right-to-Know Regulations (X" designates that the ingredients are listed)								
Chemical Name	New J	v Jersey Massach		usetts	setts Pennsylvania		Illinois	Rhode Island
Zinc (Powder)	X	X X			X			X
Graphite	X		X		X			X
Talc	X		X		X			X
Calcium Oxide	cium Oxide X X		X	X X			X	
<b>EPA Pesticide Registration Number</b>		Not appli	cable					

















#### **Section 16 - Other Information**

Last Revision Date:	07/02/2015	
Preparation Date:	07/07/2015	
Disclaimer/Statement of Liability:	The information contained herein is believed to be accurate but is	
	not warranted to be so. Data and calculations are based on	
	information furnished by the manufacturer of the product and	
	manufacturers of the components of the product. Users are	
	advised to confirm in advance of need that information is current,	
	applicable and suited to the circumstance of use. Vendor assumes	
	no responsibility for injury to vendee or third persons proximately	
	caused by the material if reasonable safety procedures are not	
	adhered to as stipulated in the data sheet. Furthermore, vendor	
	assumes no responsibility for injury caused by abnormal use of	
	this material even if reasonable safety procedures are followed.	
	Any questions regarding this product should be directed to the	
	manufacturer of the product as described in Section 1.	

Key to abbre	viations		
ACGIH	American Conference of Governmental Industrial	TWA	Time-Weighted Averages are based on 8h/day, 40h/week
	Hygiene		exposures
NIOSH	National Institute of Occupational Safety and	STEL	Short Term Exposure Limits are based on 15-minute
	Health		exposures
OSHA	Occupational Safety and Health Administration	STEV	Short Term Exposure Value
MSHA	Mine Safety and Health Administration	TWAEV	Time Weighted Average Exposure Values
MARPOL	International Convention for the Prevention of	IBC Code	International Bulk Chemical Code
73/78	Pollution from Ships,		
	1973, as modified by the Protocol of 1978		
	relating thereto, as amended.		
IMDG	International	CEPA	Canadian Environmental Protection Act
	Maritime Dangerous Goods		
WHMIS	Workplace Hazardous Materials Information	CERCLA	Comprehensive Environmental Response, Compensation,
	System		and Liability Act
SARA	Superfund Amendments and Reauthorization Act	TPQs	Threshold Planning Quantities
EPCRA RQ	Emergency Planning & Community Right-to-	PBT	Persistent Bioaccumulative Toxic
	Know Act Reportable Quantities		
N/A	Not Applicable	NDA	Not Data Available

















