

24/7 FLASHING BLINKERSTOP[®]

BlinkerStop[®] Flashing LED signs are edge-lit signs engineered to capture drivers' attention and increase roadway compliance with highly visible red LEDs.

- Proven to reduce blow-throughs by 52.9%
- Programmed to flash 24 hours a day, 7 days a week with Dusk 'til Dawn options available
- Solar or AC power options to work in any setting
- Lightweight system for simple installation
- MUTCD-compliant, made in the USA
- Ruggedized BlinkerStop[®] upgrade available that can withstand extreme conditions, including falling debris, heavy winds and plowed or blowing snow



POPULAR OPTIONS

Other options available upon request




17W SOLAR PANEL
14Ah BATTERY CAPACITY



13W SELF-CONTAINED
TOP-OF-POLE SOLAR CABINET
28Ah BATTERY CAPACITY



120VAC



FRONT

BACK

SIZE	GLOBAL ITEM
36"	B1504092

SYSTEM SPECIFICATIONS

SIGN LEGEND	R1-1
DIMMING	Variable based on photocell sensor input or 6V solar panel
LED TYPE	Red environmentally-sealed, high-power LED
LED LIFE EXPECTANCY	100,000 hours
VISIBILITY	Daytime: more than 1,000 feet Nighttime: more than 1 mile
ENCLOSED ALUMINUM CHANNELS	Protect wiring against inclement weather, tampering and vandalism
AUTONOMY	30+ days (when applicable)
OPERATING TEMPERATURE RANGE	-40°F to 122°F (-40°C to 50°C)
DIMENSIONS	24"W x 24"H x 1"D 30"W x 30"H x 1"D 36"W x 36"H x 1"D 48"W x 48"H x 1"D
WARRANTY	2 year limited solar panel warranty 3 year limited battery warranty 5 year limited system warranty



© 2023 Traffic and Parking Control Co., Inc.