



### Adjustable Spread Telescoping Beams

- Manufactured to exceed all ASME B30.20 and OSHA regulations.
- Painted safety yellow for increased visibility.
- **ALL** Spreader Beams shipped with proof load certification paperwork.
- Durable construction ideally suited to jobsite or warehouse use.
- Standard with swivel latch hooks. Top rigging not included - please call for pricing
- Made in U.S.A.
- Custom designs available - call for engineering.
- Minimum horizontal top rigging angle of 45°.
- Ideally suited for adding stability to critical lifts.



**SHOWN WITH OPTIONAL  
TOP RIGGING**

Telescoping Adjustable Spreader Beams						
Working Load Limit in Pounds*	Model Number Headroom (in) Weight (lbs)	Outside Spread (L) in Feet*				A (in) C (in) E (in)
		Min Max 4 - 6	Min Max 6 - 10	Min Max 8 - 14	Min Max 12 - 20	
4,000	<b>Part Number</b>	<b>12805</b>	<b>12822</b>	<b>12813</b>	<b>12829</b>	1.00
	HR =	5.37	5.12	5.12	5.12	0.50
	LBS =	80	120	155	235	0.89
10,000	<b>Part Number</b>	<b>12834</b>	<b>12842</b>	<b>12848</b>	<b>12853</b>	1.25
	HR =	6.53	6.28	6.28	6.28	0.75
	LBS =	130	190	250	365	1.08
20,000	<b>Part Number</b>	<b>12864</b>	<b>12872</b>	<b>12880</b>	<b>12885</b>	1.66
	HR =	7.63	7.63	7.63	7.63	1.00
	LBS =	185	265	345	505	1.31

\*Minimum horizontal top rigging angle is 45° on all fixed and adjustable spreaders. M&W recommends a minimum horizontal top rigging angle of 60°. Adjustable on 1" increments.

- Manufactured to exceed all ASME B30.20 and OSHA regulations.
- Painted safety yellow for increased visibility.
- ALL Spreader Beams shipped with proof load certification paperwork.
- Durable construction ideally suited to jobsite or warehouse use.
- Made in U.S.A.
- Custom designs available - call for engineering.
- ALL lifting equipment individually proof loaded per OSHA requirements.
- Minimum horizontal top rigging angle of 45°
- Ideally suited for adding stability to critical lifts.
- Beam only. Shackles supplied by others.



**SHOWN WITH  
OPTIONAL  
TOP RIGGING  
& SHACKLES**

Telescoping Adjustable Large Capacity Shackle End Spreader Beams						
Working Load Limit in Pounds*	Shackle Size	Model Number Headroom (in) Weight (lbs)	Outside Spread (L) in Feet*			
			Min Max 5'6" - 7'	Min Max 7 - 10	Min Max 10 - 14	Min Max 14 - 20
40,000	1-1/2" Top 1-1/2" Bottom	<b>Part Number</b>	<b>20127</b>	<b>20126</b>	<b>20125</b>	<b>20124</b>
		HR =	7.6	7.6	7.6	7.6
		LBS =	350	410	560	760
60,000	1-3/4" Top 1-3/4" Bottom	<b>Part Number</b>	<b>20132</b>	<b>20131</b>	<b>20130</b>	<b>20129</b>
		HR =	7.1	7.1	7.1	7.1
		LBS =	370	490	660	890
80,000	2" Top 2" Bottom	<b>Part Number</b>	<b>20137</b>	<b>20136</b>	<b>20135</b>	<b>20134</b>
		HR =	9.3	9.3	9.3	9.3
		LBS =	575	700	950	1,250
100,000	2" Top 2" Bottom	<b>Part Number</b>	<b>20142</b>	<b>20141</b>	<b>20140</b>	<b>20139</b>
		HR =	9.3	9.3	9.3	9.3
		LBS =	575	700	950	1,250

\*Minimum horizontal top rigging angle is 45° on all fixed and adjustable spreaders. M&W recommends a minimum horizontal top rigging angle of 60°. Adjustable on 6" increments.

