


**TWIN HOIST LIFTING BEAMS**

- Manufactured to exceed all ASME B30.20 and OSHA regulations.
  - Painted safety yellow for increased visibility.
  - **ALL** Lifting Beams proof loaded and shipped with certification paperwork.
  - Durable construction ideally suited to jobsite or warehouse use.
  - Quick and easy lifting of loads with two hoists. Lifting must be done within 5° of vertical.
  - Ideally suited to low headroom applications.
  - Alloy swivel hook bottom standard connection.
  - Made in U.S.A.
  - Custom designs available - call for engineering.
  - **ALL** lifting equipment individually proof loaded per OSHA requirements.
  - All dimensions in inches unless otherwise noted.
- ⚠ Prop 65 – See Page 100**



Working Load Limit in Pounds*	Part number Headroom Weight	Spread in Feet - L								A	B	C	D	E
		6	8	10	12	14	16	18	20					
4,000	<b>Part Number</b>	<b>16427</b>	<b>16428</b>	<b>16429</b>	<b>16430</b>	<b>16431</b>	<b>16432</b>	<b>16433</b>	<b>16434</b>	3.0	5.0	0.88	0.63	0.96
	HR=	15.10	16.10	16.10	17.10	18.10	18.10	19.10	20.10					
	Weight	140	191	260	320	560	640	765	1,055					
6,000	<b>Part Number</b>	<b>16435</b>	<b>16436</b>	<b>16437</b>	<b>16438</b>	<b>16439</b>	<b>16440</b>	<b>16441</b>	<b>16442</b>	3.0	5.0	1.00	0.63	1.08
	HR=	16.50	17.50	18.50	18.50	19.50	19.50	20.50	20.50					
	Weight	150	225	265	485	600	690	960	1,260					
10,000	<b>Part Number</b>	<b>16443</b>	<b>16444</b>	<b>16445</b>	<b>16446</b>	<b>16447</b>	<b>16448</b>	<b>16449</b>	<b>16450</b>	3.0	5.0	1.00	0.75	1.56
	HR=	22.31	22.31	22.31	23.31	23.31	23.31	25.31	25.31					
	Weight	300	380	470	670	920	1,040	1,005	1,305					
15,000	<b>Part Number</b>	<b>16451</b>	<b>16452</b>	<b>16453</b>	<b>16454</b>	<b>16455</b>	<b>16456</b>	<b>16457</b>	<b>16458</b>	4.0	7.0	1.00	0.75	2.17
	HR=	25.75	26.75	26.75	26.75	28.75	31.75	31.75	31.75					
	Weight	310	395	580	810	950	1,215	1,575	1,740					
20,000	<b>Part Number</b>	<b>16459</b>	<b>16460</b>	<b>16461</b>	<b>16462</b>	<b>16463</b>	<b>16464</b>			4.0	7.0	1.25	1.00	2.28
	HR=	27.53	27.53	29.53	32.53	32.53	32.53							
	Weight	370	585	725	975	1,565	1,770							

\* Call for specifications on larger sizes and capacities