

TACHIT®

Ben Clements and Sons, Inc.

We Offer Solutions for Productivity.

Model # AP65 Series: Hand-Held Label Applicators.

- Available in 3 widths (see chart below).
- Unique mechanical sensor adjusts the stroke of the trigger at the die-cut so only one label is applied with each pull of the trigger.
- Lightweight and fully portable.
- Soft pull trigger dispenses the label.
- Perfect for hand labeling of agricultural products, palletized goods and for use anywhere a portable label applicator is needed.
- Can dispense labels with a maximum label width of 3.93" (100 mm).
- For die-cut labels on a 1" core.
- For high production repetitive labeling applications.



	AP65-30:	AP65-60:	AP65-100:
Maximum Roll Diameter:	3.93" (100 mm)	3.93" (100 mm)	3.93" (100 mm)
Core Size:	1" (25.4 mm)	1" (25.4 mm)	1" (25.4 mm)
Maximum Liner Width:	1.20" (30 mm)	2.36" (60 mm)	3.93" (100 mm)
Minimum Liner Width:	.75" (19 mm)	1" (25 mm)	2.15" (55 mm)
Maximum Label Length:	2.36" (60 mm)	2.36" (60 mm)	2.36" (60 mm)
Minimum Label Length:	.78" (20 mm)	.78" (20 mm)	.78" (20 mm)
Weight:	11.2 OZ (318 g)	13.1 OZ (372 g)	15.0 OZ (425 g)

Ben Clements and Sons, In.