ICE MACHINE CLEANER



12/12/2022



1. Identification

1.1. Product identifier

Product Identity ICE MACHINE CLEANER

Alternate Names 90-351, Blended Formula, ICE MACHINE CLEANER

For Ice Machines- 16 oz

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use It is a most effective food grade liquid descaler to

remove scale and lime deposits from ice machines.

Read all precautions and instructions carefully before **Application Method**

and after use.

1.3. Details of the supplier of the safety data sheet

Company Name ComStar International Inc.

20-47 128th Street,

College Point, NY 11356

Telephone No. 718-445-7900

> 800-328-0142 Fax: 718-353-5998

1-800-424-9300 & 703-527-3887 CHEMTREC **Emergency 24 HR response No:**

Note: The CHEMTREC phone number is only for emergencies involving spills, leaks, fire, exposure, or

accident. Please direct all other inquiries to our customer service phone number.

2. Hazard(s) identification

2.1. Classification of the substance or mixture

Skin Irrit. 2; H315 Causes Skin Irritation

Eye Dam. 1; H318 Causes serious eye damage

2.2. Label elements

Using the Toxicity Data listed in section 11 and 12 the product is labeled as follows.



Warning

[HAZARD STATEMENT]

H314 Causes severe skin burns and eye damage.

H318 Causes serious eye damage.

[Prevention]:

P234 Keep only in original container

ICE MACHINE CLEANER SDS Revision Date:



12/12/2022

P264 Wash skin thoroughly after handling.

P270 Do not eat, drink, or smoke when using this product

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

[Response]:

P301 + P312 + P330 If swallowed: Call a poison center/ doctor if you feel unwell. Rinse mouth.

P301 + P330 + P331 If swallowed: Rinse mouth. Do not induce vomiting.

P303 + P361 + P353 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

P305 + P351 + P338 + P310 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/ doctor.

P363 Wash contaminated clothing before reuse.

P390 Absorb spillage to prevent material damage.

[Storage]:

P405 Store locked up.

P406 Store in corrosive resistant container with a resistant inner liner.

[Disposal]:

P501 Dispose of contents/ container to an approved waste disposal plant.

2.3. Hazards not otherwise classified (HNOC) or not covered by GHS

None

3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

Ingredient/Chemical Designations	Weight %	GHS Classification	Notes
PHOSPHORIC ACID CAS#: 7664-38-2	>15	Acute Tox. 4 (Oral), H302 Skin Corr. 1B, H314	
SURFACTANT PACKAGE CAS#: 9016-45-9	>10	Acute toxicity, 4 (Oral), H302 Serious eye damage,1; H318 Acute aquatic toxicity,1; H400	

In accordance with paragraph (i) of §1910.1200, the specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret.

4. First aid measures

4.1. Description of first aid measures

General First aiders need to protect themselves. Show this material safety data sheet to the doctor

in attendance.

Inhalation After inhalation: fresh air. Call in physician.

Page 2 of 11

^{*}The full texts of the phrases are shown in Section 16.

ICE MACHINE CLEANER

SDS Revision Date:





Eyes After eye contact: rinse out with plenty of water. Immediately call-in ophthalmologist.

Remove contact lenses.

Skin In case of skin contact: Take off immediately all contaminated clothing. Rinse skin with

water/ shower. Call a physician immediately.

Ingestion After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of

perforation). Call a physician immediately. Do not attempt to neutralize.

4.2. Most important symptoms and effects, both acute and delayed

Overview The most important known symptoms and effects are described in the labelling (see section

2.2) and/or in section 11

4.3 Indication of any immediate medical attention and special treatment needed

No data available

5. Fire-fighting measures

5.1. Extinguishing media

Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical, or carbon dioxide. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given. For this substance/mixture no limitations of extinguishing agents are given.

5.2. Special hazards arising from the substance or mixture

Oxides of phosphorus

Not combustible.

Ambient fire may liberate hazardous vapours.

5.3. Advice for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

5.4. Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

ERG Guide No. ---

6. Accidental release measures

6.1. Personal precautions, protective equipment, and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert. For personal protection see section 8.

6.2. Environmental precautions

ICE MACHINE CLEANER
SDS Revision Date:

12/12/2022



Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

6.4 Reference to other section

For disposal see section 13.

7. Handling and storage

7.1. Precautions for safe handling

For precautions see section 2.2.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions

No metal containers.

Storage class Storage class (TRGS 510): 8B: Non-combustible, corrosive hazardous materials

7.3. Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated

8. Exposure controls and personal protection

8.1. Control parameters

Exposure

Component	CAS-No.	Value	Control parameters	Basis
phosphoric acid	7664-38-2	TWA	1 mg/m3	USA. ACGIH Threshold Limit Values (TLV)
		STEL	3 mg/m3	USA. ACGIH Threshold Limit Values (TLV)
		TWA	1 mg/m3	USA. NIOSH Recommended Exposure Limits
		ST	3 mg/m3	USA. NIOSH Recommended Exposure Limits
		TWA	1 mg/m3	USA. Occupational Exposure Limits (OSHA) - Table Z-1 Limits for Air Contaminants
		PEL	1 mg/m3	California permissible exposure limits for chemical contaminants (Title 8, Article 107)
		STEL	3 mg/m3	California permissible exposure limits for chemical contaminants (Title 8, Article 107)

ICE MACHINE CLEANER SDS Revision Date:



12/12/2022

8.2 Exposure controls

Appropriate engineering controls

Immediately change contaminated clothing. Apply preventive skin protection. Wash hands and face after working with substance.

Personal protective equipment

Eye/face protection

Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU). Tightly fitting safety goggles

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

Full contact

Material: Nitrile rubber Minimum layer thickness: 0.11 mm Break through time: 480 min Material tested:Dermatril® (KCL 740 / Aldrich Z677272, Size M)

Splash contact

Material: Nitrile rubber Minimum layer thickness: 0.11 mm Break through time: 480 min Material tested:Dermatril® (KCL 740 / Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374 If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the EC approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

protective clothing

Respiratory protection

required when vapours/aerosols are generated.

Our recommendations on filtering respiratory protection are based on the following standards: DIN EN 143, DIN 14387 and other accompanying standards relating to the used respiratory protection system.

Control of environmental exposure

Do not let product enter drains.

9. Physical and chemical properties

AppearanceGreen LiquidOdorNo data availableOdor thresholdNo data available

ICE MACHINE CLEANER

SDS Revision Date:

12/12/2022



pH No data available

Melting point / freezing point No data available

Initial boiling point and boiling range No data available

Flash Point No data available

Evaporation rate (Ether = 1) No data available

Flammability (solid, gas) No data available

Upper/lower flammability or explosive limits No data available

No data available

Vapor pressure (Pa) No data available

Vapor pressure (Pa)No data availableVapor DensityNot MeasuredDensity1.685 g/cm3Relative densityNo data availableSolubility in WaterNo data availablePartition coefficient n-octanol/water (Log Kow)No data availableAuto-ignition temperatureNot applicableDecomposition temperatureNo data available

Explosive properties Not classified as explosive.

Oxidizing properties none

9.2. Other information

No other relevant information.

10. Stability and reactivity

No data available

10.1. Reactivity

Viscosity (cSt)

No data available

10.2. Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3. Possibility of hazardous reactions

No data available.

10.4. Conditions to avoid

no information available

10.5. Incompatible materials

Strong bases, Powdered metals

10.6. Hazardous decomposition products

In the event of fire: see section 5

11. Toxicological information

11.1 Information on toxicological effects

ICE MACHINE CLEANER

SDS Revision Date:

12/12/2022



Mixture

Acute toxicity

Oral: No data available Acute toxicity estimate Oral - 1,471 mg/kg (Calculation method) Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Inhalation: No data available

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages: damage of respiratory

tract

Dermal:

No data available

Skin corrosion/irritation

Mixture causes burns.

Serious eye damage/eye irritation

Mixture causes serious eye damage. Risk of blindness!

Respiratory or skin sensitization

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

IARC: No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC.

NTP: No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

OSHA: No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

Reproductive toxicity

No data available

Specific target organ toxicity - single exposure

No data available

Specific target organ toxicity - repeated exposure

No data available

Aspiration hazard

No data available

11.2 Additional Information

Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin., spasm, inflammation and edema of the larynx, spasm, inflammation and edema of the bronchi,

ICE MACHINE CLEANER







pneumonitis, pulmonary edema, burning sensation, Cough, wheezing, laryngitis, Shortness of breath, Headache, Nausea Other dangerous properties cannot be excluded. Handle in accordance with good industrial hygiene and safety practice.

Stomach - Irregularities - Based on Human Evidence

Components phosphoric acid Acute toxicity

LD50 Oral - Rat - 1,250 mg/kg

Remarks: Lungs, Thorax, or Respiration: Acute pulmonary edema.

Liver: Changes in liver weight. (RTECS)

Inhalation: No data available Dermal: No data available

Skin corrosion/irritation

Skin - Rabbit

Result: Causes burns. - 24 h

Remarks: (ECHA) (Regulation (EC) No 1272/2008, Annex VI)

Serious eye damage/eye irritation

Causes serious eye damage.

Respiratory or skin sensitization

No data available

Germ cell mutagenicity

Test Type: Ames test

Test system: Escherichia coli/Salmonella typhimurium

Result: negative

Test Type: Mutagenicity (mammal cell test): chromosome aberration.

Test system: Human lymphocytes

Result: negative

Test Type: In vitro mammalian cell gene mutation test

Test system: mouse lymphoma cells

Result: negative

Carcinogenicity

No data available

Reproductive toxicity

No data available

Specific target organ toxicity - single exposure

No data available

Specific target organ toxicity - repeated exposure

No data available

Aspiration hazard

No data available

ICE MACHINE CLEANER
SDS Revision Date:

12/12/2022



12. Ecological information

12.1. Toxicity

Mixture

No data available

12.2. Persistence and degradability

No data available

12.3. Bioaccumulative potential

No data available

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

12.6 Endocrine disrupting properties

No data available

12.7. Other adverse effects

No data available.

Components

phosphoric acid

Toxicity to daphnia and other aquatic invertebrates static test EC50 - Daphnia magna (Water flea) - > 100 mg/l - 48 h (OECD Test Guideline 202)

Toxicity to algae static test ErC50 - Desmodesmus subspicatus (green algae) - >100 mg/l - 72 h (OECD Test Guideline 201)

Toxicity to bacteria static test EC50 - activated sludge - > 1,000 mg/l - 3 h (OECD Test Guideline 209)

13. Disposal considerations

13.1. Waste treatment methods

Product Waste material must be disposed of in accordance with the national and local regulations. Leave chemicals in original containers. No mixing with other waste. Handle uncleaned containers like the product itself. See www.retrologistik.com for processes regarding the return of chemicals and containers, or contact us there if you have further questions.

14. Transport information

DOT (Domestic Surface Transportation)

IMO / IMDG (Ocean Transportation) ICAO/IATA

14.1. UN UN 3264 **number**

UN 3264

UN 3264

ICE MACHINE CLEANER

SDS Revision Date:



12/12/2022

14.2. UN proper UN 3264, Phosphoric Acid **shipping name** Solution, Class 8, II (Each not

exceeding 1 L capacity),

14.3. Transport DOT Hazard Class: 8

hazard class(es)

14.4. Packing II

group

14.5. Environmental hazards

IMDG Marine Pollutant: No

14.6. Special precautions for user

No further information

UN 3264, Phosphoric Acid Solution, Class 8, II (Each not exceeding 1 L capacity),

IMDG: 8 Sub Class:

Ш

II

UN 3264, Phosphoric Acid Solution, Class 8, II (Each not exceeding 1 L capacity),

Air Class: 8

15. Regulatory information

SARA 302 Components

This material does not contain any components with a section 302 EHS TPQ.

SARA 313 Components

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 311/312 Hazards

Acute Health Hazard, Chronic Health Hazard

Massachusetts Right to Know Components

No components are subject to the Massachusetts Right to Know Act.


16. Other information

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

The opinions expressed are those of qualified experts within ComStar International Inc. We believe that the information contained is current as of the date of the Material Safety Data Sheet. Since the use of this information and of these opinions and the conditions of the use of the product are not within the control of ComStar International Inc., it is the user's obligation to determine the conditions of safe use of the product.

End of Document

ICE MACHINE CLEANER



ComStar

12/12/2022