

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



1. Identification

1.1. Product identifier

Product Identity

POWER CLEAN

Alternate Names

55-032, 55-033, Blended Formula, POWER CLEAN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use

See Technical Data Sheet.

Application Method

See Technical Data Sheet.

1.3. Details of the supplier of the safety data sheet

Company Name

ComStar International Inc.
20-45 128th Street,
College Point, NY 11356

Telephone No.

718-445-7900
800-328-0142
Fax: 718-353-5998

2. Hazard(s) identification

2.1. Classification of the substance or mixture

Skin Irrit. 2; H315 Cause skin irritation

2.2. Label elements

Using the Toxicity Data listed in section 11 and 12 the product is labeled as follows.



Warning

[Prevention]:

P261 Avoid breathing dust / fume / gas / mist / vapors / spray.

P271 Use only outdoors or in a well-ventilated area.

[Response]:

P312: Call a POISON CENTER or doctor / physician if you feel unwell.

P340 Remove victim to fresh air and keep at rest in a position comfortable for breathing.

[Storage]:

No GHS storage statements

[Disposal]:

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



No GHS disposal statements

3. Composition/information on ingredients

This product contains the following substances that present a hazard within the meaning of the relevant State and Federal Hazardous Substances regulations.

| Ingredient/Chemical Designations | Weight % | GHS Classification | Notes |
|---------------------------------------------------------|----------|--------------------|--------|
| DIPROPYLENE GLYCOL MONOMETHYL ETHER CAS#: 34590-94-8 | >15 | Eye Irrit. 2B | [1][2] |
| SURFACTANT CAS#: 68648-81-7 | <15 | Not Classified | [1] |
| DEFOAMER CAS#: Not Est | <5 | Not Classified | [1] |
| SODIUM GLUCONATE CAS#: 527-07-01 | >10 | Not Classified | [1] |
| Water & Other Non-hazardous compounds CAS#: N/A | Balance | Not Classified | [1] |

In accordance with paragraph (i) of §1910.1200, the specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret.

[1] Substance classified with a health or environmental hazard.

[2] Substance with a workplace exposure limit.

[3] PBT-substance or vPvB-substance.

*The full texts of the phrases are shown in Section 16.

4. First aid measures

4.1. Description of first aid measures

| | |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| General | In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person. |
| Inhalation | Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped, give artificial respiration. If unconscious place in the recovery position and obtain immediate medical attention. Give nothing by mouth. |
| Eyes | Irrigate copiously with clean water for at least 15 minutes, holding the eyelids apart and seek medical attention. |
| Skin | Remove contaminated clothing. Wash skin thoroughly with soap and water or use a recognized skin cleanser. |
| Ingestion | If swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting. |

4.2. Most important symptoms and effects, both acute and delayed

| | |
|-------------------|---------------------------------------------------------------------------|
| Overview | No specific symptom data available. See section 2 for further details. |
| Inhalation | Harmful if inhaled. |

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



5. Fire-fighting measures

5.1. Extinguishing media

Water fog, CO₂, dry chemical, universal foams

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition: No hazardous decomposition data available.

Avoid breathing dust / fume / gas / mist / vapors / spray.

5.3. Advice for fire-fighters

Wear self-contained breathing apparatus and protective clothing.

ERG Guide No. ---

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Put on appropriate personal protective equipment (see section 8).

6.2. Environmental precautions

Do not allow spills to enter drains or waterways.

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

6.3. Methods and material for containment and cleaning up

Absorb spill with vermiculite or other inert material, then place in a container for chemical waste.

For Large Spills: Flush spill area with water spray. Prevent run-off from entering drains, sewers, or streams, collect run-off.

7. Handling and storage

7.1. Precautions for safe handling

Avoid contact with eyes and skin. Wash thoroughly after handling. Do not breathe vapors or fumes.

Prevention of Fire and Explosion: Keep from contact with oxidizing materials, alkalis and acids. Store away from heat, sunlight and moisture.

See section 2 for further details. - [Prevention]:

7.2. Conditions for safe storage, including any incompatibilities

Handle containers carefully to prevent damage and spillage.

Incompatible materials: Oxidizing agents, alkali metals

See section 2 for further details. - [Storage]:

7.3. Specific end use(s)

No data available.

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



8. Exposure controls and personal protection

8.1. Control parameters

Exposure

| CAS No. | Ingredient | Source | Value |
|------------|---------------------------------------|----------|---------------------------------------------------------------------------------|
| 34590-94-8 | DIPROPYLENE GLYCOL MONOMETHYL ETHER | OSHA | 100 ppm |
| | | ACGIH | 100 ppm |
| | | NIOSH | TWA 100 ppm (600 mg/m ³) ST 150 ppm (900 mg/m ³) [skin] |
| | | Supplier | No Established Limit |
| 68648-81-7 | SURFACTANT | OSHA | No Established Limit |
| | | ACGIH | No Established Limit |
| | | NIOSH | No Established Limit |
| | | Supplier | No Established Limit |
| Not Est | DEFOAMER | OSHA | No Established Limit |
| | | ACGIH | No Established Limit |
| | | NIOSH | No Established Limit |
| | | Supplier | No Established Limit |
| 527-07-01 | SODIUM GLUCONATE | OSHA | No Established Limit |
| | | ACGIH | No Established Limit |
| | | NIOSH | No Established Limit |
| | | Supplier | No Established Limit |
| N/A | Water & Other Non-hazardous compounds | OSHA | No Established Limit |
| | | ACGIH | No Established Limit |
| | | NIOSH | No Established Limit |
| | | Supplier | No Established Limit |

Carcinogen Data

| CAS No. | Ingredient | Source | Value |
|------------|-------------------------------------|--------|--------------------------------------------------------------------|
| 34590-94-8 | DIPROPYLENE GLYCOL MONOMETHYL ETHER | OSHA | Select Carcinogen: No |
| | | NTP | Known: No; Suspected: No |
| | | IARC | Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No; |
| 68648-81-7 | SURFACTANT | OSHA | Select Carcinogen: No |
| | | NTP | Known: No; Suspected: No |
| | | IARC | Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No; |
| Not Est | DEFOAMER | OSHA | Select Carcinogen: No |
| | | NTP | Known: No; Suspected: No |
| | | IARC | Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No; |
| 527-07-01 | SODIUM GLUCONATE | OSHA | Select Carcinogen: No |
| | | NTP | Known: No; Suspected: No |
| | | IARC | Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No; |

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



| | | | |
|-----|---------------------------------------|------|--------------------------------------------------------------------|
| N/A | Water & Other Non-hazardous compounds | OSHA | Select Carcinogen: No |
| | | NTP | Known: No; Suspected: No |
| | | IARC | Group 1: No; Group 2a: No; Group 2b: No; Group 3: No; Group 4: No; |

8.2. Exposure controls

Respiratory

If engineering controls do not maintain airborne concentrations to an acceptable level, a NIOSH approved respirator must be worn.

Respirator Type: Organic vapor. If respirators are used, a program should be instituted to assure Compliance with OSHA Standard 29 CFR 1910.134.

Eyes

Safety glasses with side shields, goggles or face shield are recommended.

Skin

Wear overalls to keep skin contact to a minimum.

Engineering Controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. Supplementary local exhaust ventilation, closed systems, or respiratory protection may be needed in special circumstances such as poorly ventilated spaces, evaporation from large surfaces, spraying, heating, etc. Recommended Decontamination Facilities: Eye bath, washing facilities.

Other Work Practices

Use good personal hygiene practices. Wash hands before eating, drinking, smoking or using toilet. Promptly remove soiled clothing and wash thoroughly before reuse.

See section 2 for further details. - [Prevention]:

9. Physical and chemical properties

| | |
|-------------------------------------------------|----------------------------------------------------------------------------------------------|
| Appearance | Green Liquid |
| Odor | Slight |
| Odor threshold | Not Measured |
| pH | 12 pH |
| Melting point / freezing point | Not Measured |
| Initial boiling point and boiling range | < 200 F |
| Flash Point | None |
| Evaporation rate (Ether = 1) | Not Measured |
| Flammability (solid, gas) | Not Applicable |
| Upper/lower flammability or explosive limits | Lower Explosive Limit: 135C(275F): NA Upper Explosive Limit: 199C(390F): NA |
| Vapor pressure (Pa) | 6 mmHg (at 70 F) |
| Vapor Density | Not Measured |
| Specific Gravity | < 2 (H2O = 1) |
| Solubility in Water | Complete |
| Partition coefficient n-octanol/water (Log Kow) | Not Measured |
| Auto-ignition temperature | (ASTM D 2155): NA |
| Decomposition temperature | Not Measured |

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



Viscosity (cSt) 25C/77F: NA
Volatiles (% by weight) NA
Octanol/Water Partition Coefficient NA

9.2. Other information

No other relevant information.

10. Stability and reactivity

10.1. Reactivity

Hazardous Polymerization will not occur.

10.2. Chemical stability

Stable under normal circumstances.

10.3. Possibility of hazardous reactions

No data available.

10.4. Conditions to avoid

No data available.

10.5. Incompatible materials

Strong Oxidizers

10.6. Hazardous decomposition products

No hazardous decomposition data available.

11. Toxicological information

Acute toxicity

| Ingredient | Oral LD50, mg/kg | Skin LD50, mg/kg | Inhalation Vapor LC50, mg/L/4hr | Inhalation Dust/Mist LC50, mg/L/4hr | Inhalation Gas LC50, ppm |
|--------------------------------------------------|-------------------|-------------------|---------------------------------|-------------------------------------|--------------------------|
| DIPROPYLENE GLYCOL MONOMETHYL ETHER (34590-94-8) | 5230 mg/kg Rat | >13,000 mg/kg | 500 ppm | No data available | No data available |
| SURFACTANT (68648-81-7) | No data available | No data available | No data available | No data available | No data available |
| DEFOAMER (Not Est) | No data available | No data available | No data available | No data available | No data available |
| SODIUM GLUCONATE (527-07-01) | No data available | No data available | No data available | No data available | No data available |
| Water & Other Non-hazardous compounds (N/A) | No data available | No data available | No data available | No data available | No data available |

Note: When no route specific LD50 data is available for an acute toxin, the converted acute toxicity point estimate was used in the calculation of the product's ATE (Acute Toxicity Estimate).

| Classification | Category | Hazard Description |
|-----------------------------|----------|--------------------|
| Acute toxicity (oral) | --- | Not Applicable |
| Acute toxicity (dermal) | --- | Not Applicable |
| Acute toxicity (inhalation) | --- | Not Applicable |

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



| | | |
|-------------------------------|-----|----------------|
| Skin corrosion/irritation | --- | Not Applicable |
| Serious eye damage/irritation | --- | Not Applicable |
| Respiratory sensitization | --- | Not Applicable |
| Skin sensitization | --- | Not Applicable |
| Germ cell mutagenicity | --- | Not Applicable |
| Carcinogenicity | --- | Not Applicable |
| Reproductive toxicity | --- | Not Applicable |
| STOT-single exposure | --- | Not Applicable |
| STOT-repeated exposure | --- | Not Applicable |
| Aspiration hazard | --- | Not Applicable |

12. Ecological information

12.1. Toxicity

No additional information provided for this product. See Section 3 for chemical specific data.

Aquatic Ecotoxicity

| Ingredient | 96 hr. LC50 fish, mg/l | 48 hr. EC50 crustacea, mg/l | ErC50 algae, mg/l |
|--------------------------------------------------|------------------------------|-----------------------------|-------------------|
| DIPROPYLENE GLYCOL MONOMETHYL ETHER (34590-94-8) | >10,000, Pimephales promelas | 1919, Daphnia | Not Available |
| SURFACTANT (68648-81-7) | Not Available | Not Available | Not Available |
| DEFOAMER (Not Est) | Not Available | Not Available | Not Available |
| SODIUM GLUCONATE (527-07-01) | Not Available | Not Available | Not Available |
| Water & Other Non-hazardous compounds (N/A) | Not Available | Not Available | Not Available |

12.2. Persistence and degradability

There is no data available on the preparation itself.

12.3. Bioaccumulative potential

Not Measured

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This product contains no PBT/vPvB chemicals.

12.6. Other adverse effects

No data available.

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



13. Disposal considerations

13.1. Waste treatment methods

Observe all federal, state and local regulations when disposing of this substance.

14. Transport information

| | DOT (Domestic Surface Transportation) | IMO / IMDG (Ocean Transportation) | ICAO/IATA |
|-------------------------------------------|----------------------------------------------|-----------------------------------------------------------------|----------------------------------|
| 14.1. UN number | Not Applicable | Not Regulated | Not Regulated |
| 14.2. UN proper shipping name | Not Regulated | Not Regulated | Not Regulated |
| 14.3. Transport hazard class(es) | DOT Hazard Class: Not Applicable | IMDG: Not Applicable Sub Class: Not Applicable | Air Class: Not Applicable |
| 14.4. Packing group | Not Applicable | Not Applicable | Not Applicable |
| 14.5. Environmental hazards | | | |
| IMDG | Marine Pollutant: No | | |
| 14.6. Special precautions for user | No further information | | |

15. Regulatory information

| | |
|-------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Regulatory Overview | The regulatory data in Section 15 is not intended to be all-inclusive, only selected regulations are represented. |
| Toxic Substance Control Act (TSCA) | All components of this material are either listed or exempt from listing on the TSCA Inventory. |
| WHMIS Classification | Not Regulated |
| US EPA Tier II Hazards | Fire: No Sudden Release of Pressure: No Reactive: No Immediate (Acute): No Delayed (Chronic): No |

EPCRA 311/312 Chemicals and RQs:

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

EPCRA 302 Extremely Hazardous:

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

EPCRA 313 Extremely Hazardous:

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

Proposition 65 - Carcinogens (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

Safety Data Sheet

POWER CLEAN

SDS Revision Date:

07/01/2018



Proposition 65 - Developmental Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

Proposition 65 - Female Repro Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

Proposition 65 - Male Repro Toxins (>0.0%):

To the best of our knowledge, there are no chemicals at levels which require reporting under this statute.

New Jersey RTK Substances (>1%):

DIPROPYLENE GLYCOL MONOMETHYL ETHER

Pennsylvania RTK Substances (>1%):

16. Other information

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantee or warranty of any kind, expressed or implied, is made with respect to the information contained herein. We accept no responsibility and disclaim all liability for any harmful effects which may be caused by exposure to our products. Customers/users of this product must comply with all applicable health and safety laws, regulations, and orders.

This is the first version in the GHS SDS format. Listings of changes from previous versions in other formats are not applicable.

The opinions expressed are those of qualified experts within ComStar International Inc. We believe that the information contained is current as of the date of the Safety Data Sheet. Since the use of this information and of these opinions and the conditions of the use of the product are not within the control of ComStar International Inc., it is the user's obligation to determine the conditions of safe use of the product.

End of Document