



SAFETY DATA SHEET



1. Product and Company Identification

Product identifier	Povidone Iodine Pads and Swabsticks	SDS 0054
Other means of identification	Not available	
Recommended use	Antiseptic	
Recommended restrictions	For Professional and Hospital Use	
Manufacturer	Professional Disposables International, Inc Two Nice-Pak Park, Orangeburg, NY 10962-1376 or Distributed By: Professional Disposables International, LTD Vaughan, Ontario L4L 4K9 Canada Phone: (USA) 1-845-365-1700 (M-F 9am - 5pm) Phone: (CANADA) 1-800-263-7067 Emergency Phone: 1-800-999-6423	

2. Hazards Identification

Physical hazards	Not classified.	
Health hazards	Serious eye damage/eye irritation	Category 2B
Environmental hazards	Not determined.	
OSHA defined hazards	None additional.	
Label elements		
Hazard symbol	None.	
Signal word	Warning	
Hazard statement	Causes eye irritation.	
Precautionary statement		
Prevention	Wash thoroughly after handling.	
Response	If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.	
Storage	Store away from incompatible materials.	
Disposal	Dispose of waste and residues in accordance with local authority requirements.	
Hazard(s) not otherwise classified (HNOC)	None known.	
Supplemental information	Not applicable.	

3. Composition/Information on Ingredients

Mixture

Chemical name	Common name and synonyms	CAS number	%
2-Pyrrolidinone, 1-ethenyl-, homopolymer, compound with iodine		25655-41-8	7 - 13

Composition comments	The exact % concentration of composition has been withheld as a trade secret in accordance with paragraph (i) of the OSHA HCS 1910.1200. Inactive Ingredients: Water, Sodium Hydroxide
-----------------------------	---

4. First Aid Measures

Inhalation	Not a normal route of exposure. If symptoms develop move victim to fresh air. If symptoms persist, obtain medical attention.
Skin contact	In case of skin irritation, discontinue use of product.
Eye contact	Rinse cautiously with water for several minutes. Remove contact lenses, if applicable, and continue flushing for 15 minutes. Obtain medical attention if irritation develops or persists.
Ingestion	Not a normal route of exposure. Obtain medical attention or call a Poison Center right away.
Most important symptoms/effects, acute and delayed	Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Indication of immediate medical attention and special treatment needed	Treat patient symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. If you feel unwell, seek medical advice (show the label where possible). Show this safety data sheet to the doctor in attendance. Avoid contact with eyes.

5. Fire Fighting Measures

Suitable extinguishing media	Treat for surrounding material.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Firefighters should wear a self-contained breathing apparatus.
Special protective equipment and precautions for firefighters	Firefighters should wear full protective clothing including self contained breathing apparatus.
Fire-fighting equipment/instructions	In the event of fire, cool product with water spray.
Specific methods	Cool product exposed to flames with water until well after the fire is out.
General fire hazards	No unusual fire or explosion hazards noted.
Hazardous combustion products	May include and are not limited to: Oxides of carbon. Oxides of nitrogen. Iodine.
Explosion data	
Sensitivity to mechanical impact	Not available.
Sensitivity to static discharge	Not available.

6. Accidental Release Measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate protective equipment and clothing during clean-up. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Pick up and discard. Prevent entry into waterways, sewers or confined areas. For waste disposal, see Section 13 of the SDS.
Environmental precautions	Do not discharge into lakes, streams, ponds or public waters.

7. Handling and Storage

Precautions for safe handling	Avoid contact with eyes. Use good industrial hygiene practices in handling this material. Use according to package label instructions.
Conditions for safe storage, including any incompatibilities	Store at room temperature and avoid excess heat. Store away from incompatible materials (see Section 10 of the SDS). Keep out of reach of children.

8. Exposure Controls/Personal Protection

Occupational exposure limits	No exposure limits noted for ingredient(s).
Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	This material does not have established exposure limits.
Appropriate engineering controls	Provide eyewash station.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Follow standard industrial hygiene practices.
Skin protection	
Hand protection	Follow standard industrial hygiene practices.
Other	As required by employer code.
Respiratory protection	Where exposure guideline levels may be exceeded, use an approved NIOSH respirator.
Thermal hazards	Not available.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and immediately after handling the product. When using do not eat or drink.

9. Physical and Chemical Properties

Appearance	Liquid saturated on pad / Swabstick saturated with liquid
Physical state	Solid.

Form	Solid.
Color	Yellow to Dark reddish brown
Odor	iodine
Odor threshold	Not available.
pH	Not available
Melting point/freezing point	Not available.
Initial boiling point and boiling range	207 °F (97.22 °C)
Pour point	Not available.
Specific gravity	0.877 (liquid)
Partition coefficient (n-octanol/water)	Not available
Flash point	Not available
Evaporation rate	Not available
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available
Flammability limit - upper (%)	Not available
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available
Relative density	Not available.
Solubility(ies)	Pad is not soluble/Stick is not soluble
Auto-ignition temperature	Not available
Decomposition temperature	Not available.
Viscosity	Not available.

10. Stability and Reactivity

Reactivity	May react with incompatible materials.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Chemical stability	Stable under recommended storage conditions.
Conditions to avoid	Do not mix with other chemicals. Contact with incompatible materials.
Incompatible materials	Caustics. Oxidizers. Reducing agents.
Hazardous decomposition products	May include and are not limited to: Oxides of carbon. Oxides of nitrogen. Iodine.

11. Toxicological Information

Routes of exposure	Eye, Skin contact, Skin absorption, Inhalation, Ingestion.
Information on likely routes of exposure	
Ingestion	Health injuries are not known or expected under normal use.
Inhalation	Health injuries are not known or expected under normal use.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	May be irritating to eyes.
Symptoms related to the physical, chemical and toxicological characteristics	Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Information on toxicological effects	
Acute toxicity	

Components	Species	Test Results
2-Pyrrolidinone, 1-ethenyl-, homopolymer, compound with iodine (CAS 25655-41-8)		
Acute		
<i>Inhalation</i>		
LC50	Not available	
<i>Oral</i>		
LD50	Mouse	8100 mg/kg
Skin corrosion/irritation	In case of skin irritation, discontinue use of the product. Topical application of povidone-iodine elevates serum concentrations of iodine.	
Exposure minutes	Not available.	
Erythema value	Not available.	
Oedema value	Not available.	
Serious eye damage/eye irritation	May cause irritation.	
Corneal opacity value	Not available.	
Iris lesion value	Not available.	
Conjunctival reddening value	Not available.	
Conjunctival oedema value	Not available.	
Recover days	Not available.	
Respiratory or skin sensitization		
Respiratory sensitization	Not available.	
Skin sensitization	This product is not expected to cause skin sensitization.	
Germ cell mutagenicity	The finished product is not expected to have chronic health effects.	
Mutagenicity	The finished product is not expected to have chronic health effects.	
Carcinogenicity	Not classified or listed by IARC, NTP, OSHA and ACGIH.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Teratogenicity	The finished product is not expected to have chronic health effects.	
Specific target organ toxicity - single exposure	Not classified.	
Specific target organ toxicity - repeated exposure	Not classified.	
Aspiration hazard	Not classified.	
Chronic effects	Chronic ingestion of iodides may produce 'iodism' which is characterized by skin rash, nasal discharge, sneezing, fever, headaches, weakness, anemia and loss of weight.	
Further information	Not available.	
Name of Toxicologically Synergistic Products	Not available.	

12. Ecological Information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
Persistence and degradability	No data is available on the degradability of this product.
Bioaccumulative potential	No data available.
Mobility in soil	No data available.
Mobility in general	Not available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal Considerations

Disposal instructions	Dispose of contents/container in accordance with local/regional/national/international regulations. Discard after single use.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	Assign as required.
Waste from residues / unused products	Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Since emptied packages may retain product residue, follow label warnings even after container is emptied.

14. Transport Information

U.S. Department of Transportation (DOT)

Not regulated as dangerous goods.

Transportation of Dangerous Goods (TDG - Canada)

Not regulated as dangerous goods.

15. Regulatory Information

Canadian federal regulations This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

NPN 00489948 – Pad / NPN 00489964 - Swabstick

WHMIS status Exempt

WHMIS classification Exempt - Registered product - (NPN see above)

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)
Not regulated.

Other federal regulations

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

US state regulations This product does not contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

US - California Proposition 65 - Carcinogens & Reproductive Toxicity (CRT): Listed substance

Not listed.

US. Massachusetts RTK - Substance List

Not regulated.

US. Pennsylvania RTK - Hazardous Substances

Not regulated.

US. Rhode Island RTK

Not regulated.

Inventory status


Country(s) or region	Inventory name	On inventory (yes/no)*
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

16. Other Information

LEGEND	
Severe	4
Serious	3
Moderate	2
Slight	1
Minimal	0

HEALTH	/ 2
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	X



Disclaimer

The information in the sheet was written based on the best knowledge and experience currently available. Information contained herein was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the requirements of all applicable legislation and regulatory instruments. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this document.

Issue date

24-February-2015

Effective date

15-February-2015

Expiry date

15-February-2018

Further information

For any questions surrounding this SDS, please contact the supplier/manufacturer listed on the first page of the document.

Revision 0.

Bulk Liquid # 4BS41101.

Prepared by

Dell Tech Laboratories, Ltd. Phone: (519) 858-5021

Other information

This Safety Data Sheet was prepared to comply with the current OSHA Hazard Communication Standard (HCS) adoption of the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

This SDS conforms to the ANSI Z400.1/Z129.1-2010 Standard.

This document was created with Win2PDF available at <http://www.win2pdf.com>.
The unregistered version of Win2PDF is for evaluation or non-commercial use only.
This page will not be added after purchasing Win2PDF.