



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

SECTION 1: PRODUCT IDENTIFICATION

Product: Alcohol Prep Pads

Product Label Name: Dukal Alcohol Prep Pads (private label included)

Company Name and Address: Dukal Corporation
2 Fleetwood Court
Ronkonkoma, NY 11779

Emergency Telephone Number: 631-656-3800

Recommended use: This product is intended for use as a skin antiseptic. It is for external use only.

SECTION 2: HAZARDOUS IDENTIFICATION

Hazard Class/Category: Flammable Liquid – 3
Eye Irritation – 2B

Hazard Symbol:



Signal Word: Warning

Hazard Statements: Flammable liquid and vapor. (H226)
Causes eye irritation. (H320)

Precautionary statements:

General: Keep out of reach of children. (P102)

Eyes: IF IN EYES: Rinse cautiously with water for several minutes.
If eye irritation persists: Get medical advice/attention.
(P305+P338) (P337+P313)

SECTION 3: INFORMATION ON INGREDIENTS

Component Name	CAS #	Concentration	R Phrase
Isopropyl Alcohol	67-63-0	>60%	R11



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

SECTION 4: FIRST-AID MEASURES

Emergency first aid procedures by route of exposure:

Inhalation: If symptoms are experienced, remove source of contamination or move victim to fresh air. If affected person is not breathing, apply artificial respiration. If breathing is difficult, give oxygen. Seek medical attention.

Ingestion: Do not induce vomiting. If the material is swallowed have victim drink 1-3 glasses of water to dilute stomach contents. Seek medical attention or advice.

Skin: If irritation is experienced, rinse with water. If irritation persists, seek medical attention.

Eyes: Rinse eyes with water for 15 minutes holding the eye open. Seek medical attention if irritation persists

SECTION 5: FIRE-FIGHTING MEASURES

Flammability Classification: Flammable Liquid IB Extinguishing Media: Use methods appropriate for the surrounding fire. Consider water spray or fog, carbon dioxide, dry chemical powder, or alcohol resistant foam.

Products of Combustion: Upon decomposition this product may emit carbon dioxide, carbon monoxide and/or low molecular weight hydrocarbons.

Fire Fighting Equipment/Instructions: Wear protective clothing and equipment suitable for the surrounding fire, including helmet, facemask, and self contained breathing apparatus.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions: For large spills wear gloves, safety glasses and when levels exceed OSHA PEL use appropriate NIOSH approved respiratory protection. Keep unnecessary personnel away. Eliminate all sources of ignition or flammables that may come into contact with a spill of this material.

Environmental Precautions: Prevent discharge to open waters.

Method for Containment: Absorb spilled liquid in suitable non-flammable inert material such as clay, vermiculite or diatomaceous earth.

Methods for Clean-Up: Ventilate area of leak or spill. Use spark-proof tools to sweep or scrape up and containerize in approved chemical waste container. Wash spill area with water.

SECTION 7: HANDLING AND STORAGE

Handling: Keep away from heat, sparks and flame. Prevent contact with eyes. Use in well ventilated area.

Storage: Keep the container tightly closed and in a cool, well ventilated place.



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

SECTION 8: EXPOSURE CONTROLS

Isopropyl Alcohol (67-63-0)

ACGIH: 200 ppm TWA

OSHA: 400 ppm TWA; 980 mg/m³ TWA

Engineering Controls: Normal room ventilation is usually adequate under normal use.

Personal Protective Equipment (PPE):

Eye/Face Protection: None needed under normal use – Wear goggles if exposed to unusual amount and splashing

Skin Protection: None needed under normal use -- Wear overalls or apron if splashing is possible

Respiratory Protection: May be needed if vapor concentrations are high.

General Hygiene Considerations: None needed under normal use.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Non-woven cloth saturated with liquid. <0.5mL of free liquid in packaging.

Appearance/Color: Clear

Odor: Alcohol

Flash Point: 53.1°F/ 11.7 °C – Closed Cup Method

PH: Not Available.

Vapor Density: 2.1 (air=1)

Boiling Point: 80°C

Vapor Pressure: No data

Melting Point: No data

Freezing Point: Not Available

Flammability Properties (see section 5)

Solubility (in water): Soluble

Specific Gravity @ 25°C: 0.88-0.92

Evaporation Rate: Not Available

Octanol/Water partition coefficient : Not Available

Auto-ignition temperature: Not Available

Decomposition temperature: Not Available

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable under normal ambient temperatures 70°C (21°C)

Condition to Avoid: Avoid excessive heat or sources of ignition.

Incompatible Materials: This product reacts with strong acid, strong bases, and oxidizing agents.

Hazardous Decomposition: Upon decomposition, this product evolves carbon monoxide, carbon dioxide, and/or low weight hydrocarbons.



SAFETY DATA SHEET

PASSION. PARTNERSHIP. POSSIBILITIES.

Hazardous Reactions: Hazardous polymerization will not occur.

SECTION 11: TOXICOLOGICAL INFORMATION

ACUTE EFFECTS:

A: General Product information

Product contains isopropyl alcohol.

B: Acute Toxicity

Low order of acute toxicity is possible.

CHRONIC EFFECTS: Component

Isopropyl Alcohol (67-63-0) -- This product is not expected to cause long term adverse effects

Carcinogenicity: ACGIH A4 – Not Classifiable as a Human Carcinogen

Neurotoxicity: No information available

Mutagenicity: No information available for product.

Reproductive: This product is not expected to cause reproductive health effects

Developmental: This product is not expected to cause reproductive health effects.

Target Organs: When consumed, ethyl alcohol can target the respiratory system, skin, eyes, CNS, liver, blood and reproductive system.

SECTION 12: ECOLOGICAL INFORMATION

Solutions of alcohols are toxic to aquatic life at moderate to low concentrations. No long-term ecological effects are likely. Concentrated solutions of alcohols and surfactants may cause damage to aquatic and terrestrial plants.

SECTION 13: DISPOSAL CONSIDERATIONS

Dispose in accordance with federal state and local regulations. Labels should not be removed from containers until they have been cleaned. Do not cut, puncture or weld near container. Do not incinerate closed containers. Empty containers may contain hazardous residues. Dispose of containers with care.

SECTION 14: TRANSPORTATION INFORMATION

Product contains <0.5mL total liquid per unit. Some free liquid may be present.

DOT (ORM-D Exemption)

Proper Shipping Name	ISOPROPANOL
Hazard Class	3
Packing Group	II
Description	CONSUMER COMMODITY/ LTD QTY, ORM-D
Emergency Response Guide Number	127

<u>UN-No.</u>	UN1219
Proper Shipping Name	ISOPROPANOL
Hazard Class	3
Packing Group	II
Description	UN1219, ISOPROPANOL, 3, II



SAFETY DATA SHEET

PASSION. PARTNERSHIP. POSSIBILITIES.

Limited Quantity (Per Package) 1 Liter

IATA

UN-No.	UN1219
Proper Shipping Name	ISOPROPANOL
Hazard Class	3 (Flammable Liquid)
Packing Group	II
Description	UN1219, ISOPROPANOL, 3, II
Marine Pollutant	NO

IMDG/IMO

UN-No.	UN1219
Proper Shipping Name	ISOPROPANOL
Hazard Class	3
Packing Group	II
EMS No.	F-E, S-D
Special Provisions	223, 274,
Description	UN1219, ISOPROPANOL, 3, II, (23°C C.C.)
Marine Pollutant	NO

DOT Ground ORM-D Exemption: Consumer Commodity / Limited Quantity

ORM-D (Other Regulated Material – Domestic): Consumer Commodity, Limited Quantity.

“ORM-D, Consumer Commodity” label for domestic ground shipping in consumer packaging only. Suitable ORM-D labelling for air and vessel shipments requires additional labelling and Shipping Papers, in accordance with DOT CFR 172.

“Limited Quantity” marking required on each package for ground shipping of limited quantities (1 Liter or less) without Shipping Papers, as defined in DOT CFR 172.101.

SECTION 15: REGULATORY INFORMATION

DOT / USA

Label Information: Flammable Liquid

WHMIS / CANADA

Class: B2 Flammable Liquid

SECTION 16: OTHER INFORMATION

Issue Date:	03-26-14
Revision Date:	06-29-16



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

Disclaimer:

The information provided in this SDS is correct and is to the best of our knowledge, at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.