1 - PRODUCT IDENTIFICATION

PRODUCT NAME: Cherry Deodorizer

PRODUCT TYPE: Neutral Liquid Cleaning Compound

PRODUCT NUMBER: C0542XXX (Last 3 characters vary with the packaging)

COMPANY: Simoniz USA, Inc.

201 Boston Turnpike Bolton, CT 06043 1-800-227-5536

www.simoniz.com

EMERGENCY PHONE: (800) 255-3924 (CHEM-TEL)

2 - HAZARDS IDENTIFICATION

CLASSIFICATION OF SUBSTANCE/MIXTURE: Eye Irritation (2B)

SYMBOLS:....

SIGNAL WORD: WARNING!

HAZARD STATEMENT: Causes skin irritation. Causes serious eye irritation

PRECAUTIONARY STATEMENTS:

PREVENTION: Wash hands thoroughly after handling.

RESPONSE:..... IF IN EYES: Rinse cautiously with water for several minutes.

Remove contact lenses if present and easy to do - continue

rinsing. If eye irritation persists get medical advice/attention.

STORAGE:......N/A
DISPOSAL:.....N/A

3 - COMPOSITION / INFORMATION ON INGREDIENTS

INGREDIENT C.A.S. NUMBER CONCENTRATION (%)

Water 7732-18-5 97-100 Nonylphenoxypolyethyleneoxyethanol 9016-45-9 0-3

4 - FIRST-AID MEASURES

BREATHING (INHALATION): .. If victim shows signs of discomfort or irritation, remove to fresh air. If symptoms persist, get immediate medical attention.

SWALLOWING (INGESTION):. DO NOT INDUCE VOMITING! Drink a large quantity of water or

milk. Do not attempt to give liquids to an unconscious person.

Get immediate medical attention!

EYES: Ingestion. Not likely to be inhaled in dangerous amounts.

SKIN (DERMAL): Flush from skin and clothing with large amounts of fresh water. If

irritation persists, consult physician. Wash contaminated clothing

before wearing.

5 – FIRE-FIGHTING MEASURES

FLASHPOINT: This product is non-flammable.

EXTINGUISHING MEDIA: This product is non-flammable. Use extinguishing media suitable

for materials already burning.

SPECIAL FIRE FIGHTING PROCEDURES:.....Firefighters working in areas where this

product is present should be equipped with an approved, fully

enclosed SCBA.

UNUSUAL FIRE AND EXPLOSION HAZARDS:..... None known.

6 - ACCIDENTAL RELEASE MEASURES

SPILL PROCEDURES:...... Dike to prevent spillage into streams or sewer systems. Consult

local, state and federal authorities.

WASTE DISPOSAL: As recommended by local, state and federal authorities.

7 - HANDLING and STORAGE

STORAGE:..... Store in a cool, well ventilated area. Avoid overheating or

freezing.

HANDLING: Under normal use according to label instructions, special

protection should not be necessary. Wear eye protection if product is likely to splash.Do not place this product in an unmarked container! Keep away from children! Spilled material

is slippery.

8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

RESPIRATORY PROTECTION:.....Not usually needed. Vapors not normally

harmful.

PROTECTIVE CLOTHING:...... Nitrile or PVC gloves, and chemical splash goggles.

ADDITIONAL MEASURES:..... Under normal use according to label instructions, special

protection should not be necessary. Wear eye protection if product is likely to splash.Do not place this product in an unmarked container! Keep away from children! Spilled material

is slippery.

INGREDIENT C.A.S. NUMBER PEL

Water 7732-18-5 No limits established

PAGE 2 of 4

Nonylphenoxypolyethyleneoxyethanol

9016-45-9

No limits established

9 - PHYSICAL / CHEMICAL PROPERITES

APPEARANCE & ODOR:...... Red transparent liquid, cherry scented. ODOR THRESHOLD: N/A MELTING POINT: 210 degrees F. FREEZING POINT: N/A BOILING POINT: 210 degrees F. **BOILING POINT RANGE:** N/A FLASHPOINT: This product is non-flammable. **EVAPORATION RATE:** N/A FLAMMABILITY (solid/gas): ... N/A EXPLOSION LIMITS:..... N/A VAPOR PRESSURE:..... N/A VAPOR DENSITY (AIR=1): Greater than 1. **SPECIFIC GRAVITY:.....** 1.00 **SOLUBILITY IN WATER:** Completely soluble. PARTITION COEFFICIENT: N/A AUTO-IGNITION TEMPERATURE:N/A DECOMPOSITION TEMPERATURE:N/A VISCOSITY: Water thin

10 - STABILITY and REACTIVITY

STABILITY: Stable under normal conditions. **HAZARDOUS DECOMP.:** This product not known to polymerize. **INCOMPATIBILITY:** Do not mix with other chemicals.

11 - TOXICOLOGICAL INFORMATION

ROUTE(S) OF ENTRY:LISTED CARCINOGEN:	Ingestion. Not likely to be inhaled in dangerous amounts. None over 0.1%.
	AVATED:May aggravate pre-existing dermatitis.
	. Not likely to be inhaled in hazardous amounts. Maintain
adequate ventilation in the work	carea.
INGESTION:	. This material can cause irritation or damage to stomach and
esophagus.	
EYES:	. May cause severe eye irritation.
SKIN (DERMAL):	. Not likely to irritate. Prolonged exposure to undiluted product
may cause irritation.	
ACUTE TOXICITY* (ORAL):	>2000 mg/kg
ACUTE TOXICITY* (DERMAL)	:>2000 mg/kg
ACUTE TOXCITY* (INHALATION	ON): >20,000 ppm V (Gas), >20 mg/l (Vapor), >5
mg/l (Dust)	

^{*}Determined using the additivity formula for mixtures (GHS Purple Book, 3.1.3.6)

12 - ECOLOGICAL INFORMATION

ENVIRONMENTAL FATE AND DISTRIBUTION: N/A

13 - DISPOSAL CONSIDERATIONS

WASTE DISPOSAL: As recommended by local, state and federal authorities.

14 - TRANSPORTATION INFORMATION

PROPER SHIPPING NAME: Not D.O.T. regulated.

HAZARD CLASS: UN/NA NUMBER: PACKAGING GROUP:

15 - REGULATIONS

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29CFR 1910.1200

16 – OTHER INFORMATION

ADDITIONAL: The information contained in this SDS is based on the data

available to us from sources we believe to be reliable. No warranty or guaranty expressed or implied is made regarding the accuracy of this data or the results obtained from the reliance on this data. The manufacturer assumes no responsibility for injury from the use of this product. Be safe- read this product safety information and pass it on to all persons who may be exposed to this product. Federal law requires it. This product and/or all of its components are either included on or exempt from the TSCA

Inventory of Chemical Substances.

REVISION DATE: 05/07/15