1 – PRODUCT IDENTIFICATION

2 – HAZARDS IDENTIFICATION

CLASSIFICATION OF SUBSTANCE/MIXTURE:..... Skin Irritation (2) Eye Irritation (2B) Skin Sensitizer (1B)

SYMBOLS:....



SIGNAL WORD:	WARNING!
HAZARD STATEMENT:	Causes skin irritation. Causes eye irritation. May cause an allergic skin reaction.
	•
PRECAUTIONARY STATEMENTS:	
PREVENTION:	Wash hands thoroughly after handling. Wear protective
	gloves/protective clothing/eye protection/face protection. Avoid
	breathing dust/fume/gas/mist/vapours/spray. Contaminated
	work clothing should not be allowed out of the workplace.
DECDONCE.	o
RESPONSE:	IF ON SKIN: Wash with plenty of water and soap. Specific
	treatment (see First AID Section on this label). If skin irritation
	occurs: Get medical advice/attention. Take off contaminated
	clothing and wash before reuse. IF IN EYES: Rinse cautiously
	with water for several minutes. Remove contact lenses if present
	•
	and easy to do – continue rinsing. If skin irritation or a rash
	occurs: Get medical advice/attention.
STORAGE:	Store in a dry place. Store in a closed container
DISPOSAL:	Dispose of container and contents in accordance with local
	regulations.

3 – COMPOSITION / INFORMATION ON INGREDIENTS

INGREDIENT

Water Acrylate Copolymer

Diethylene Glycol Ethyl Ether Olefin-Acrylate Polymer

Tributoxy Ethyl Phosphate Zinc Compounds

C.A.S. NUMBER

7732-18-5 Trade Secret* (withheld by Manufacturer) 111-90-0 Trade Secret* (withheld by Manufacturer) 78-51-3 38714-47-5

Percentages of ingredients are being withheld as trade secret information. This information will be disclosed as necessary to authorized individuals

4 – FIRST-AID MEASURES

5 – FIRE-FIGHTING MEASURES

6 – ACCIDENTAL RELEASE MEASURES

WASTE DISPOSAL: As recommended by local, state and federal authorities.

7 – HANDLING and STORAGE

STORAGE:	. Store in a cool, well ventilated area. Avoid overheating or
	freezing.
HANDLING:	Do not place this product in an unmarked container. Avoid eye
	contact. Spilled material is slippery.

8 – EXPOSURE CONTROLS / PERSONAL PROTECTION

RESPIRATORY PROTECTION:Not usually needed. Vapors not normally harmful.

PROTECTIVE CLOTHING:...... Special protection not usually needed. Wear eye protection if product is likely to splash.

ADDITIONAL MEASURES: Do not place this product in an unmarked container. Avoid eye contact. Spilled material is slippery.

INGREDIENT

C.A.S. NUMBER

PEL

Water Acrylate Copolymer Diethylene Glycol Ethyl Ether Olefin-Acrylate Polymer Tributoxy Ethyl Phosphate Zinc Compounds 7732-18-5 Trade Secret 111-90-0 Trade Secret 78-51-3 38714-47-5

No limits established No limits established 5 mg/m3 TWA 0.5mg/m3 TWA 5 mg/m3 TWA

9 – PHYSICAL / CHEMICAL PROPERITES

APPEARANCE & ODOR: White opaque liquid. No significant odor. ODOR THRESHOLD: N/A MELTING POINT: 210 degrees F. FREEZING POINT: N/A BOILING POINT:..... 210 degrees F. BOILING POINT RANGE:..... N/A FLASHPOINT: This product is non-flammable. EVAPORATION RATE:.....N/A FLAMMABILITY (solid/gas):.... N/A EXPLOSION LIMITS:..... N/A VAPOR PRESSURE: N/A VAPOR DENSITY (AIR=1):..... Greater than 1. SPECIFIC GRAVITY: 1.02 **SOLUBILITY IN WATER:** Completely soluble. PARTITION COEFFICIENT: N/A AUTO-IGNITION TEMPERATURE:.....N/A DECOMPOSITION TEMPERATURE:N/A VISCOSITY: Water thin

10 – STABILITY and REACTIVITY

11 – TOXICOLOGICAL INFORMATION

*Determined using the additivity formula for mixtures (GHS Purple Book, 3.1.3.6)

12 – ECOLOGICAL INFORMATION

ENVIRONMENTAL FATE AND DISTRIBUTION: N/A

13 – DISPOSAL CONSIDERATIONS

WASTE DISPOSAL: As recommended by local, state and federal authorities.

14 – TRANSPORTATION INFORMATION

PROPER SHIPPING NAME:..... Not D.O.T. regulated. HAZARD CLASS:..... UN/NA NUMBER: PACKAGING GROUP :.....

15 - REGULATIONS

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29CFR 1910.1200

PAGE 4 of 5

16 – OTHER INFORMATION