




Model VF750
Model VF1100

Indirect Fired Oil Heaters

- Reliable Riello burner
- Remote thermostat
- Wheels for easy portability
- Long lasting stainless steel combustion chamber
- High static centrifugal blower
- Ductable to 150 ft.
- 100% dry heat, clean of combustion by-products
- Recirculation capability
- Available with 200 gallon fuel cell



VF750 with optional 200 gallon fuel cell

SPECIFICATIONS		
	VF750	VF1100
	750,000 BTU/hr	1,000,000 BTU/hr
Fuel	#1 or #2 Diesel, Kerosene	#1 or #2 Diesel, Kerosene
Fuel Consumption	5.33 GPH	7.16 GPH
Burner	Riello 40 F20	Riello 40 F22
Electrical	240 Volts 20 Amps	240 Volts 25 Amps
Fan	9400 CFM, 1.2" Static Pressure, 3HP	11,200 CFM, 1.2" Static Pressure, 4HP
Thermostat	Remote On/Off with 50' cord	Remote On/Off with 50' cord
Temperature Rise	110°F	110°F
Dimensions	100"L x 36"W x 64"H	104"L x 41"W x 73"H
Duct Outlet (max duct length)	1-30" Dia. (150'), 2-20" Dia. (90')	1-30" Dia. (150'), 2-24" Dia. (90')
Duct Inlet (recirculation)	30" Dia., 30' Max Length	30" Dia., 30' Max Length
Approx. Weight	948 lbs.	1,160 lbs.



342 N. 400 E. Valparaiso, IN 46383
219-464-8818 • 219-462-7985 • www.heatwagon.com