

PREDATOR SS

Semi-Automatic Stretch Wrap System

Simple and easy to use, the Predator SS is the affordable solution to stretch wrap your load without stretching your budget. The Predator SS is loaded with features, including top and bottom counters, photo eye, and two (2) wrapping modes.

State-of-the-art INFO screen shows current machine operation and makes troubleshooting easy. The Simplified Stretch allows you to precisely adjust your stretch level and film force on your load with the turn of a knob.



Low Profile shown
High Profile available

HIGHLIGHTS

- » Simplified Stretch allows you to precisely adjust the film stretch and force on your load, giving you greater film performance and utilization.
- » INFO Screen allows for simple operation and helps make troubleshooting easy
- » Simple and sturdy design makes the Predator SS an easy-to-use, affordable, and reliable machine

PREMIUM FEATURES



Simplified Stretch

Simplified Stretch is easy to use, just turn the knob to adjust your film stretch and force on the load for better film performance and to best suit your wrapping needs.




Control Panel

Programmable settings allow for consistent wrapping from load to load and maximum film savings.



Advanced INFO Screen

Provides system diagnostics for easy troubleshooting.



Semi-Automatic Controls

Photo eye and top and bottom wrap counters increase productivity and efficiency.



High or Low Profile

Highlight will build the correct system for your application. The Predator SS is available in either High or Low Profile. The High Profile can be easily loaded with a fork lift. The Low Profile can use an optional ramp for loading with hand pallet jacks.

CONTROL PANEL FEATURES

- INFO displays machine operation and provides data for diagnosis
- 2 Wrap Modes, Select Spiral Up/Down or Spiral Up Only
- System Reset
- Turntable Jog
- Carriage Jog
- Keyed Electrical Cabinet
- 0-9 Top and Bottom Wraps
- Start
- Banding
- Adjustable Turntable Speed
- Adjustable Carriage Speed
- Stop
- Power Safety Disconnect
- Universal and Easy to Use

SYSTEM SPECIFICATIONS

Simplified Stretch	Fully Adjustable 60% to 150%, Typical	Load Weight Capacity	Low & High Profile 4,000 pounds
Turntable	Low Profile 60" Diameter, 12 RPM High Profile 48"x48" Octagonal, 12 RPM	2 Wrap Modes	Spiral Up/Down and Spiral Up Only
Wrap Height	Up to 80"	Electrical Requirements	115 V, 15 Amp
Carriage Lift Motor	Baldor 90 VDC	Machine Weight	Low & High Profile 1,050 Pounds
Operating Controls	Allen-Bradley MicroLogix 1200 PLC	Options	Complete selection of options available for both High and Low Profile Models.

Contact:

HIGHLIGHT
INDUSTRIES, INC.