


PREDATOR UX Low Profile Turntable

The Predator UX Low Profile Turntable is the simple addition to aid in stretch wrapping your loads. With variable speeds up to 12 RPM and steel plate construction, the Predator UX Low Profile Turntable is ready for years of reliable operation.

Combined with the optional ramp and Highlight Handwrapper, the Predator UX Low Profile Turntable will save time and reduce fatigue while wrapping.



SYSTEM SPECIFICATIONS

Turntable	59" Diameter
Turntable Speed	Adjustable up to 12 RPM
Controls	Easy Footswitch Operation
Load Capacity	4,000 Pounds
Drives	1/2 HP AC Drive System with Soft Start

PREMIUM FEATURES

- 1/4" steel plate construction
- Front and rear forklift portable
- 14 cam rollers with center bearing support
- Optional 48" ramp with various length porches available
- Modular-ready to accept Synergy 0.5 or Predator XS Tower

SYNERGY High Profile Turntable

The Synergy High Profile Turntable is the perfect addition to your warehouse for wrapping your loads. The High Profile design makes loading and unloading with a forklift easy, and allows you to wrap any size pallet.

With variable speeds up to 12 RPM, and durable all steel construction, the Synergy High Profile Turntable is ready for for years of industrial use.



SYSTEM SPECIFICATIONS

Turntable	48" Octagonal
Turntable Speed	Adjustable up to 12 RPM
Controls	Easy Footswitch Operation
Load Capacity	4,000 Pounds
Drives	3/4 HP AC Drive System with Soft Start

PREMIUM FEATURES

- Easy loading for forklift operators
- Heavy duty steel diamond plate surface
- Impact-absorbing flexible coupling
- Self-aligning casters with 8" drive wheel
- Modular-ready to accept any Synergy or Predator Tower

SYNERGY Low Profile Turntable

The Synergy Low Profile Turntable is designed with reliable AC drives, durable steel construction, and bigger motors to make it technologically advanced and ready to accept upgrades.

The steel construction and AC drive system of the Synergy Low Profile Turntable will ensure reliable operation. The optional ramp makes loading your products with a hand pallet jack simple and convenient.



SYSTEM SPECIFICATIONS

Turntable	65" Diameter
Turntable Speed	Adjustable up to 12 RPM
Controls	Easy Footswitch Operation
Load Capacity	4,000 Pounds
Drives	3/4 HP AC Drive System with Soft Start


PREMIUM FEATURES

- Durable steel plate construction
- Rear Forklift Portable
- Optional 48" ramp with porches available
- Modular-ready to accept Synergy 0.5, 1 or 1.5 Tower
- 10 cam rollers with center bearing support

SYNERGY Heavy Duty Low Profile Turntable

The Synergy Heavy Duty Low Profile Turntable's *precision-engineered* design allows for a maximized 5,000 pound capacity, and will stand up to decades of use stretch wrapping in an industrial environment.

The Synergy Heavy Duty Low Profile Turntable can accept an optional ramp for easy loading with hand pallet jacks, and will reduce fatigue and increase productivity when wrapping your loads.



SYSTEM SPECIFICATIONS

Turntable	59" Diameter
Turntable Speed	Adjustable up to 12 RPM
Controls	Easy Footswitch Operation
Load Capacity	5,000 Pounds
Drives	3/4 HP AC Drive System with Soft Start

PREMIUM FEATURES

- Heavy duty 3/8" steel plate construction
- 12 cam rollers with center bearing support
- Front and rear forklift portable
- Modular-ready to accept Synergy 0.5, 1, 1.5, 2, 2.5 or 3 Tower
- Optional 48" ramp with porch available

Contact: