



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

SECTION 1: PRODUCT IDENTIFICATION

PRODUCT: BZK Prep Pads and Towelette

Product Label Name: BZK Prep Pads and Towelette

Company Name and Address: Dukal Corporation
2 Fleetwood Court
Ronkonkoma, NY 11779

Emergency Telephone Number: 631-656-3800

Recommended use: First Aid Antiseptic.

SECTION 2: HAZARDOUS IDENTIFICATION

Hazard Class/Category: Eye Irritant – 2B
Skin Irritant – 3

Hazard Symbol: No Symbol

Signal Word: Warning

Hazard Statements: Causes eye irritation (H320)
Causes mild skin irritation (H316)

Precautionary statements:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention. (P305+P351) (P337+P313)

Skin: If skin irritation occurs: Wash with plenty of soap and water. (P332+P352)

SECTION 3: INFORMATION ON INGREDIENTS

Ingredient list	Cas #	%
Benzalkonium Chloride	8001-54-5	0.50%
Sodium bicarbonate	144-55-8	0.05%
Purified Water	7732-18-5	QS to 100

OSHA Standard Format

SECTION 4: FIRST-AID MEASURES

First aid procedures

Inhalation:	Not a normal route of exposure. May cause respiratory tract irritation.
Ingestion	Not a normal route of exposure. May cause stomach distress, nausea or vomiting.
Target organs:	Eyes. Skin.
Chronic effects	Prolonged or repeated exposure can cause drying, defatting and dermatitis.
Signs and symptoms	Symptoms may include redness, edema, drying, defatting and cracking of the skin.
Overexposure:	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting.
Eye contact:	Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention.
Skin contact:	In case of skin irritation, wash with plenty of soap and water. Discontinue use of product.
Inhalation:	Not a normal route of exposure. If symptoms develop, move victim to fresh air. If symptoms persist, obtain medical attention.
Ingestion:	Not a normal route of exposure. Do not induce vomiting. Never give anything by mouth if victim is unconscious, or is convulsing. Obtain medical attention.
Note to Physician:	Symptoms may be delayed.
General Advice:	If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance. Keep out of reach of children. Avoid contact with eyes.

SECTION 5: FIRE-FIGHTING MEASURES

Flammable properties	Not flammable by OSHA criteria
Suitable extinguishing media	Treat for surrounding material.
Specific hazards arising from the chemical:	Not available
Protective equipment for firefighters	Firefighters should wear full protective clothing including self-contained breathing apparatus.
Hazardous combustion products	May include and are not limited to: Oxides of carbon. Hydrogen chloride.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions	Keep unnecessary personnel away. Do not touch or walk through spilled material. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep people away from and upwind of spill/leak.
Methods for containment	Prevent entry into waterways, sewers, basements or confined areas.
Methods for cleaning up	Pick up and discard towel.

SECTION 7: HANDLING AND STORAGE

Handling	Use good industrial hygiene practices in handling this material.
Storage	Keep out of reach of children. Store in a closed container away from incompatible materials.

SECTION 8: EXPOSURE CONTROLS

Engineering controls	General ventilation normally adequate.
Personal protective equipment	
Eye / face protection	Follow standard industrial hygiene practices.



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

Hand protection	Not required.
Skin and body protection	As required by employer code.
Respiratory protection	Where exposure guideline levels may be exceeded, use an approved NIOSH respirator.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Liquid saturated on wipe
Color	Clear liquid
Form	Liquid saturated on wipe.
Odor	Characteristic
Odor threshold	Not available
Physical state	Solid
pH	Not available
Melting point	Not available
Freezing point	Not available
Boiling point	101.11 °C (214 °F)
Flash point	Not available
Evaporation rate	Not available
Flammability limits in air, lower	Not available
Flammability limits in air, upper	Not applicable
Vapor pressure	Not available
Vapor density	Not available
Specific gravity	Not available
Octanol/water coefficient	Not available
Solubility (H₂O)	Not available
Auto-ignition temperature	Not available
VOC (Weight %)	Not available
Viscosity	Not available
Percent volatile	Not available

SECTION 10: STABILITY AND REACTIVITY

Chemical stability	Stable under recommended storage conditions.
Conditions to avoid	Do not mix with other chemicals.
Incompatible materials	Caustics. Acids. Oxidizers.
Hazardous decomposition products	May include and are not limited to: Oxides of carbon. Hydrogen chloride.

OSHA Standard Format



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

Possibility of hazardous reactions Hazardous polymerization does not occur.

SECTION 11: TOXICOLOGICAL INFORMATION

Effects of acute exposure

Eye	May cause irritation.
Skin	In case of skin irritation, discontinue use of the product.
Inhalation	Not a normal route of exposure. May cause respiratory tract irritation.
Ingestion	Not a normal route of exposure. May cause stomach distress, nausea or vomiting.
Sensitization	Non-hazardous by WHMIS/OSHA criteria.
Chronic effects	Non-hazardous by WHMIS/OSHA criteria.
Carcinogenicity	Non-hazardous by WHMIS/OSHA criteria.
Mutagenicity	Non-hazardous by WHMIS/OSHA criteria.
Reproductive effects	Non-hazardous by WHMIS/OSHA criteria.
Teratogenicity	Non-hazardous by WHMIS/OSHA criteria.

SECTION 12: ECOLOGICAL INFORMATION

None available

SECTION 13: DISPOSABLE INFORMATION

Waste codes	Not available
Disposal instructions	Discard after single use. Review federal, state/provincial, and local government requirements prior to disposal. Discard with solid waste. Dispose in accordance with all applicable regulations.
Waste from residues / unused	Not available
Contaminated packaging	Not available

SECTION 14: TRANSPORTATION INFORMATION

U.S. Department of Transportation	Not regulated as dangerous goods.
Transportation of Dangerous Goods	Not regulated as dangerous goods.

SECTION 15: REGULATORY INFORMATION

Occupational Safety and Health Administration (OSHA)

29 CFR 1910.1200 hazardous No chemical



PASSION. PARTNERSHIP. POSSIBILITIES.

SAFETY DATA SHEET

SECTION 16: OTHER INFORMATION

Issue Date: 06-18-2014
Revision Date: 06-13-2016

Disclaimer:

The information provided in this SDS is correct and is to the best of our knowledge, at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.