



ULTRATECH
INTERNATIONAL, INC.

Ultra-Containment Berm[®] Comparison Guide



Description (Click for more information)	Cost	Drive-in/out	Set-up Required (beyond initial deployment)	Standard Height	Other Heights Available	Standard Material	Other Materials Available
Collapsible Wall Model	\$	-	Yes	12"	18", 24"	Copolymer-2000	PVC, XR5, Urethane
Compact Model	\$\$\$	-	Yes	12"	-	Copolymer-2000	PVC, XR5, Urethane
Economy Model	\$	-	Yes	12"	18"	Copolymer-2000	PVC, XR5, Urethane
Foam Wall Model	\$\$	4 Sides	No	4"	2", 6"	Copolymer-2000	PVC, XR5, Urethane
Modular Model (Gorilla Berm)	\$\$\$	4 Sides	No	6"	-	PVC	Copolymer-2000, XR5, Urethane
Rapid Rise	\$\$	4 Sides	No	12"	24"	Copolymer-2000	PVC, XR5, Urethane
Stake Wall Model	\$\$\$	4 Sides	No	12"	-	Copolymer-2000	PVC, XR5, Urethane
Ultimate Model	\$\$	2 Sides	Only 2 Long Slides	12"	-	Copolymer-2000	PVC, XR5, Urethane
Containment Wall	\$\$\$	-	Yes	36"	12", 24"	Polyethylene	None
Mini Foam Wall Model	\$	4 Sides	No	6"	-	PVC	None

Berm Fabric Material	Weight	Thickness	Min Temp	Max Temp	Cold Crack	Tear Strength	Puncture Resistance
Copolymer-2000	30 oz/yd ²	30 mils nominal	-25°F	160°F	-25°F	30 lb _f nominal	50 lb _f typical
Urethane	23 oz/yd ²	25 mils nominal	-45°F	160°F	-45°F	58 lb _f nominal	750 lb _f
PVC	22 oz/yd ²	24 mils nominal	-30°F	145°F	-30°F	46 lb _f nominal	91 lb _f
XR5	30 oz/yd ²	30 mils minimum	-30°F	160°F	-30°F	55 lb _f nominal	250 lb _f minimum



Collapsible Wall



Compact



Economy



Foam Wall



Modular (Gorilla)



Rapid Rise



Stake Wall



Containment Wall



Mini Foam Wall