

MANUAL STENCILING

HAND-OPERATED STENCIL MACHINES

Dependable. Durable. Dynamic.

Now the power to cut and create high-profile stencils designed for your specific applications is in the palm of your hand. Our hand-operated stencil machines are built for the long run and help to make the stenciling process fast, easy – and effective.



Contact your distributor to order or to see the full line of superior quality Marsh products.

MANUAL STENCILING HAND-OPERATED STENCIL MACHINES

Features:

- **Punch and die** - Case-hardened dies have wear-resistant cutting edges. Zinc alloy punch is stronger, lasts longer than steel, fits closer, cuts cleaner and is more corrosion-resistant
- **Aluminum rotating parts** - Lightweight for faster, smoother operation
- **Unobstructed hand wheel** - No spokes or lugs to interfere with hand
- **Durable finish** - Baked-on powder coat, industrial black finish
- **Sealed-in lubrication** - Parts rotating on center spindle "ride on oil" from saturated felt rings in base of machine, providing years of self lubrication and reduced operating sound
- **Large dial** - Easy to read
- **Word space button and release lever** - For quicker, neater, easier cutting
- **Accurate spacing** - Simple cam and ratchet spaces automatically
- **Quick, shock-free centering** - Makes character selection smoother and easier
- **Rubber base mounts** - Smooth, soft feel to cutting operation
- **Special character punch and dies** - Can be individually quoted
- **API logo available**
- **Spanish ñ characters available**
- **18-month warranty**



R and R-5 Model - 1"

- R: 4 lines, any length; 14 characters/foot
- R-5: 5 lines, any length; 14 characters/foot

H Model - 1/2"

- 6 lines, any length; 23 characters/foot

S Model - 3/4"

- 4 lines, any length; 16 characters/foot

Q Model - 1/4"

- 10 lines, any length; 43 characters/foot

Models	Size Cut	Lines	Net Weight	Gross Weight	Largest Package Dimensions (L x W x H)
R	1" / 25 mm	4	64 lb / 30 kg	71 lb / 33 kg	26" x 13" x 20" / 660 mm x 330 mm x 508 mm
R-5	1" / 25 mm	5	64 lb / 30 kg	71 lb / 33 kg	26" x 13" x 20" / 660 mm x 330 mm x 508 mm
S	3/4" / 19 mm	4	47 lb / 21 kg	53 lb / 24 kg	22" x 12" x 19" / 559 mm x 305 mm x 483 mm
H	1/2" / 13 mm	6	47 lb / 21 kg	53 lb / 24 kg	22" x 12" x 19" / 559 mm x 305 mm x 483 mm
Q	1/4" / 7 mm	10	47 lb / 21 kg	53 lb / 24 kg	22" x 12" x 19" / 559 mm x 305 mm x 483 mm

