

CM[®] LODESTAR[®]



Making the Grade

**It's what the
food processing
industry demands.**

**It's what the
CM Lodestar delivers.**

The CM Lodestar, the most popular electric chain hoist on the market, combines maximum versatility with cleanliness to handle a wide range of food and beverage industry applications that require food grade hoists.

Whether positioning loads for maximum ergonomic benefits, lifting heavy containers for storage or transportation, or performing maintenance on production machinery, the Lodestar provides a full array of benefits. Lubricated with Lubriplate FP-150, a food processing load chain oil, the Lodestar is ideal for all areas where cleanliness is a must every day.

In addition to the Lodestar, stainless steel chain and fittings are available to provide secure lifts for any food processing application.

The ideal choice for food processing environments



- 1/4, 1/2, and 1 Ton Capacities
- Single speed
- Stainless steel load chain, upper hook, lower hook and block assembly, and chain container.
- FDA-approved white epoxy powder coat paint. Also available with unpainted cast aluminum housings or electroless nickel plated housings in lieu of epoxy paint
- NEMA 4 and NEMA 4X control stations
- Sealed weather-proof construction and gear train lifetime lubricated with non-oxidizing grease
- 115/230 1-phase and 230/460 3-phase models
- Lifetime warranty

Single Phase Industrial Clean Room Hoists						
Model	Speed (fpm)	Capacity (Tons)	Power	Lift (ft)	Product Code Classic	Product Code New
B	16	1/4	115-1-60	10	2722/2788CR10	2722NHCR10
				15	2722/2788CR15	2722NHCR15
				20	2722/2788CR20	2722NHCR20
F	16	1/2	115-1-60	10	2752/2788CR10	2752NHCR10
				15	2752/2788CR15	2752NHCR15
				20	2752/2788CR20	2752NHCR20
H	8	1	115-1-60	10	2762/2789CR10	2762NHCR10
				15	2762/2789CR15	2762NHCR15
				20	2762/2789CR20	2762NHCR20
Dual Voltage Industrial Clean Room Hoists						
Model	Speed (fpm)	Capacity (Tons)	Power	Lift (FT)	Product Code Classic	Product Code New
B	16	1/4	230/460	10	2725/2788CR10	2725NHCR10
				15	2725/2788CR15	2725NHCR15
				20	2725/2788CR20	2725NHCR20
F	16	1/2	230/460	10	2755/2788CR10	2755NHCR10
				15	2755/2788CR15	2755NHCR15
				20	2755/2788CR20	2755NHCR20
H	8	1	230/460	10	2765/2789CR10	2765NHCR10
				15	2765/2789CR15	2765NHCR15
				20	2765/2789CR20	2765NHCR20

Additional Products For Food Processing Environments



Stainless Steel Chain

Sizes available from 9/32" to 1/2" (7 to 13 mm)


Working Load Limit Up to 6,500 lb. (2,950 kg)

- Made from 300 series stainless
- Higher temperature resistance than standard grade 80 chain
- Safely used in the food handling industry



Zephyr Hand Hoist

- 1/4-ton to 10-ton capacity
- Stainless steel load chain, upper and lower hooks, and lower hook block
- FDA approved food grade epoxy paint
- Food grade lubricants
- Wide array of available options, including stainless steel lift wheel, hand chain wheel, and chain container; solid stainless steel or electroless nickel plated housings in lieu of epoxy painting



Stainless Steel Trolley

- 1/4-ton to 2-ton capacity standard Larger units built to order
- Constructed entirely of corrosion resistant stainless steel, these trolleys are well suited for virtually all clean room environments
- Two stainless steel precision ball bearings per wheel, sealed and lubricated for life
- Ideal for humid environments and wash-down areas
- Rated for up to 225 degrees Fahrenheit ambient temperature



635 Motorized Trolley

- 1/8-ton thru 2-ton capacities
- Weather-proofed electrical enclosure
- FDA approved white epoxy powder coat painted frames
- Stainless steel and nickel plated hardware
- Stainless steel trackwheels
- Trolley fits American Standard beams as well as Wide Flange Beams including 3.25" patented tracks