

MECHANICAL DOCKLEVELER - RR-68-20

APPROX WEIGHT: 2141 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON





ARCHITECTURAL REVIEW FOR CORRECTNESS OF PIT AND FOR COMPLIANCE TO STATE AND LOCAL CODES IS RECOMMENDED.

PLEASE CIRCLE SPECIFICATIONS:

NEW	(PIT) CONSTRUCTION		
EXISTING	(PIT) CONSTRUCTION		

STANDARD FEATURES

DOCKEVELER MODEL NUMBER: RR-68-20

PIT WIDTH IS: 74 INCHES PIT LENGTH IS: 86 INCHES

PIT DEPTH IS 24 INCHES AT FRONT, 23 3/4 INCHES AT BACK

DOCK HEIGHT IS 48 INCHES (48 INCHES STANDARD)

DOCKLEVELER CAPACITY (GROSS ROLLING LOAD) IS 20,000 LBS.

VERTICAL SERVICE RANGÈ IS 12 INCHES ABOVE AND 12 INCHES BELOW DOCK


INCLUDES (2) 1014-4.5 LAMINATED DOCK BUMPERS

SINGLE AXLE CAPACITY NOT TO EXCEED 70% OF LOAD

ALL STRUCTURAL STEEL CONSTRUCTION WELDING MEETS AWS.
DESIGN, ENGINEERING, AND FABRICATION COMPLIES WITH OSHA & ANSI MH30.1
-INSTALL TO MEET ALL APPLICABLE STATE & LOCAL CODES FOR YOUR AREA!

SPECIAL FEATURES

NONE



_	SI	EE DRAWING NUMBERS RR-1 THRU RR-4 FOR MORE INSTALLATION INFO
	A P P R O V	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. ANY MODIFIED UNITS ARE NON-RETURNABLE [] As drawn [] As marked
	Α	Signed:Date:
	L	Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING
Þ	ISTRIE	BUTOR'S NAME: P.O.#

		Fillited Name			
		LEAD TIME WILL START UP	APPROVAL DRAWING		
ĺ	DISTRI	BUTOR'S NAME:	P.O.# X		
		ESTIL MANUFAC	W.O.# X		
- 1		^{VN BY:} TJM	DATE: 02/	27/12	SALES: X
ĺ	REFER	ENCE: X		SCALE: NTS	FILE NAME:
0	QUOT	ED LEAD TIME: X	QUOTE #	1	07-007-012