
## ADJUSTABLE STEP-MATE STANDS - MODEL: ASP-24

APPROX WEIGHT: 44.96 lbs.

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



## STANDARD FEATURES

MODEL NUMBER IS ASP-24

CAPACITY: 500 LBS

OVERALL WIDTH: 23 13/16"

OVERALL LENGTH: 22 7/8"

BOTTOM STEP HEIGHT: MIN. 6", MAX. 8 1/4" TOP STEP HEIGHT: MIN. 13", MAX. 15 1/4"

STEPS:

-SERRATED STEEL 11 3/4" DEEP

LEGS:

-ADJUSTABLE

-ANTI-SLIP TIPS

TOUGH BAKED IN POWDER COATED YELLOW FINISH

## SPECIAL FEATURES

NONE

## DIMENSION TO FRANCE + 1/4"

		DIVIENSION TOLERANCE 1 1/4			
			RSIGNED, AGR ITED SATISFIES D		
	<b>A</b>		NTS. I ALSO AC		
	P		FIRM PRODUCT		
	P		CE WITH ALL AF CAL REGULATION		
	R				RETURNABLE
	0				
	V		] As drawn	[ ] As m	arked
	Ā	Signed:			Date:
	L	Printed Name:			
		LEAD TIME WILL ST	TART UPON RECEI	IPT OF SIGNED	APPROVAL DRAWING
FOR INTERNAL	L OOL OIVLI	BUTOR'S NAME:			P.O.# X
PROJECT S	IGN OFF VI	ESTIL MANU	EACTI IRIN		W.O.# ,,
SALES			IACIONIN		X
ENG.	DRAW	'N BY: X	DATE: XX	/XX/XX	SALES: X
EAD	REFER	ENCE: X	7(7()	SCALE: 1:10	FILE NAME:
FAB.				SCALE: 1:10	
POWER	QUOT	ED LEAD TIME: X	QUOTE #		14-007-049