


MANUAL SCISSOR CART, CART-24-15-M



TWO SPEED MANUAL FOOT PUMP:
 -AUTOMATIC SHIFT @ 800 - 1000 PSI
 WHEN LOADED.

STANDARD FEATURES

- MODEL NUMBER: CART-24-15-M
- CAPACITY: 1,500 LBS.
- PLATFORM WIDTH: 24"
- PLATFORM LENGTH: 48"
- PLATFORM LOWERED HEIGHT: 9"
- PLATFORM RAISED HEIGHT: 42 1/2"
- OVERALL WIDTH: 36"
- OVERALL LENGTH: 69 1/2"
- CASTERS: TWO 4 X 2 PHENOLIC SWIVEL
TWO 4 X 2 PHENOLIC RIGID

SPECIAL FEATURES

NONE

PRODUCTION WILL START UPON
 RECEIPT OF SIGNED APPROVAL
 DRAWING

**SPECIAL UNITS ARE NON-RETURNABLE
 *AVAILABLE AT ADDITIONAL COSTS

All graphics provided are for reference only.
 If certain dimensions are critical please
 verify those dimensions with your salesperson

FOR INTERNAL USE ONLY PROJECT SIGN OFF	
SALES	
ENG	
FAB.	
POWER	

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN & DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT & INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS & STANDARDS.
ANY MODIFIED UNITS ARE NON-RETURNABLE
 As drawn As marked
 Signed: _____ Date: _____
 Printed Name: _____
 LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME: VESTIL MANUFACTURING		P.O.#: -
DRAWN BY: SR		DATE: 5-12-05
REFERENCE: -	SCALE: 1:14	SALES: -
QUOTED LEADTIME: -	QUOTE #: -	DRWG./FILE NAME: CART-24-15-M