



# HEAVY DUTY PRECISION TURRET BEARING - PTB-40

APPROX WEIGHT: 188 lbs.  
 DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\*ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE\*\*\*



## STANDARD FEATURES

MODEL# PTB-40  
 DIAMETER: 40"  
 HEIGHT: 2 1/4"  
 CAPACITY: 6000 LBS  
 LOW PROFILE DESIGN

- SUPERIOR PLATED FINISH FOR CORROSION RESISTANCE
- GREASE-ABLE POINTS FOR SIMPLE MAINTENANCE
- SHIELDED BEARINGS TO PROTECT DEBRIS AND RETAIN GREASE
- MULTIPLE BOLT LOCATIONS FOR MOUNTING
- CAPTURED BALL BEARING DESIGN PREVENTS RINGS FROM SEPARATING

FOR INTERNAL USE ONLY PROJECT SIGN OFF	
SALES	
ENG.	
FAB.	
POWER	

ALL THE DIMENSIONS ARE IN MM.  
 DIVIDE BY 25.4 TO CONVERT TO IN

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY.  
 IF CERTAIN DIMENSIONS  
 ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS  
 WITH YOUR SALESPERSON

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

**ANY MODIFIED UNITS ARE NON-RETURNABLE**  
 As drawn     As marked

Signed: \_\_\_\_\_ Date: \_\_\_\_\_  
 Printed Name: \_\_\_\_\_

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME: X		P.O.# X
DRAWN BY: SJA		W.O.# X
DATE: 11/2/2016	SALES: X	FILE NAME: PTB-40
REFERENCE: X	SCALE: 1:1	
QUOTED LEAD TIME: X	QUOTE # X	