
MOBILE TILTING WORK TABLE - WPT-1624

APPROX WEIGHT: 95.83 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



Α

Ρ

Ρ

R

0

٧

Α

STANDARD FEATURES

MODEL NUMBER IS WPT-1624 OVERALL WIDTH IS 26 5/16" **OVERALL LENGTH IS 23 3/8"** OVERALL HEIGHT IS 44 1/16" MAX CAPACITY OF UNIFORM EVENLY DISTRIBUTED LOAD IS 200 LBS LOWERED HEIGHT OF LEVEL POSITIONED PLATFORM IS 31 1/2" MAX RAISED HEIGHT OF LEVEL POSITIONED PLATFORM IS 42" PLATFORM SIZE IS 17" W X 24" L LIP HEIGHT IS 2" PLATFORM TILT IS 0° TO 45° PLATFORM HEIGHT AND TILT ARE MANUALLY ADJUSTED (2) 4" X 1 1/4" POLYURETHANE SWIVEL CASTERS (2) 4" X 1 1/4" POLYURETHANE SWIVEL CASTERS W/ DOUBLE LOCKS

SPECIAL FEATURES

NONE

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

ANY MODIFIED UNITS ARE NON-RETURNABLE

[] As drawn [] As marked Signed: Printed Name:_____

<i>LEA</i>	<u>D TIME</u>	WILL	<u>START</u>	<u>UPON</u>	RECEIPT	<u> </u>	SIGNED	<u>APPR</u>	<u>'OVAL</u>	DRAN	/INC
DISTRIBUTO	R'S NAM	E:						P.O.#			

Sierraser erre ru anner	X	
VESTIL MANUFAC	W.O.# X	
DRAWN BY: DEY	DATE: 04/04/2012	SALES: X
reference: X	SCALE: 1:1	4 FILE NAME:
QUOTED LEAD TIME: X	QUOTE #	33-007-061