

➤ **APPROX WEIGHT: 800.81 lbs.**  
➤ ***DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!***

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

## STANDARD FEATURES

MODEL NUMBER: TCD-U-60-AC  
USABLE CHUTE WIDTH: 34 3/4"  
USAGE CHUTE LENGTH: 35 7/8"  
USABLE CHUTE HEIGHT: 77 5/8"

OVERALL LENGTH: 75 5/8"  
OVERALL WIDTH: 46 1/16"  
OVERALL HEIGHT: 78 1/8"

OVERALL ROTATED HEIGHT: 140 1/4"  
MAXIMUM ROTATED ANGLE: 45°  
DUMP HEIGHT: 59 13/16"

WORKS WITH TRASH CANS OF  
17 1/2" TO 34 3/4" WIDTH  
20 1/2" TO 35 7/8" LENGTH  
27" TO 50" HEIGHT

UNIFORM CAPACITY IS 400 LBS


CASTERS:  
FRONT: 8" X 2" GFN SWIVEL  
REAR: 8" X 2" GFN RIGID

## TWO ADJUSTABLE FLOOR LOCKS

POWER UNIT: 115 V AC SINGLE PHASE  
CONTROL: HAND

## SPECIAL FEATURES

NONE



DIMENSION TOLERANCE  $\pm 1/4'$

APPROVAL	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.		FOR INTERNAL USE ONLY PROJECT SIGN OFF		DISTRIBUTOR'S NAME: <b>VESTIL MANUFACTURING</b>		P.O.# X	
	<b>ANY MODIFIED UNITS ARE NON-RETURNABLE</b>		SALES		DRAWN BY: SJA		W.O.# X	
	[ ] As drawn [ ] As marked		ENG.		DATE: 7/23/2016		SALES: X	
	Signed: _____ Date: _____		FAB.		REFERENCE: X		SCALE: 1:32	
	Printed Name: _____		POWER		QUOTED LEAD TIME: X		QUOTE # X	
	LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING						FILE NAME: 34-007-033-001	