
LIFT AND TILT SCISSOR TABLE - EHLTT-4848-1-47 APPROX WEIGHT: 1120.91 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PA *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

APPROX WEIGHT: 1120.91 lbs.

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS EHLTT-4848-1-47 MAX CAPACITY IS 1,000 LBS PLATFORM WIDTH IS 48" FRAME WIDTH IS 30" **OVERALL LENGTH IS 56"** PLATFORM LENGTH IS 48" PLATFORM RAISED HEIGHT IS 47" PLATFORM LOWERED HEIGHT IS 11"

OVERALL HEIGHT IS 83 7/16" PLATFORM TILITS ON THE END OF THE LEG ASSEMBLY PLATFORM TILTING STYLE IS A SLIDE TILT Ø1/4" x 60" CHAIN AND HOOK (NOT DRAWN TO SCALE) MAXIMUM TILT ANGLE IS 45°

SPECIAL FEATURES NONE

F	PLEASE	<u>CIRC</u>	LE	SPE	CII	FIC	ATI	ONS
	POWER	AC		DC	DC (12V)		AIR/OIL	
	MOTOR V	OLTA	GE	115	208	3	230	460
	DEDICATED CIRCUIT REQUIRED 60Hz							0Hz
	motor phase - sh		INGL	NGLE		THREE		
	CONTR	ROL		HANE)		FO) T

FOR INTERNAL USE ONLY

PROJECT SIGN OFF

SALES

ENG.

FAB.

POWER

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
REPRESENTED SATISFIES DESIGN AND DIMENSION
REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
CONFIRM PRODUCT AND INSTALLATION
COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
AND LOCAL REGULATIONS AND STANDARDS.
ANY MODIFIED UNITS ARE NON-RETURNABLE
[] As drawn [] As marked
Signed: Date:
Dale.

QUOTE #

Χ

Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

Ρ

0

V

QUOTED LEAD TIME: Y

1	DISTRIBUTOR'S NAME:		
ı	VESTIL MANUFAC	G	
ı	DRAWN BY: BCN	DATE: 2/3	/2017
1	reference: X		SCALE:

W.O.# SALES: X SCALE: 1:25 FILE NAME:

02-007-021-001

DIMENSION TOLERANCE ± 1/4"