

## **SUPERIOR<sup>®</sup>**

### **Portable Traffic/Security Gate**

**General:** Gates shall be "**Superior Portable Gates**" as manufactured by List Industries Inc. or approved equal.

Gates shall be **GREENGUARD GOLD Certified<sup>SM</sup>**

**Finishing:** Shear Bars are to be zinc plated. Picket Channels are fabricated from galvanized sheet steel. All remaining portable gate parts to be cleaned and coated after fabrication with a seven stage iron phosphate solution to inhibit corrosion, followed by a high-grade powder coat finish electrostatically sprayed and baked at 325 degrees Fahrenheit for a minimum of 30 minutes to provide a tough durable finish. Color: Classic Chrome.

**Vertical Picket Channels:** 3/4" x 3/8" x 14 gauge galvanized steel channel spaced 6" on center.

**Shear Bars (lattice bars):** 3/16" x 5/8" zinc plated flat bar, fitted with free-floating nylon rollers.

**Body of Gate:** Anchored to 2-5/8" x 1" x 12 gauge 7/8" outside diameter welded tubing.

**Carriage Channels:** Shall be 2-5/8" x 1" x 12 gauge cold rolled steel. Each carriage channel is fitted with two 2-1/2" ball bearing swivel casters.

**Unit Retainer Channel:** 2-9/32" x 1" x 12 gauge cold-rolled steel.

**Male Lock Channel:** 2-1/4" x 1" x 12 gauge cold-rolled steel.

**Female Lock Channel:** 1-7/8" x 1-5/8" x 14 gauge box type cold-rolled steel.

**Padlocking Arrangement (standard):** Padlocks by others. Cylinder locking device is an available option providing additional security.

**Floor Anchor Kits (optional):** Available for special installation conditions.

**Warranty:** Superior Portable Gates are covered against all defects in materials and workmanship excluding finish, damage resulting from deliberate destruction and vandalism under this section **for a period of one year from date of purchase.**