HBD BOX DUMPER CUSTOMER INFORMATION CONTACT: SURVEY SHEET COMPANY: ____ PHONE: **CONTAINER TYPE & SIZE** CIRCLE ONE OR MORE: BASKET PALLET **GAYLORD OTHER** IF OTHER, PLEASE DESCRIBE: WIDTH HOLD DOWN LENGTH: WIDTH: HEIGHT DIAMETER: CHUTE HEIGHT: NOTE: 6,000 LB. **CAPACITY UNITS USE DOUBLE-ACTING** STANDARD CHUTE IS 52"W x 50"L. IF SPECIAL CHUTE SIZE IS REQUIRED. CYLINDERS. PLEASE INDICATE IDEAL CHUTE DIMENSIONS: STANDARD FEATURES DUMP HEIGHT AND: HOLD DOWN BAR HEIGHTS 18" - 36" 18" - 42" CAPACITY (CIRCLE ONE): 2,000 LBS. 4,000 LBS. **OPTIONS** (LIST ALL THAT APPLY) SPECIAL DUMP HEIGHT: _____ DUMP HEIGHT SPECIAL CAPACITY: SPECIAL HOLD DOWN BAR HEIGHTS: TAPERED CHUTE (LIST OPENING WIDTH): SPECIAL COLOR (STANDARD BLUE): **VESTIL** STAINLESS STEEL CHUTE: **MANUFACTURING** 2999 N. WAYNE ST. POWER (460V, 3 PHASE STANDARD) IF CUSTOM, INDICATE BELOW **ANGOLA, IN 46703** Ph: 260-665-7586 A/C (110V _____ 220V _____ 460V ____ OTHER ___ Fax: 260-665-1339 SINGLE PHASE _____ THREE PHASE info@vestil.com ROTARY AIR / HYDRAULIC (80 CFM @ 80 PSI, 1/2 GPM) Is this a repeat quote or repeat order? If yes, please idicate Prev. Quote No.: Prev. Order No.: CONTROLS: ____ HAND ____ FOOT ____ AUTOMATED POWER UNIT: EXTERNAL INTERNAL (STANDARD) SIDE MTG. IF EXTERNAL, LENGTH OF CORDS (8' STD): IF ANY OTHER SPECIAL POWER OR CONTROLS ARE REQUIRED, PLEASE INDICATE: **APPLICATION INFORMATION** STARTS PER HOUR: HOURS PER SHIFT: **DUTY CYCLE:** SHIFTS PER DAY: DAYS PER WEEK: DUTY CYCLE IS CALCULATED BY STARTS PER HOUR OR NUMBER OF TIMES "UP" BUTTON IS PUSHED. JOGGING (BOUNCING OF CHUTE) IS NOT RECOMMENDED. ANTICIPATED CYCLE TIME: SPECIAL TEMPERATURE REQUIREMENTS: ARE THERE OVERHEAD HEIGHT RESTRICTIONS? IS THIS A HAZARDOUS LOCATION? IF YES: CLASS: DIV: GROUP: OTHER SPECIAL REQUESTS OR APPLICATION INFORMATION: