

NEW!



Lateral Mobile Aisle with V-Grip™ Shelving

Make the most of limited space with Equipto's affordable high-density system that dramatically increase storage capacity while still permitting immediate access to all storage areas. Movable, lateral systems consist of stationary shelving in the back row and movable shelving in the front row. The movable shelving units are mounted to mobile carriages that are easily moved from side to side on a heavy-duty track. This type of system is exceptionally flexible, can be easily expanded at any time, and provides fast access to multiple layers of storage.

- Buy complete or integrate with your existing storage equipment
- Lateral Track system creates two or three sliding rows of storage
- Mounted independently to the floor in front of new or existing equipment
- No aisles are required; maximum floor space is utilized
- Perfect for alcoves and limited spaces
- Bi-File (two-row) and Tri-File (three-row) high-density lateral sliding shelving systems are an affordable way to maximize storage capacity
- Double or triple the storage space compared to static shelving

The system works well with virtually any type of inventories/equipment and is effective in maximizing storage capacity along walls in narrow rooms or corridors. The concept of the high-density lateral sliding shelving systems is simple: two or three rows of storage equipment placed in nearly the same footprint where there was once only one!

Standard Shelving Units – 84"H x 18"D, overall height of 90"

Part Number	Dimensions	Total Width
273-5-2-1-36M System	(2) 36"W Stationary V-Grip™ Closed Shelving Units (1) Mobile 36"W Shelving Unit	72"
273-5-3-2-36M System	(3) 36"W Stationary V-Grip™ Closed Shelving Units (2) Mobile 36"W Shelving Unit	108"
273-5-4-3-36M System	(4) 36"W Stationary V-Grip™ Closed Shelving Units (3) Mobile 36"W Shelving Unit	144"