



Patented* Antimicrobial Powder Coating uses sustainable silver ions to inhibit the growth and transmission of harmful microbes on treated surfaces.

*Patents US6093407(A), US643241 (B1)



**LIVE HANDRAILS
FOR PATIENT STABILITY**

FALL PREVENTION

Safe patient handling and reducing costs associated with inpatient falls are primary concerns for healthcare providers

- ✔ **“Live” Handrails**
Advanced technology allows the patient to hold onto handrails for stability while the scale accurately calculates weight
- ✔ **Low Profile Platform** requires only minimal step up, offering the patient a more comfortable and stable weighing experience

WORKFLOW EFFICIENCY

Simple to use and intuitive scales allow caregivers to focus on patients instead of complicated equipment

- ✔ **On-Screen Help Menu**
Guides users through operating functions and provides easy access to multiple settings
- ✔ **Interactive Display**
High contrast color screen provides a user-friendly interface
- ✔ **EMR Capable**
Scale has the ability to interface with a PC or other electronic device via USB or optional Pelstar wireless technology
- ✔ **Everlock® (patent pending)**
Option that allows users to permanently lock the scale in either LB or KG to improve safety

INFECTION PREVENTION

Reducing patient's risk against Health-care Associated Infections is a major challenge for medical facilities

- ✔ **Antimicrobial* Powder Coating**
The silver ionic technology suppresses the growth of bacteria and helps protect against cross-contamination

DURABILITY

Facilities require a product to withstand frequent use, movement, and disinfection

- ✔ **Convenient Transport Handle** allows the user to easily move the scale to where it is needed in the facility
- ✔ **Rugged Scuff-Proof Wheels** enable smooth and easy portability



**CONVENIENT
TRANSPORT
HANDLE**



**Optional Height
Rod Available**



SPECIFICATIONS

- Capacity: 1,000 lb / 454 kg
- Resolution: 0.2 lb / 0.1 kg
- Platform Size (w x h x d):
22" x 15 3/4" x 2 5/8" / 559 mm x 400 mm x 67 mm
- Handrail Width: 20" / 508 mm
- Product Footprint (w x h x d):
22" x 33 1/8" X 52" / 559 mm x 841 mm x 1321 mm
- Product Weight: 42 lb / 19 kg
- Display: 1 1/2" / 38 mm High Contrast Color TFT-LCD Screen
- Rugged Scuff-Proof Wheels: 2
- Power Source: 100-240V Adapter ADPT30 (included), 6 D batteries (not included)
- Connectivity: USB, optional Pelstar wireless technology
- Functions: LB/KG Conversion, LB/KG Lock Out, Body Mass Index (BMI), Zero, Tare, Pre-tare, Hold/Release, Recall, Reweigh, Auto Zero, Auto Off, Time/Date, Variable Auto Off Time, Audible/Mute Sound Option, Everlock®
- 2 year limited warranty

| Model | Description |
|--------------|------------------------------------------------------------------|
| 3001KL-AM | Digital platform scale, pounds & kilograms |
| 3001KG-AM | Digital platform scale, kilograms only |
| 3001KL-AMUA | Scale ships unassembled, pounds & kilograms |
| 3001KG-AMUA | Scale ships unassembled, kilograms only |
| 3001KL-AMHR | Scale assembled with height rod included, pounds and kilograms |
| 3001KG-AMHR | Scale assembled with height rod included, kilograms only |
| ADPT30 | Adapter included, item # for replacement or spare |
| PLUGSET30 | Plug adapters for use outside North America |
| 3001HR | Optional height rod for 3001 models that dont include height rod |
| SS-3001KL-AM | ScaleSurance 2 year extended warranty (3001 models)* |
| PELSTARONE-P | Wireless thermal printer |

antimicrobial technology

* Not available in all countries

