

1. Identification

Product identifier **Uvex Clear Solution**

Other means of identification

Product code S471, S482, S483, S484

Recommended use Lens cleaning solution.

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Company name: Honeywell Safety Products USA, Inc

Address: 825 East Highway 151
Platteville, WI 53818 USA

Telephone: 800 873 5242

Contact Person hsptechsupport@honeywell.com

E-mail: msds@chemtrec.com

Emergency telephone number: +1-703-741-5500 for USA/Canada

2. Hazard(s) identification

Physical hazards Not classified.

Health hazards Not classified.

OSHA defined hazards Not classified.

Label elements

Hazard symbol None.

Signal word None.

Hazard statement The mixture does not meet the criteria for classification.

Precautionary statement

Prevention Observe good industrial hygiene practices.

Response Wash hands after handling.

Storage Store away from incompatible materials.

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	%
1-Methoxy-2-propanol	107-98-2	<1

Composition comments All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

Inhalation If symptomatic, move to fresh air. Get medical attention if symptoms persist.

Skin contact Wash skin with soap and water. Get medical attention promptly if symptoms occur after washing.

Eye contact Remove contact lenses. Get medical attention promptly if symptoms occur after flushing.

Ingestion Seek medical advice.

Most important symptoms/effects, acute and delayed	No specific symptoms noted.
Indication of immediate medical attention and special treatment needed	Treat symptomatically.
General information	In the case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

5. Fire-fighting measures

Suitable extinguishing media	Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media	No restrictions known.
Specific hazards arising from the chemical	None.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Self-contained breathing apparatus operated in positive pressure mode and full protective clothing must be worn in case of fire.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. For industrial use, wear appropriate personal protective equipment (See Section 8).
Methods and materials for containment and cleaning up	<p>Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.</p> <p>Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.</p> <p>Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.</p>
Environmental precautions	Treat discharge into drains, water courses or onto the ground according to applicable regulations.

7. Handling and storage

Precautions for safe handling	Observe good industrial hygiene practices. Avoid inhalation of vapors and contact with skin and eyes.
Conditions for safe storage, including any incompatibilities	Keep container closed. Store away from incompatible materials. Do not allow material to freeze. Store at room temperature.

8. Exposure controls/personal protection

Occupational exposure limits

US. ACGIH Threshold Limit Values

Components	Type	Value
1-Methoxy-2-propanol (CAS 107-98-2)	STEL	100 ppm
	TWA	50 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
1-Methoxy-2-propanol (CAS 107-98-2)	STEL	540 mg/m3
		150 ppm
	TWA	360 mg/m3
		100 ppm

Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	No exposure standards allocated.

US - California OELs: Skin designation

1-Methoxy-2-propanol (CAS 107-98-2)

Can be absorbed through the skin.

Appropriate engineering controls Not required.**Individual protection measures, such as personal protective equipment****Eye/face protection** None under normal conditions.**Skin protection****Hand protection** Chemical resistant gloves are recommended.**Other** None under normal working conditions.**Respiratory protection** Not normally needed.**Thermal hazards** Wear appropriate thermal protective clothing, when necessary.**General hygiene considerations** Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking.**9. Physical and chemical properties****Appearance****Physical state** Liquid.**Form** Liquid.**Color** Blue.**Odor** Fruity.**Odor threshold** Not available.**pH** 7 estimated**Melting point/freezing point** 32 °F (0 °C) estimated**Initial boiling point and boiling range** 212 °F (100 °C) estimated**Flash point** > 200.0 °F (> 93.3 °C)**Evaporation rate** Similar to water.**Flammability (solid, gas)** Not applicable.**Upper/lower flammability or explosive limits****Flammability limit - lower (%)** Not available.**Flammability limit - upper (%)** Not available.**Vapor pressure** Similar to water.**Vapor density** Not available.**Relative density** Not available.**Solubility(ies)****Solubility (water)** Miscible.**Partition coefficient (n-octanol/water)** Not available.**Auto-ignition temperature** Not available.**Decomposition temperature** Not available.**Viscosity** Similar to water.**Other information****Density** 1.00 g/ml estimated**Explosive properties** Not explosive.**Oxidizing properties** Not oxidizing.**10. Stability and reactivity****Reactivity** The product is stable and non-reactive under normal conditions of use, storage and transport.**Chemical stability** Material is stable under normal conditions.**Possibility of hazardous reactions** Hazardous polymerization does not occur.

Conditions to avoid	Contact with incompatible materials. Freezing. Elevated temperatures.
Incompatible materials	Strong oxidizers, strong acids, and strong bases.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Prolonged or repeated contact may dry skin and cause irritation.
Eye contact	May cause temporary eye irritation.
Ingestion	No harmful effects expected in amounts likely to be ingested by accident.

Symptoms related to the physical, chemical and toxicological characteristics No specific symptoms noted.

Information on toxicological effects

Acute toxicity Not expected to be acutely toxic.

Components	Species	Test Results
1-Methoxy-2-propanol (CAS 107-98-2)		
Acute		
Dermal		
LD50	Rabbit	13000 mg/kg
Oral		
LD50	Rat	> 5000 mg/kg

Skin corrosion/irritation Prolonged or repeated contact may dry skin and cause irritation.

Serious eye damage/eye irritation May cause temporary eye irritation.

Respiratory or skin sensitization

Respiratory sensitization	Not classified.
Skin sensitization	Not a skin sensitizer.

Germ cell mutagenicity Not classified.

Carcinogenicity Not classified.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

NTP Report on Carcinogens

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Reproductive toxicity Not classified.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not classified.

Chronic effects Not classified.

Further information No other specific acute or chronic health impact noted.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence and degradability No data available.

Bioaccumulative potential The product is not expected to bioaccumulate.

Mobility in soil This product is miscible in water. Expected to be mobile in soil.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations. Do not allow runoff to sewer, waterway or ground.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company. Waste codes should be assigned by the user based on the application for which the product was used.

Waste from residues / unused products Dispose of in accordance with local regulations.

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

US federal regulations This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Toxic Substances Control Act (TSCA) All components of the mixture on the TSCA 8(b) inventory are designated "active".

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

1-Methoxy-2-propanol (CAS 107-98-2)

US. New Jersey Worker and Community Right-to-Know Act

1-Methoxy-2-propanol (CAS 107-98-2)

US. Pennsylvania Worker and Community Right-to-Know Law

1-Methoxy-2-propanol (CAS 107-98-2)

US. Rhode Island RTK

1-Methoxy-2-propanol (CAS 107-98-2)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

1-Methoxy-2-propanol (CAS 107-98-2)

International Inventories


Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	16-September-2019
Revision date	-
Version #	01
Further information	The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

NFPA ratings**References**

EPA: Acquire database
 ACGIH
 ACGIH Documentation of the Threshold Limit Values and Biological Exposure Indices
 HSDB® - Hazardous Substances Data Bank
 IARC Monographs. Overall Evaluation of Carcinogenicity
 National Toxicology Program (NTP) Report on Carcinogens
 NLM: Hazardous Substances Data Base
 US. IARC Monographs on Occupational Exposures to Chemical Agents
 ESIS (European chemical Substances Information System)

Disclaimer

This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.