



ACA Industrial & Industrial Weatherproof Cord Reels

Providing improved solutions through innovation

Hubbell's redesigned ACA Industrial and Industrial Weatherproof Cord Reels enhance user safety and maximize efficiency by managing cord and power in a safe and organized manner, while also meeting the demands of tough industrial environments.

ACA Industrial and Industrial Weatherproof Cord Reels are listed to UL 355 and CSA, C22.2 No. 308 with a durable, lightweight low profile cast aluminum construction. ACA reels also feature an improved mounting plate that allows customers to upgrade existing installations or use Hubbell's innovative mounting bracket for a quick, easy installation on any surface.

FEATURES

ACA Industrial & Industrial Weatherproof Cord Reels

- Durable, corrosion resistant cast aluminum construction
- Yellow or white powder coat finish
- Movable guide arm can be mounted in two positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- 16-10AWG, 3 & 4 conductor cord for greater current carrying capacity
- 10AWG fully rated at 30 amps
- Available in 25ft, 35ft and 45ft lengths

ACA Industrial Cord Reels

- UL Type 1
- 250V AC, SJO Type Cable
- Plug-in 5ft long power cord requires no electrical wiring

WCA Industrial Weatherproof Cord Reels


- UL Type 4
- 600V AC, SOW Type Cable
- 3/4 NPT conduit hub



ACA Mounting Bracket

Labor Savings Are Reel

The ACA mounting bracket allows you to decrease or eliminate the additional labor associated with installing reels at the end of the job. By starting the installation during the earlier stages of the project when there are fewer time constraints, the ACA mounting bracket reduces trim-out to a fraction of the time.



Step 1
Secure the ACA mounting bracket during the rough-in process.



Step 2
Remove two of the hex bolts from the bracket. Slide the reel into the mounting bracket.



Step 3
Replace two hex bolts and secure screws to complete the job.



WCA/ACA Industrial Reels



Series WCA Industrial Weatherproof Cord Reels (Yellow)

Accessory	Amps	Voltage	AWG	Cond.	Cord Type	Length Ft. (m)	Weight (kg)	Lbs.	Model
None	10	600V AC	16	3	SOW	45 (13.7)	23.6 (10.7)		WCA16345-BC
None	10	600V AC	16	4	SOW	45 (13.7)	25.6 (11.6)		WCA16445-BC
None	15	600V AC	14	3	SOW	45 (13.7)	28.2 (12.8)		WCA14345-BC
None	15	600V AC	14	4	SOW	45 (13.7)	30.0 (13.6)		WCA14445-BC
None	20	600V AC	12	3	SOW	45 (13.7)	31.3 (14.2)		WCA12345-BC
None	20	600V AC	12	4	SOW	40 (12.2)	32.2 (14.6)		WCA12440-BC
None	30	600V AC	10	3	SOW	40 (12.2)	33.3 (15.1)		WCA10340-BC
None	30	600V AC	10	4	SOW	35 (10.7)	34.2 (15.5)		WCA10435-BC

Note:- The above models are supplied without input or output end effectors.
 For shorter cable lengths, modify length indication in catalog number (i.e. WCA123XX); 35ft. & 25ft. Lengths available.
 For white reels, add "W" suffix to end of model number.



Series ACA Industrial Cord Reels (Yellow)

Accessory	Amps	Voltage	AWG	Cond.	Cord Type	Length Ft. (m)	Weight (kg)	Lbs.	Model
None	10A	250V AC	16	4	SJO	45 (13.7)	23.6 (10.7)		ACA16445-BC
None	15A	250V AC	14	4	SJO	45 (13.7)	25.6 (11.6)		ACA14445-BC
None	20A	250V AC	12	4	SJO	45 (13.7)	28.2 (12.8)		ACA12445-BC
None	30A	250V AC	10	4	SJO	45 (13.7)	30.0 (13.6)		ACA10345-BC
None	30A	250V AC	10	4	SJO	40 (12.2)	31.3 (14.2)		ACA10440-BC

Note:- The above models are supplied without input or output end effectors.
 For shorter cable lengths, modify length indication in catalog number (i.e. ACA124XX); 35ft. & 25ft. Lengths available.
 For white reels, add "W" suffix to end of model number.



Single Receptacle HBL5269C	10A	125V AC	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-SR15
Single Receptacle HBL5269C	15A	125V AC	14	3	SJO	45 (13.7)	24.0 (10.9)		ACA14345-SR15
Single Receptacle HBL5369C	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)		ACA12345-SR20
Dual Receptacle GFCI Module & (1) 15A Duplex Receptacle	10A	125V AC	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-DR15
Dual Receptacle GFCI Module & (1) 15A Duplex Receptacle	15A	125V AC	14	3	SJO	45 (13.7)	24.0 (10.9)		ACA14345-DR15
Dual Receptacle GFCI Module & (1) 20A Duplex Receptacle	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)		ACA12345-DR20
Blind Cord No Output End Effector	10A	125V AC	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-BC15
Blind Cord No Output End Effector	15A	125V AC	14	3	SJO	45 (13.7)	24.0 (10.9)		ACA14345-BC15
Blind Cord No Output End Effector	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)		ACA12345-BC20
Twist Lock HBL2313	20A	125V AC	12	3	SJO	45 (13.7)	26.5 (12.0)		ACA12345-TL20

Note:- 10A & 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord.
 For shorter cable lengths, modify length indication in catalog number (i.e. ACA123XX); 35ft. & 25ft. Lengths available.
 For white reels, add "W" suffix to end of model number.



Series ACA Industrial Lighted Cord Reels (Yellow)

Accessory	Amps Watts	Voltage	AWG	Cond.	Cord Type	Length Ft. (m)	Weight (kg)	Lbs.	Model
LED Hand Lamp with end light	0.07A 8+1	120V	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-LED
Fluorescent Hand Lamp	0.3A 13	120V	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-FL
Incandescent Hand Lamp	0.8A 100	125V	16	3	SJO	45 (13.7)	22.9 (10.4)		ACA16345-HL

Note:- 15A reels are supplied with HBL5266C on the power supply cord.
 For shorter cable lengths, modify length indication in catalog number (i.e. ACA163XX); 35ft. & 25ft. Lengths available.
 For white reels, add "W" suffix to end of model number.



WCA/ACA Mounting Accessories

Description	Weight lbs. (kg)	Model
Mounting bracket	2.5 (1.1)	HBL16BS
340° pivot base	3.5 (1.6)	HBL1340PB

WCA/ACA Replacement Parts

Description	Weight lbs. (kg)	Cable Type	Model
Replacement stop	0.2 (.09)	16AWG	HBL116BS
		14AWG	HBL114BS
		12AWG	HBL112BS
		10AWG	HBL110BS



<https://www.hubbell.com/gleasonreel>

