




## Fixed or 180° Swinging WS50 Booms



USE: Wall or column mounted tool rail; or use two fixed booms as support for horizontal tool rail. (Cross rail and hangers not included). End stop and end cap included. \*Eight foot (2.4m), ten foot (0.3m) and 18 foot (5.4m) booms include ladder style reinforcing superstructure. Trolley extra. Beige polyester finish.



TYPE	Dim. A in. (mm)
Swing	8.12 (206)
Fixed	7.75 (197)

### MOUNTING HOLE LAYOUT 4'-12' BOOMS

### MOUNTING HOLE LAYOUT 18' BOOM



**WS50 Rail for loads up to 50 lbs. (22.5 kg)**

BOOM LENGTH ft. (m)	BOOM TYPE	MODEL NUMBER
4.0 (1.2)	Fixed	WF50-WS04
4.0 (1.2)	Swing	WS50-WS04
6.0 (1.8)	Fixed	WF50-WS06
6.0 (1.8)	Swing	WS50-WS06
8.0* (2.4)	Fixed	WF50-WS08
8.0* (2.4)	Swing	WS50-WS08
10.0* (3.0)	Fixed	WF50-WS10
10.0* (3.0)	Swing	WS50-WS10
12.0* (3.7)	Swing	WS50-WS12
18.0* (5.4)	Swing	WS50-WS18


\*Features ladder style reinforcing rather than tie rod. Model WS50-WS18 has stacked (doubled) rail for additional strength.

### WS-UB U-BOLT ASSEMBLY

USE: Secures 4'-10' booms or other flat plates to 3" dia. vertical column. Three are required to mount boom onto vertical column. Do not use for mounting 18' boom (#WS50-WS18). Zinc plated steel.

## Rail Mounted Fixed or Swing Booms

USE: Tool rail mounted to WS50 or WA50 vertical column. End stop, end cap, safety bolt and all hardware included. Trolley extra. Beige polyester finish.




**WS30 Rail for loads up to 30 lbs. (13.5 kg)**

BOOM LENGTH ft. (m)	BOOM TYPE	MODEL NUMBER
3.0 (0.9)	Fixed	WF30-DS03
3.0 (0.9)	Swing	WS30-DS03
4.0 (1.2)	Swing	WS30-DS04

## Wall Mounted Booms

USE: Wall mounted tool rail. End stop, end cap and safety bolt included. Trolley extra. Beige polyester finish.



**WS30 Rail for loads up to 30 lbs. (13.5 kg)**

BOOM LENGTH ft. (m)	BOOM TYPE	MODEL NUMBER
3.0 (0.9)	Fixed	WF30-WS03
3.0 (0.9)	Swing	WS30-WS03
4.0 (1.2)	Fixed	WF30-WS04
4.0 (1.2)	Swing	WS30-WS04



BOOM TYPE	Dim. A in. (mm)
Fixed	3.38 (85)
Swing	3.19 (81)

## BASES AND SUPPORTS

These bases are larger than those listed with the track components and are used primarily when a more rigid structure is desired. All bases include all hardware for mounting rail to base.

### BENCH LEG BASE


USE: Mounts workstation to bench by providing a "pocket" into which WS50 track may be fitted. Models for 30" (762) or 36" (914) deep benches. Universal hole pattern in foot plus adjustable "Joiner Plate Box" provide solid grip to the bench leg. Includes hardware required for mounting rail to base. Does not include hardware required to mount base to bench. Joiner plate box included and also available separately. Black polyester finish.



Model Number	Length
62829003	3 ft.
62829006	6 ft.
62829008	8 ft.
62829009	9 ft.
62829010	10 ft.
62829011	11 ft.
62829012	12 ft.


### WS50 VERTICAL HANGER SUPPORT ASSEMBLY KIT

Hanging a tool rail safely from an overhead structure may be the best way to put a workstation where it's needed. These kits consist of a 12" long cross rail section welded to a 3 ft., 6 ft. or 9 ft. vertical rail section and a WS50-MB Mounting Base. These 50 lb. capacity hangers are for use with WS50 steel track and are sold only as kits. Tool track must be supported every six feet to preserve 50 lb. capacity rating.



### TABLE BRACKETS

USE: Mounts WS50 or WA50 vertical support columns to typical work bench. Provides greater rigidity when mounted to sheet metal tops than standard bases. For even greater strength, use model #WS50-BBS backing plate (optional) beneath bench top. Includes hardware for mounting rail to bracket. Does not include hardware for mounting base to bench. Black polyester finish.



### SUPPORT CLAMP

#### WS50-SC-For WS50 (steel) Rail WA50-SC-For WA50 (Aluminum) Rail

USE: Fasten rail to back of bench for added stability. Typically used with WS50-MB base. Black polyester finish.

**WS60-SC-For WS60 (steel) Rail also available. Mounting dimensions differ from WS50-SC.**