



- NOTES:
1. GUARD THICKNESS: 0.188 IN
 2. OVERALL HEIGHT: 36.000 IN
 3. ALL HOLES: .5625 IN
 4. HOLES 2 IN FROM ENDS
 5. MID HOLES EVENLY SPACED
 6. FASTENERS AND HARDWARE NOT INCLUDED

NON RETURNABLE

This drawing and data contained herein, are the sole property of Bluff Manufacturing. This information is considered confidential and subject to return on demand. This drawing and contents cannot be reproduced or given to a 3rd party without the written consent of an authorized representative of Bluff. The sole intent of this drawing and data is to establish a written approval agreement between Bluff and customer for Bluff to proceed with manufacturing defined herein. Accepting this drawing in hardcopy, or any form of electronic communication, will be considered a binding agreement to these terms.

APPROVAL BLOCK

- _____ APPROVED AS IS FOR MANUFACTURING.
- _____ APPROVED AS IS FOR MANUFACTURING WITH REVISIONS NOTED.
- _____ REVISE AS NOTED AND RESUBMIT.
INITIAL

****NOTE: MANUFACTURING WILL NOT COMMENCE UNTIL THE SIGNED APPROVAL DRAWING IS RECEIVED BY BLUFF MANUFACTURING.****

SIGNATURE

DATE

PGWM436

TOLERANCE SPECIFICATION (Unless Noted Otherwise)		DRAWN: Configurator	DATE: 7/7/2020	BLUFF Manufacturing 9201 SOUTH FREEWAY FORT WORTH, TEXAS 76140	
DIMENSION UNITS: (inches)		CHECKED:	DATE:		
LINEAR:	PERPENDICULAR:	SO #:	SHIP DATE:	TITLE	
0.X ± 0.06 (1/16")	⊥ ± (1/16" / ft)	QTY:	CUSTOMER:		
0.XX ± 0.03 (1/32")		FINISH - PREPARATION: SSPC-SP6	FINISH - APPLICATION: Powder Coat	SIZE	DWG NO
0.XXX ± 0.010		FINISH - COLOR: Yellow	ESTIMATED WEIGHT: 41.696 lb	C	PGWM436
WELD: +0.06/-0.00, —				REV	
REMOVE BURRS				SHEET 1 OF 1	