



**GLOBAL™
INDUSTRIAL**

Model 761217 Wall Mounted Filtered Water Cooler

Specifications



*Rated for indoor
use only*

Model 761217 Wall Mounted Filtered Water Cooler

FEATURES:

- Easy-touch front and side push-bar control
- Keyed door for easy filter access
- Laminar water flow ensures minimal splash
- Drainage system eliminates standing water
- LED filter level indicator display
- Flexible safety bubbler
- Rust-proof and dent resistant lower cover

These claims verified through internal manufacture testing

COOLING SYSTEM:

- Hermetically-sealed, single-phase reciprocating compressor; lifetime lubrication
- Fan cooled condenser with copper tube and aluminum fins; permanently lubricated motor
- Cooling system includes self-cleansing tube tank, continuous copper tubing, stainless steel tank and EPS foam insulation; meets UL requirements for self-extinguishing material
- R134a refrigerant control accurately calibrates capillary tubes
- Easily accessible and adjustable thermostat

Replacement Filters - Model 670336

- 3600-gallon capacity filtration system with NSF/ANSI 42 & 53 (lead, class 1 particulate, chlorine, taste and odor)

CONSTRUCTION:

- Stainless steel pan with integral drain
- Galvanized structural steel frame
- Rust-proof and dent resistant lower cover

Meets all ADA Guidelines

System 761217 certified by IAPMO R&T against

NSF/ANSI/CAN 372 for lead free compliance

Meets Federal and State Low-Lead Law Requirements

Certified to UL399 and CAN/CSA 22.2 No. 120




WARRANTY:

5 year limited warranty on refrigeration system. Electrical components and water system are warranted for 12 months from the date of installation, or 18 months from the factory shipment date (whichever date comes first).

Replacement Filters: Model 670336



*For more information visit: globalindustrial.com
or call 1-800-645-1232*

Specifications Chart

Specifications Chart							
Model	Voltage/Hertz	*Chilling Cap.	F.L. Amps	Rated Watts	UL399 and CAN/CSA 22.2 No. 120 Certified	ADA Compliant	System 761217 certified by IAPMO R&T against NSF/ANSI/CAN 372 for lead free compliance
761217	115V/60Hz	8 GPH	2.1	165	✓	✓	✓

*At 46° - 54° (F) against ambient air temperature of 77° (F)

PATENTED AND OTHER PATENTS PENDING



LEGEND:

A = Recommended water inlet supply location. Installation of a water shut-off valve (not included) to accept 3/8" O.D. unplated copper tube. Maximum of 3" from the wall.

B = Recommended water outline supply line location; to accommodate 1-1/4" nominal drain. Drain stub 2" from the wall.

C = Electrical supply: 3-wire recessed duplex receptacle.

D = Side louvers: Ensure proper ventilation is maintained by allowing 6" minimum clearance from the water cooler louvers on both sides of the machine to the wall.

E = 7/16" dia. wall anchor holes for fastening water cooler to the wall. This unit requires 75 lb. minimum wall anchors.

WARNING: Installations must use a GFCI (Ground Fault Circuit Interrupter)

Project Name: _____

Global Part Number: _____ Qty. _____

Contact Info: _____

Project Notes:

Approved By: _____ Signature: _____